

4

THIS DRAWING IS UNPUBLISHED.

20

3

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

2

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

DIFFERENT CODINGS

VO MARK FOR PN: 2-2311788-1 / 2-2311788-2

5-2311788-3

X	F	F	X	X	X	X	X	X	X
A-D		X	X	X	X				

DIM:310*210*28.85mm

8	0.63 SQ PIN	CuZn30	Sn OVER Ni	3
4	0.8X2.8 TAB PIN	CuZn30	Sn OVER Ni	2
1	12 WAY HOUSING	PA10T OR SPS	BLACK	4

5-2311788-2

F	X	X	F	X	X	X	X	X	X
B-C		X	X	X	X				

DIM:320*210*29mm

8	0.63 SQ PIN	CuZn30	Sn OVER Ni	3
4	0.8X2.8 TAB PIN	CuZn30	Sn OVER Ni	2
1	12 WAY HOUSING	PA10T OR SPS	BROWN	4

5-2311788-1

X	F	F	X	X	X	X	X	X	X
A-D		X	X	X	X				

DIM:320*210*29mm

8	0.63 SQ PIN	CuZn30	Sn OVER Ni	3
4	0.8X2.8 TAB PIN	CuZn30	Sn OVER Ni	2
1	12 WAY HOUSING	PA10T OR SPS	BLACK	4

4-2311788-2

F	X	X	F	X	X	X	X	X	X
B-C		X	X	X	X				

DIM:320*210*29mm

8	0.63 SQ PIN	CuZn30	Sn OVER Ni	3
4	0.8X2.8 TAB PIN	CuZn30	Sn OVER Ni	2
1	12 WAY HOUSING	PA10T OR SPS	BROWN	4

4-2311788-1

X	F	F	X	X	X	X	X	X	X
A-D		X	X	X	X				

DIM:320*210*29mm

8	0.63 SQ PIN	CuZn30	Sn OVER Ni	3
4	0.8X2.8 TAB PIN	CuZn30	Sn OVER Ni	2
1	12 WAY HOUSING	PA10T OR SPS	BLACK	4

2-2311788-2

A10

F	X	X	F	X	X	X	X	X	X
B-C		X	X	X	X				

REEL DIM:56*24mm

8	0.63 SQ PIN	CuZn30	Sn OVER Ni	3
4	0.8X2.8 TAB PIN	CuZn30	Sn OVER Ni	2
1	12 WAY HOUSING	PA10T V0	BROWN	4

2-2311788-1

A10

X	F	F	X	X	X	X	X	X	X
A-D		X	X	X	X				

REEL DIM:56*24mm

8	0.63 SQ PIN	CuZn30	Sn OVER Ni	3
4	0.8X2.8 TAB PIN	CuZn30	Sn OVER Ni	2
1	12 WAY HOUSING	PA10T V0	BLACK	4

1-2311788-8

X	F	F	X	X	X	X	X	X	X
A-D		X	X	X	X				

REEL DIM:56*24mm

8	0.63 SQ PIN	CuZn30	Sn OVER Ni	3
4	0.8X2.8 TAB PIN	CuZn30	Sn OVER Ni	2
1	12 WAY HOUSING	PA10T OR SPS	BLACK	4

1-2311788-7

F	X	F	X	X	X	X	X	X	X
B-D		X	X	X	X				

REEL DIM:56*24mm

8	0.63 SQ PIN	CuZn30	Sn OVER Ni	3
4	0.8X2.8 TAB PIN	CuZn30	Sn OVER Ni	2
1	12 WAY HOUSING	PA10T OR SPS	BLUE	4

1-2311788-6

X	F	X	F	X	X	X	X	X	X
A-C		X	X	X	X				

REEL DIM:56*24mm

8	0.63 SQ PIN	CuZn30	Sn OVER Ni	3
4	0.8X2.8 TAB PIN	CuZn30	Sn OVER Ni	2
1	12 WAY HOUSING	PA10T OR SPS	GREEN	4

1-2311788-5

F	X	X	F	X	X	X	X	X	X
B-C		X	X	X	X				

REEL DIM:56*24mm

8	0.63 SQ PIN	CuZn30	Sn OVER Ni	3
4	0.8X2.8 TAB PIN	CuZn30	Sn OVER Ni	2
1	12 WAY HOUSING	PA10T OR SPS	BROWN	4

1-2311788-4

F	X	F	X	X	X	X	X	X	X
B-D		X	X	X	X				

DIM:375*275*31mm

8	0.63 SQ PIN	CuZn30	Sn OVER Ni	3
4	0.8X2.8 TAB PIN	CuZn30	Sn OVER Ni	2
1	12 WAY HOUSING	PA10T OR SPS	BLUE	4

1-2311788-3

X	F	X	F	X	X	X	X	X	X
A-C		X	X	X	X				

DIM:375*275*31mm

8	0.63 SQ PIN	CuZn30	Sn OVER Ni	3
4	0.8X2.8 TAB PIN	CuZn30	Sn OVER Ni	2
1	12 WAY HOUSING	PA10T OR SPS	GREEN	4

1-2311788-2

F	X	X	F	X	X	X	X	X	X
B-C		X	X	X	X				

DIM:375*275*31mm

8	0.63 SQ PIN	CuZn30	Sn OVER Ni	3
4	0.8X2.8 TAB PIN	CuZn30	Sn OVER Ni	2
1	12 WAY HOUSING	PA10T OR SPS	BROWN	4

1-2311788-1

X	F	F	X	X	X	X	X	X	X
A-D		X	X	X	X				

DIM:375*275*31mm

8	0.63 SQ PIN	CuZn30	Sn OVER Ni	3
4	0.8X2.8 TAB PIN	CuZn30	Sn OVER Ni	2
1	12 WAY HOUSING	PA10T OR SPS	BLACK	4

6-2311788-5

A10

X	F	F	X	-	X	X	X	X	X	-
A-D		X	X	X	X					

DIM:320*210*28.5mm

6	0.63 SQ PIN	CuZn30	Sn OVER Ni	3
4	0.8X2.8 TAB PIN	CuZn30	Sn OVER Ni	2
1	12 WAY HOUSING	PA10T OR SPS	BLACK	4

2311788-8

F	X	F	X	-	X	X	X	X	X	-
B-D		X	X	X	X					

DIM:375*275*31mm

6	0.63 SQ PIN	CuZn30	Sn OVER Ni	3
4	0.8X2.8 TAB PIN	CuZn30	Sn OVER Ni	2
1	12 WAY HOUSING	PA10T OR SPS	BLUE	4

2311788-7

X	F	X	F	-	X	X	X	X	X	-
A-C		X	X	X	X					

DIM:375*275*31mm

6	0.63 SQ PIN	CuZn30	Sn OVER Ni	3
4	0.8X2.8 TAB PIN	CuZn30	Sn OVER Ni	2
1	12 WAY HOUSING	PA10T OR SPS	GREEN	4

2311788-6

F	X	X	F	-	X	X	X	X	X	-
B-C		X	X	X	X					

DIM:375*275*31mm

6	0.63 SQ PIN	CuZn30	Sn OVER Ni	3
4	0.8X2.8 TAB PIN	CuZn30	Sn OVER Ni	2
1	12 WAY HOUSING	PA10T OR SPS	BROWN	4

2311788-5

X	F	F	X	-	X	X	X	X	X	-
A-D		X	X	X	X					

DIM:375*275*31mm

6	0.63 SQ PIN	CuZn30	Sn OVER Ni	3
4	0.8X2.8 TAB PIN	CuZn30	Sn OVER Ni	2
1	12 WAY HOUSING	PA10T OR SPS	BLACK	4

2311788-4

F	X	F	X	-	-	-	-	-	-	-
B-D		X	X	X	X					

DIM:375*275*31mm

4	0.8X2.8 TAB PIN	CuZn30	Sn OVER Ni	2
1	4 WAY HOUSING	PA10T OR SPS	BLUE	1

2311788-3

X	F	X	F	-	-	-	-	-	-	-
A-C		X	X	X	X					

DIM:375*275*31mm

4	0.8X2.8 TAB PIN	CuZn30	Sn OVER Ni	2
1	4 WAY HOUSING	PA10T OR SPS	GREEN	1

2311788-2

F	X	X	F	-	-	-	-	-	-	-
B-C		X	X	X	X					

DIM:375*275*31mm

4	0.8X2.8 TAB PIN	CuZn30	Sn OVER Ni	2
1	4 WAY HOUSING	PA10T OR SPS	BROWN	1

2311788-1

X	F	F	X	-	-	-	-	-	-	-
A-D		X	X	X	X					

DIM:375*275*31mm

4	0.8X2.8 TAB PIN	CuZn30	Sn OVER Ni	2
1	4 WAY HOUSING	PA10T OR SPS	BLACK	1

TE P/N

DESCRIPTION

A	B	C	D	5	6	7	8	9	10	11	12
CODING				PIN LOCATION							

TRAY

QTY	PART DESCRIPTION	MATERIAL	COLOR/FINISH	ITEM NO
-----	------------------	----------	--------------	---------

“X”...EXISTING

“F”...FILLED

“-”...DO NOT EXISTING

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	K.WEI	18JUN2017
CHK	E.JIANG	08AUG2017
APVD	L.YIN	09AUG2017

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	0 PLC ±0.1
	1 PLC ±0.1
	2 PLC ±0.01
	3 PLC ±0.001
	4 PLC ±0.0001
	ANGLES ±
MATERIAL	FINISH
-	-
-	-

PRODUCT SPEC	-
APPLICATION SPEC	-
WEIGHT	-
CUSTOMER DRAWING	-

TE Connectivity

NAME

4 WAY POWER/10 WAY/12 WAY HYBRID HEADER

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C=2311788	-

SCALE	2:1	SHEET	2	OF	2	REV	A10
-------	-----	-------	---	----	---	-----	-----

1471-9 (3/13)