








REV.	ECN NO OR DESCRIPTION	REVISED	DATE




- NOTES:
1. MATERIAL:
 - 1.1 HOUSING: HIGH TEMPERATURE THERAL PLASTIC, COLOR: SEE TABLE .
 - 1.2 CONTACT & LATCH: COPPER ALLOY .
 2. FINISH:
 - 2.1 CONTACT: (SEE TABLE) GOLD PLATED ON CONTACT AREA, 100μ" MIN. MATTE-TIN ON SOLDER TAIL, WITH ENTIRE CONTACT UNDERPLATED 50μ" MIN. NICKEL.
 - 2.2 LATCH: 100μ" MIN. TIN OVER 50μ" MIN. NICKEL PLATED.



UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS:	ANGLES:	TITLE	SATA 7+15P 沉板0.9公座		
X : ±0.25	X : ±2°	DWN	xiong	PART NO. SATA-012-M22S1BY-B	
X.X : ±0.20	X.X : ±1°	CHKD	lee	SCALE: 1:1	UNIT: mm
X.XX : ±0.15		APVD	wang	SIZE: A4	SHEET: 10F 1
		CUSTOMER COPY			
				REV: A4	



REV.	ECN NO OR DESCRIPTION	REVISED	DATE





一吸塑盒=60PCS

最上层放一个空吸塑盒

每叠=20盘

PE膜“工”字型缠绕

4叠=80盘



△ 说明:

1. 一盘吸塑盒=60 PCS
2. 每叠20盘=60 PCS/盘*20
=1200 PCS
3. 一箱=4叠=每叠1200 PCS *4
=4800 PCS/箱

UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS:	ANGLES:	TITLE	SATA 7+15P 沉板0.9公座		
X :±0.25	X :±2°	DWN	xiong	PART NO. SATA-012-M22S1BY-B	
X.X :±0.20	X.X :±1°	CHKD	lee	SCALE:1:1	UNIT: mm
X.XX :±0.15		APVD	wang	SIZE: A4	SHEET:10F 1
		CUSTOMER COPY			