



	Pitch dimension			Nominal dimension						
variable range	over ~ 6	over ~ 10	over ~ 24	over 0	over 30	over 60	over 100	over 150	over 150	
Tolerance	$\pm 0.1$	$\pm 0.15$	$\pm 0.25$	$\pm 0.20$	$\pm 0.3$	$\pm 0.5$	$\pm 0.7$	$\pm 1$	$\pm 1$	0.05/1



2		插针	H65	N	镀镍锡	
1		插座	PA66 UL94V-0	1	绿色	
序号	代号	名称	材质	数量	电镀/颜色	备注

#### 技术参数:

过压类别/Overvoltage Category	/污染等级/Pollution Degree	III/3	III/2	II/2
额定电压/电流/Rated Voltage(V)/Current(A)	/	250V/8A		
耐电压/Withstanding voltage(V/1Min)		2000		
额定冲击电压(Rated impulse voltage) [KV]		4.0		
绝缘电阻/Insulation resistance		常态≥500MΩ		
接触电阻/Contact resistance		<20mΩ		
单PIN插针保持力/Binding force(N)		>25N		
耐焊接热/Resistance to soldering temperature		260°C±5°C		
间距/Pitch(mm)/线数范围/Poles		5.08/N=02~12P		
使用温度范围/Operating temperature(°C)		-40~+105		
相对湿度/Relative humidity		湿度≤95%(温度+40°C)		
符合RoHS环保要求/Conform to RoHS		Yes		



NAME: 插拔式接线端子（插座）

NAME: HX-HE440-5.08-2P

设计	黄彬	工乙		视角		图幅:A4
审核	张传	标准化		比例	3:1	单位:mm
批准	罗小春	日期	2023.7.17	页面	1/1	版本/次:A/0