








REV.	ECN NO OR DESCRIPTION	REVISED	DATE



PIN NO.	SIGNAL NAME
P1	GND
P2	A+
P3	A-
P4	GND
P5	B-
P6	B+
P7	GND



SPECIFICATION:
MATERIAL:
HOUSING: LCP LG431-9731L 30% G/F UL 94V-0
COLOR: BLACK
CONTACT: PHOSPHOR BRONZE C2680 H,T=0.25mm
PEG: BRASS C2680R H,T=0.30mm
SHELL: spcc,T=0.30mm
FINISH:
CONTACT: 1u" GOLD/TIN PLATING ON CONTACT AREA
100u" MIN. TIN-LEAD PLATING ON SOLDERTAILS
50u" MIN. NICKEL UNDERPLATING OVERALL
PEG: 100u" MIN. TIN-LEAD PLATING ON SOLDERTAILS
50u" MIN. NICKEL UNDERPLATING OVERALL
SHELL: 100u" MIN. TIN-LEAD PLATING ON SOLDERTAILS
50u" MIN. NICKEL UNDERPLATING OVERALL

UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS:	ANGLES:	TITLE	SATA 7P公座双柱B型端子A型鱼叉H=2.45带铁壳直脚		
X :±0.25	X :±2°	DWN	xiong	PART NO. SATA-001-M07S2BY-A	
X.X :±0.20	X.X :±1°	CHKD	lee	SCALE:1:1	UNIT: mm
X.XX :±0.10		APVD	wang	SIZE: A4	SHEET:10F 1
CUSTOMER COPY					