


SOT-23


1. BASE

2. EMITTER

3. COLLECTOR

Marking: 1P
特征 Features

- 最大功率耗散 300mW; Power Dissipation of 300mW
- 高稳定性和可靠性。High Stability and High Reliability

机械数据 Mechanical Data

- 封装: SOT-23 封装 SOT-23 Small Outline Plastic Package
- 环氧树脂 UL 易燃等级 Epoxy UL: 94V-0
- 安装位置: 任意 Mounting Position: Any

极限值和温度特性(TA = 25°C 除非另有规定)

Maximum Ratings & Thermal Characteristics (Ratings at 25°C ambient temperature unless otherwise specified.)

Parameters	Symbol	Value	Unit
Collector-Base Voltage	V _{CBO}	75	V
Collector-Emitter Voltage	V _{CEO}	40	V
Emitter -Base Voltage	V _{EBO}	6	V
Collector Current-Continuous	I _C	600	mA
Collector Current-Pulsed	I _{CM}	900	mA
Collector Power Dissipation	P _C	300	mW
Junction Temperature	T _j	150	°C
Storage Temperature	T _{stg}	-55-+150	°C
Thermal resistance From junction to ambient	R _{θJA}	417	°C/W

电特性 (TA = 25°C 除非另有规定)







Electrical Characteristics (Ratings at 25°C ambient temperature unless otherwise specified.)




参数 Parameter	符号 Symbols	测试条件 Test Condition	界限 Limits		单位 Unit
			Min	Max	
Collector-base breakdown voltage	V(BR)CBO	IC=10uA, IE=0	75		V
Collector-emitter breakdown voltage	V(BR)CEO	IC=10mA, IB=0	40		V
Emitter-base breakdown voltage	V(BR)EBO	IE=10uA, IC=0	6		V
Collector cut-off current	ICEX	VCE=30V, VEB(off)=3V		10	nA
Collector cut-off current	ICBO	VCB=60V, IE=0		10	nA
Emitter cut-off current	IEBO	VEB=3V, IC=0		100	nA
DC current gain	hFE(1)*	VCE=10V, IC=150mA	100	300	
	hFE(2)*	VCE=10V, IC=0.1mA	40		
	hFE(3)*	VCE=10V, IC=500mA	42		
Collector-emitter saturation voltage	VCE(sat)1*	IC=500mA, IB=50mA		1.00	V
Collector-emitter saturation voltage	VCE(sat)2*	IC=150mA, IB=15mA		0.30	V
Base -emitter saturation voltage	VBE(sat)1*	IC=500mA, IB=50mA		2.00	V
Base -emitter saturation voltage	VBE(sat)2*	IC=150mA, IB=15mA		1.20	V
Transition frequency	f _T	VCE=20V, IC=20mA, f=100MHz	300		MHz
Delay time	t _d	VCC=30V, VBE(off)=-0.5V, IC=150mA, IB1=15mA		10	nS
Rise time	t _r			25	nS
Storage time	t _s			225	nS
Fall time	t _f	VCC=30V, IC=150mA, IB1=IB2=15mA		60	nS

*Pulse test: pulse width ≤ 300us, duty cycle ≤ 2.0%.

CLASSIFICATION OF hFE(1)

HFE	100-300	
RANK	L	H
RANGE	100-200	200-300

Typical characteristics




SOT-23 PACKAGE OUTLINE Plastic surface mounted package


SYMBOL	DIMENSIONS	
	MIN.	MAX.
A	0.900	1.150
A1	0.000	0.100
A2	0.900	1.050
b	0.300	0.500
c	0.080	0.150
D	2.800	3.000
E	1.200	1.400
E1	2.250	2.550
e	0.950TYP	
e1	1.800	2.000
L	0.550REF	
L1	0.300	0.500
θ	0°	8°

Unit: mm

焊盘设计参考Precautions: PCB Design

Recommended land dimensions for SOT-23 diode. Electrode patterns for PCBs


Note:

1. Controlling dimension: In millimeters.
2. General tolerance: $\pm 0.05\text{mm}$.
3. The pad layout is for reference purposes only.

NOTICE

The information presented in this document is for reference only. Involving product optimization and productivity improvement, ChipNobo reserves the right to adjust product indicators and upgrade some technical parameters. ChipNobo is entitled to be exempted from liability for any delay or non-delivery of the information disclosure process that occurs.

本文件中提供的信息仅供参考。涉及产品优化和生产效率改善，ChipNobo 有权调整产品指标和部分技术参数的升级，所出现信息披露过程存在延后或者不能送达的情形，ChipNobo 有获免责权。

The product listed herein is designed to be used with residential and commercial equipment, and do not support sensitive items and specialized equipment in areas where sanctions do exist. ChipNobo Co., Ltd or anyone on its behalf, assumes no responsibility or liability for any damages resulting from improper use.

此处列出的产品旨在民用和商业设备上使用，不支持确有限制地区的敏感项目和特殊设备，ChipNobo 有限公司或其代表，对因不当使用而造成的任何损害不承担任何责任。

For additional information, please visit our website <http://www.chipnobo.com>, or consult your nearest Chipnobo sales office for further assistance.

欲了解更多信息，请访问我们的网站 <http://www.chipnobo.com>，或咨询离您最近的 Chipnobo 销售办事处以获得进一步帮助。