





SECTION C-C

■ Specification :


- 1. Rating:
Voltage :12V AC/DC max., 2V DC min.
Current: 10mA AC/DC max., 10μA DC min.
- 2. Contact Resistance : 100mΩ Max
- 3. Insulation Resistance : 100MΩ at 500V
- 4. Withstand Voltage : AC100V (50-60Hz)
for 1 minute
- 5. Mating Force : 3.0kgf max
- 6. Operating Life : 5000 Cycles



SECTION A-A



RECOMMENDED PCB LAYOUT
TOLERANCE:±0.05mm



SECTION B-B

—		new		2015/5/3	A	瀚源	
ECN BO.		DESCRIPTION.		DATE.	REV.		
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1	
ITEM	contact	1	Copper Alloy	Tin Plating		UNLESS OTHERWISE SPECIFIED, TOLERANCE: X. xx ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAR ±3°	X. xx ±0.25
	Base	1	Nylon	Purpie			X.x ±0.20
							X.xx ±0.15
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK	FILE.NO.
Mikey		Tom		Jerry		HanElectricity Co.,LTD	
PART NAME		CPG151101S11-16		3RD ANGLE PROJ			
MODEL NAME		CPG151101S11-16					