







装吸取盖示意图

Technical drawing of a vacuum suction cover assembly, showing two views with dimensions:

- Front View (Left):** Shows a cylindrical component with a diameter of 4.50 ± 0.15 mm. The central shaft has a diameter of 1.08 ± 0.15 mm.
- Side View (Right):** Shows the component's profile with a total width of 8.50 ± 0.15 mm and a total height of 7.58 ± 0.15 mm. The central shaft diameter is 1.08 ± 0.15 mm.



3.1 工作温度: $-30^{\circ}\text{C} \sim +85^{\circ}\text{C}$

<i>PIN NUMBER</i>	<i>SIGNAL NAME</i>	<i>PIN NUMBER</i>	<i>SIGNAL NAME</i>
<i>A1</i>	<i>GND</i>	<i>B12</i>	<i>GND</i>
<i>A4</i>	<i>VBUS</i>	<i>B9</i>	<i>VBUS</i>
<i>A5</i>	<i>CC1</i>	<i>B8</i>	<i>SBU2</i>
<i>A6</i>	<i>Dp1</i>	<i>B7</i>	<i>Dn2</i>
<i>A7</i>	<i>Dn1</i>	<i>B6</i>	<i>Dp2</i>
<i>A8</i>	<i>SBU1</i>	<i>B5</i>	<i>CC2</i>
<i>A9</i>	<i>VBUS</i>	<i>B4</i>	<i>VBUS</i>
<i>A12</i>	<i>GND</i>	<i>B1</i>	<i>GND</i>

_____		new			2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.			DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER				SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	161N-4BQC65		UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X. ±0.25		
			MODEL NAME	161N-4BQC65				X.x ±0.20 X.xx ±0.15 ANGULAR ±3°		
			3RD ANGLE PROJ	HanElectricity Co.,LTD					FILE.NO.	

瀚源