



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

NOTES:

SPECIFICATION:



1. CURRENT RATING: 5A MAX
2. VOLTAGE: 100 VAC
3. TEMPERATURE RANGE: -40 °C ~ 85 °C
4. CONTACT RESISTANCE: 40 MILLIONHM MAX
5. INSULATION RESISTANCE: 100 MEGOHMS MIN.
6. INSERTION FORCE : 5N~20N
7. UNMATING FORCE: 8N~20N
8. DURABILITY: 10,000 CYCLES




D



E



F



G

USB TYPE-C PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A2	SSR4p1	B11	SSR4p1
A3	SSR4n1	B10	SSR4n1
A4	Vbus	B9	Vbus
A5	CC1	B8	SBUI
A6	DP1	B7	DP2
A7	DP2	B6	DP1
A8	SBUI	B5	CC2
A9	Vbus	B4	Vbus
A10	SSR4n2	B3	SSR4n2
A11	Vbus	B2	SSR4p2
A12	GND	B1	GND

6

5

4

3

2

1

FUYOU® - 广东富盈兴业精密科技实业有限公司
Guangdong FUYOU Precision Electronic Technology Co.,Ltd.

A

B

C

D

E

F

G