





Schottky Diodes
Reverse Voltage-45to200v
Forward current-10A

Features


Schottky chip
Low forward voltage drop
Ideal for surface mounted applications
Low power loss, high efficiency
Plastic Case Material has UL Flammability

Mechanical Data


Package: TO-220AB, TO-220F, TO-263, TO-252
Terminals: Tin Plated leads, solderable per
Mil-STD-750 Method 2026
Polarity: As marked
Molding compound meets UL 94 V-0 flammability rating,
ROHS-compliant




TO-220AB



TO-220F



TO-263



TO-252

Maximum Ratings (Ta=25°C Unless otherwise)

Type Number	SYMBOL	MBR 10L45	MBR 10L60	MBR 10L100	MBR 10L150	MBR 10L200	Umit
Maximum Recurrent Peak Reverse Voltage	V _{RRM}	45	60	100	150	200	V
Maximum RMS Voltage	V _{RMS}	31.5	42	70	105	140	V
Maximum DC Blocking Voltage	V _{DC}	45	60	100	150	200	V
Maximum Average Forward Rectified Current at TL = 100 °C	IO(AV)	10.0					A
Peak Forward Surge Current 8.3ms Single half-sine-wave superimposed on rated load(JEDEC Method) on rated	IFSM	100.0					A
Forward Surge Current (Non-repetitive) @1ms, square wave, 1 cycle, Tj=25°C		200.0					A
Current squared time @1ms≤t8.3≤ms Tj=25°C , Rating of per diode	I²t	41.5					A²S
Maximum Forward Voltage at 5.0A DC	V _{FM}	0.55	0.65	0.75	0.85	0.9	V
Maximum Reverse Current TA = 25°C	IR	0.2		0.1			mA
at Rated DC Blocking Voltage TA = 100°C		50		20			mA
Typical Junction Capacitance	CJ	400		300			pF
Typical Thermal Resistance TO-220AB,TO-263	R _{QJC}	2.0					°C/W
TO-220F		4.0					
TO-252		5.0					
Operating Junction Temperature Range	T _J	—55to+150					°C
Storage Temperature Range	T _{STG}	—55to+150					°C



FIG. 1 MAXIMUM AVERAGE FORWARD CURRENT DERATING




FIG. 2 TYPICAL FORWARD CHARACTERISTICS




FIG. 3 MAXIMUM NON-REPEITIVE SURGE CURRENT






FIG. 4 TYPICAL REVERSE CHARACTERISTICS(per element)





MARKING INFORMATION

TO-220AB/CT




 = Polar line

 = Logo

***** = Date Code Marking

MBR***** = Marking Code

TO-220F/FCT



 = Polar line


 = Logo

***** = Date Code Marking

MBR***** = Marking Code

TO-263/CS

TO-252/DS



 = Polar line


 = Logo


***** = Date Code Marking


MBR***** = Marking Code



Package Outline Dimensions millimeters

T0-220AB/CT						
	DIM	INCHES		MM		NOTE
		min	max	min	max	
	A	—	0.41	—	10.30	
	B	0.33	0.34	8.30	8.70	
	C	0.18	0.19	4.50	4.90	
	D	0.57	0.60	14.60	15.20	
	E	0.53	0.56	13.50	14.10	
	a	0.10	0.10	2.45	2.65	
	b	—	0.16	—	4.10	
	c	0.03	0.04	0.72	0.92	
	d	0.01	0.02	0.30	0.50	
	e	—	0.15	—	3.80	Ø
	f	0.05	0.06	1.20	1.40	

T0-220F/FCT						
	DIM	INCHES		MM		NOTE
		min	max	min	max	
	A	—	0.41	—	10.30	
	B	0.61	0.64	15.60	16.20	
	C	0.18	0.19	4.50	4.90	
	D	0.26	0.28	6.60	7.00	
	E	0.50	0.53	12.80	13.40	
	a	0.10	0.10	2.45	2.65	
	b	—	0.16	—	4.10	
	c	0.03	0.04	0.72	0.92	
	d	0.02	0.02	0.40	0.60	
	e	—	0.15	—	3.80	Ø
	f	0.09	0.11	2.40	2.80	

T0-263/CS						
	DIM	INCHES		MM		NOTE
		min	max	min	max	
	A	—	0.41	—	10.30	
	B	0.33	0.34	8.30	8.70	
	C	0.18	0.19	4.50	4.90	
	D	0.38	0.39	9.60	10.00	
	E	0.21	0.22	5.30	5.70	
	a	0.10	0.10	2.45	2.65	
	b	—	0.16	—	4.10	
	c	0.03	0.04	0.72	0.92	
	d	0.01	0.02	0.30	0.50	
	e	0.05	0.06	1.20	1.40	



T0-252DS					
DIM	INCHES		MM		NOTE
	min	max	min	max	
A	0.25	0.27	6.3	6.9	
B	0.23	0.25	5.8	6.4	
C	0.08	0.10	2.1	2.5	
D	0.35	0.43	9.0	11.0	
E	0.21	0.22	5.3	5.5	
a	0.08	0.10	2.1	2.5	
b	0.06	0.06	1.4	1.6	
c	0.02	0.03	0.6	0.8	
d	0.02	0.02	0.4	0.6	
e	0.02	0.02	0.4	0.6	

Important Statements and disclaimers.

Do not copy or modify file information without permission.

Xumao Micro reserves the right to modify this document and its products.

Specifications are available without prior notice. Customer shall obtain and confirm the latest product information and specifications prior to final design, purchase or use.

Xumao Micro does not assume any implied warranties, including warranties of fitness for special purposes, non-infringement and merchantability.

The products shown here are not designed and licensed for demanding equipment at a level of reliability or for human life and any life-saving related applications or life-sustaining, such as medical devices, transportation equipment, aerospace machinery, and so on. Customers who use or sell these products for such applications do so at their own risk.

As Xumao Micro uses batch number as tracking benchmark, please provide batch number for tracking in case of exception.