


KL101X

PHOTO TRANSISTOR

LSOP4 晶体管光耦 (消费级)



* 本文档中包含的信息反映了具有代表性的使用场景，仅供技术参考。

The information contained in this document reflects representative usage scenarios and is intended for technical reference only.

* 本文档中提到的产品型号和规格如有更改或改进，恕不另行通知。在生产使用之前，客户应参考产品规格书的最新数据表。

Product models and specifications mentioned in this document are subject to change or improvement without notice. Customers should refer to the latest data sheets in the product specifications prior to production use.

* 在使用本文档中引用的产品时，请确保产品在数据手册中规定的环境和电气限制范围内运行。如果客户使用超过指定的限制，晶台将不会对任何后续问题负责。

When using the products referenced in this document, ensure that the products are operated within the environmental and electrical limits specified in the data sheet. If the customer uses the product beyond the specified limits, Kinglight will not be responsible for any subsequent problems.

* 本文档中的信息适用于电子元器件应用中的典型用法。如有任何特殊用途，请向晶台咨询，以获得进一步的帮助。

The information in this document applies to typical use in electronic component applications. For special applications, please contact Kinglight for further assistance.

* 未经晶台允许，不得复制或转载本文件的内容和信息。对于最新的信息，请参考官方网站 www.kinglight-semi.com。

The contents and information in this document may not be copied or reproduced without the permission of Kinglight. For the latest information, please visit the official website www.kinglight-semi.com.

1. 产品特点 Product features

- 电流转换率(Current transfer ratio)
CTR: 50~600% at $I_F = 5\text{mA}$, $V_{ce} = 5\text{V}$
CTR: 63~320% at $I_F = 10\text{mA}$, $V_{ce} = 5\text{V}$
- 输入与输出高隔离电压($V_{iso} = 5000\text{ V rms}$)
High isolation voltage between inputs and output ($V_{iso} = 5000\text{ V rms}$)
- 8mm长爬电距离 8mm long creepage distance
- 紧凑型4引脚LSOP外形尺寸为2.1mm Compact 4 Pin LSOP with a 2.1 mm profile
- 不含卤素(溴<900ppm, 氯<900ppm, 溴+氯<1500ppm)
Halogen free (Br < 900ppm, Cl < 900ppm, Br+Cl < 1500ppm)
- 符合欧盟REACH法规 Compliance with EU REACH
- 无Pb且符合ROHS标准 Pb free and compliant with RoHS standards
- 安全审批 Safety approval
CQC认证已批准(编号:CQC23001407998) CQC approved (No.CQC23001407998)
UL认证已批准 (编号:UL-CA-2340753-0) UL approved (No.UL-CA-2340753-0)
VDE认证已批准(编号:40059021) VDE approved (NO.40059021)


2. 产品描述 Product Description

- KL101X系列由一个红外发射二极管,光耦合到一个光电晶体管构成光电耦合器
KL101X series contains an infrared emitting diode, optically coupled to a phototransistor detector.
- 它们封装在4引脚LSOP封装中 They are packaged in a 4-pin LSOP package

3. 产品应用 Product Applications

- 家用电器, 如电风扇加热器等 Home appliances, such as fan heaters, etc.
- 可编程控制器 Programmable controllers
- 电信设备 Telecommunication equipments
- 不同电位和阻抗电路间的信号传输
Signal transmission between circuits of different potentials and impedances
- 测量仪器等 measuring instruments, etc

4. 功能图 Functional Diagram



引脚配置 Pin Configuration

1. 阳极Anode
2. 阴极Cathode
3. 发射极Emitter
4. 集电极Collector

5. 光电特性 Electrical-Optical characteristics

• 最大限度额定值(温度=25°C) Absolute Maximum Ratings(Ta=25°C)

参数 Parameter		符号 Symbol	额定值 Rated Value	单位 Unit
输入 Input	正向电流 Forward current	I_F	60	mA
	峰值正向电流(1us脉冲) Peak forward current (1us pulse)	I_{FP}	1.5	A
	反向电压 Reverse voltage	V_R	6	V
	输入功耗 Input Power dissipation	P_D	100	mW
输出 Output	集电极电流 Collector current	I_C	50	mA
	集电极与发射极间电压 Collector and emitter Voltage	V_{CEO}	80	V
	发射极与集电极间电压 Emitter and Collector Voltage	V_{ECO}	7	V
	输出功耗 Output Power dissipation	P_C	150	mW
总消耗功率 Total Consume Power		P_{TOT}	250	mW
隔离电压 (1*) Isolation Voltage		V_{iso}	5000	Vrms
工作温度 Operating temperature		T_{OPR}	-55 to +110	°C
储存温度 Storage temperature		T_{STG}	-55 to +125	°C
焊接温度 (2*) Soldering temperature		T_{SOL}	260	°C

附注(Notes):

1* 交流电源1分钟内, 相对湿度40~60%环境下, 隔离电压测试方法, 引脚1&2短接在一起, 引脚3&4短接在一起
AC for 1 minute, 40~60%RH in this test, Pin 1,2 are shorted together, and 3,4 are shorted together

2* 焊接时间为10秒 Soldering time is 10 seconds

6. 电气特性(Ta=25°C,除非另有规定)

Electrical Characteristics(Ta=25°C unless specified otherwise)

参数 Parameter		符号 Symbol	最小值 Min.	规格值 Typ.	最大值 Max.	单位 Unit	条件 Condition
输入 In put	正向电压 Forward voltage	V_F	-	1.45	1.5	V	$I_F=50\text{mA}$
	反向电流 Reverse current	I_R	-	-	10	μA	$V_R=6\text{V}$
	输入电容 Input capacitance	C_{in}	-	50	-	pF	$V=0, f=1\text{kHz}$
输出 Out put	集电极与发射极间暗电流 Collector-Emitter dark current	I_{CEO}	-	-	100	nA	$V_{CE}=20\text{V}$ $I_F=0\text{mA}$
	集电极与发射极间击穿电压 Collector-Emitter breakdown voltage	V_{CEO}	80	-	-	V	$I_C=0.1\text{mA}$ $I_F=0\text{mA}$
	发射极与集电极间击穿电压 Emitter-Collector breakdown voltage	V_{ECO}	7	-	-	V	$I_E=0.1\text{mA}$ $I_F=0\text{mA}$
传输特性 Transfer Characteristics	集电极与发射极间饱和电压 Collector-Emitter saturation voltage	$V_{CE(sat)}$	-	-	0.3	V	$I_F=10\text{mA}$ $I_C=1\text{mA}$
	隔离电阻 Isolation resistance	R_{ISO}	5×10^{10}	-	-	Ω	$V_{IO}=500\text{Vdc}$ 40~60% R.H.
	浮动电容 Floating capacitance	C_f	-	-	1.0	pF	$V_{IO}=0, f=1\text{MHz}$
	上升时间 Rise time	t_r	-	-	18	μs	$V_{CE}=5\text{V},$ $I_C=5\text{mA},$ $R_L=100\Omega$
	下降时间 Fall time	t_f	-	-	18	μs	
	开启时间 Turn on time	T_{on}	-	4	-	μs	$V_{CE}=5\text{V},$ $I_C=5\text{mA},$ $R_L=100\Omega$
	关闭时间 Turn off time	T_{off}	-	3	-	μs	

• 温度Ta=25℃下规格值 Typical values at Ta = 25℃

Transfer Characteristics level table (Ta=25℃ unless specified otherwise)

参数 Parameter		符号 Symbol	最小值 Min.	规格值 Typ.	最大值 Max.	单位 Unit	条件 Condition
电流传输比 Current Transferratio	KL1010	CTR	50	-	600	%	I _F =5mA V _{CE} =5V
	KL1017		80	-	160		
	KL1018		130	-	260		
	KL1019		200	-	400		
	KL1012	CTR	63	-	125	%	I _F =10mA V _{CE} =5V
	KL1013		100	-	200		
	KL1014		160	-	320		
	KL1012		22	-	-		I _F =1mA V _{CE} =5V
	KL1013		34	-	-		
	KL1014		56	-	-		

7. 特性曲线 Characteristic Curves

图1. 正向电流与正向电压的关系
Figure1. Forward Current VS Forward Voltage




图2. 集电极暗电流与环境温度的关系
Collector Dark Current vs Ambient Temperature




图3. 集电极电流与正向电流的关系
Figure1. Forward Current VS Forward Voltage




图4. 电流传输比与正向电流
Current Transfer Ratio vs Forward Current




图5. 集电极电流与集电极-发射极电压
Collector Current vs Collector-Emmitter Voltage




图6. 集电极电流与集电极-发射极电压
Collector Current vs Collector-Emmitter Voltage




图7. 电流传输比与环境温度关系









图8. 电流传输比与环境温度关系

图9. 开启时间/关闭时间 vs 集电极电流
Ton/Toff Time vs Collector Current图10. 开启/关闭时间与正向电流的关系
Ton/Toff Time vs Forward Current图11. 开关时间测试电路与波形
Switching Time Test Circuit vs Waveforms

8. 订单信息 Order Information

• 材料编号 Part Number

KL101X (Y)-V

(料号PN:KL101X-Y-V-AW)

附注(Notes):

- KL101 = 材料编号 Part No.
- X = 表示CTR等级(0、2、3、4、7、8或9)
CTR Rank (0, 2, 3, 4, 7, 8 or 9)
- Y = 载带和卷轴包装方式(TA、TB)
Tape and reel option (TA, TB)
- V = 表示VDE标识(客户指定镭射字符才加"V")
VDE (Only add "V" to laser characters specified by the customer)
- AW = 表示消费级 Consumer-grade


选项 Option	描述 Description	包装数量 Packing quantity
TA	TA载带和卷轴选项 TA Tape & reel option	每卷3500pcs 3500 units per tube
TB	TB载带和卷轴选项 TB Tape & reel option	每卷3500pcs 3500 units per tube
TA-V	TA载带和卷轴选项 +VDE TA Tape & reel option + VDE	每卷3500pcs 3500 units per tube
TB-V	TB载带和卷轴选项 + VDE TB Tape & reel option + VDE	每卷3500pcs 3500 units per tube
/	内盒装: 每盒3盘 Inner box packaging: 3reels/box	每盒10500pcs 10500pcs per box
/	每箱装:10个内盒 Pack per Carton:10 inner boxes	每箱105000pcs 105000pccs per Carton

选项 Option	描述 Description	包装数量(旧版) Packing quantity
TA	TA载带和卷轴选项 TA Tape & reel option	每卷3000pcs 3000 units per tube
TB	TB载带和卷轴选项 TB Tape & reel option	每卷3000pcs 3000 units per tube
TA-V	TA载带和卷轴选项 +VDE TA Tape & reel option + VDE	每卷3000pcs 3000 units per reel
TB-V	TB载带和卷轴选项 + VDE TB Tape & reel option + VDE	每卷3000pcs 3000 units per reel
/	内盒装: 每盒3盘 Inner box packaging: 3reels/box	每盒9000pcs 9000pcs per box
/	每箱装:10个内盒 Pack per Carton:10 inner boxes	每箱90000pcs 90000pccs per Carton


9. 封装尺寸(单位:毫米) Package Drawing(Unit:mm)

- 包装尺寸 (尺寸单位为mm)

Package Dimension (Dimensions in mm)




- 表面贴片类型PIN脚焊盘布局 Surface patch type PIN foot pad layout



附注(Notes):

- 推荐焊盘尺寸仅供参考 Suggested pad dimension is just for reference only
- 请根据个人需求修改焊盘尺寸 Please modify the pad dimension based on individual need

10. 设备标记 Device marking




附注(Notes):

- KL = 表示晶台光电有限公司 Denotes KingLight
- 101X = 表示材料部件号 Denotes Device Part Number
X 表示CTR等级(0、2、3、4、7、8 或 9) CTR Rank (0, 2, 3, 4, 7, 8 or 9)
- Y = 表示1位年份代码 Denotes 1 digit Year code
- WW = 表示2位周别代码 Denotes 2 digit Week code
- V = 表示VDE标识(客户指定镭射字符才加"V")
VDE (Only add "V" to laser characters specified by the customer)


11. 料带和卷轴包装规格 Tape & Reel Packing Specifications

• 选择TA Option TA




卷轴进给方向 Direction of feed from reel

• 选择TB Option TB



卷轴进给方向 Direction of feed from reel

料带尺寸Material belt size




尺寸编号 Dimension No.	A0	B0	D0	D1	E	F
尺寸(mm) Dimension(mm)	3.9±0.1	10.82±0.1	1.5±0.1	1.5±0.1	1.75±0.1	7.5±0.1
尺寸编号 Dimension No.	P0	P1	P2	T	W	K0
尺寸(mm) Dimension(mm)	4.0±0.1	8.0±0.1	2.0±0.1	0.4±0.05	16.0±0.3	2.25±0.1

12. 焊接温度曲线 Temperature Profile Of Soldering

• 回流焊温度曲线 Reflow soldering

建议在下面所示的温度和时间分布条件下, 进行一次回流焊作业, 不得超过三次

One time soldering reflow is recommended within the condition of temperature and time profile shown below. Do not solder more than three times.



项目 Item	符号 Symbol	最小值 Min.	最大值 Max.	单位 Unit
预热温度 Preheat Temperature	T_s	150	200	°C
预热时间 Preheat Time	t_s	60	120	s
升温速率 Ramp-Up Rate (T_L to T_p)	-	-	3	°C/s
液相线温度 Liquidus Temperature	T_L	217		°C
高于液相线温度(T_L)的时间 Time above Liquidus Temperature T_L	t_L	60	100	s
峰值温度 Peak Temperature	T_p	-	260	°C
T_c 在(T_p-5)和 T_p 之间的时间 Time During Which T_c Is Between (T_p-5) and T_p	t_p	-	30	s
降温速率 Ramp-down Rate(T_p to T_L)	-	-	6	°C/s