




RoHS+REACH




NO.	COMPONENTS	MATERIALS	SPECIFICATION:FINISH/COLOR	QTY.
1	HOUSING	PA9T/PA10T UL94V-0	BLACK	1
2	TER	BRASS	SURFACE PLATING: TIN PLATING	N



NOTE(UNLESS OTHERWISE SPECIFIED):

1. ALL MATERIAL MUST BE COMPLY WITH ROHS+REACH.
2. PRODUCT PERFORMANCE:
 - 2.1 RATED VOLTAGE(MAX.):250V AC/DC
 - 2.2. RATED CURRENT(MAX.):5.0A AC/DC
 - 2.3 DIELECTRIC STRENGTH:1500V AC FOR 1 MINUTE BETWEEN ADJACENT TERMINAL, NO BREAKDOWN
 - 2.4 INSULATION RESISTANCE:1000 MΩ MIN. 500VDC FOR 1 MINUTE BETWEEN ADJACENT TERMINAL
 - 2.5 CONTACT RESISTANCE:20 mΩ MAX.
 - 2.6 OPERATING TEMPERATURE:-25° C to +85° C
- 3.PART NO. LEGEND: 1WF09-148XXX-00XXX

WATER CODE
004:04PIN



RECOMMENDED PCB LAYOUT
(TOLERANCE:±0.10)

WATER CODE	CONTACTS	DIMENSIONS	
		A	B
00001	2	3.00	9.65
	3	6.00	12.65
	4	9.00	15.65
	5	12.00	18.65
	6	15.00	21.65
	7	18.00	24.65
	8	21.00	27.65
	9	24.00	30.65
	10	27.00	33.65
	11	30.00	36.65
	12	33.00	39.65


5.0			
4.0			
3.0			
2.0			
1.0	21.08.30	NEW	TGC
REV.	DATE	DESCRIPTION	DRAWING

DRAWING:	TGC	
CHECKED:		
APPROVAL:		
UNIT:	MM	PROJECTION:
SCALE:	1/1	
SHEET:	1/2	



CHIN-BAN
Electronics Technology

DESCRIPTION:	3.0 Pitch Wafer 180° DIP K Type Single Row		
PART NO:	1WF09-148XXX-00XXX		REV: 1.0
DRAWING NO:	UK0483		SIZE: A4



RoHS+REACH

2PIN

9PIN

10PIN

3PIN

8PIN

11PIN

4PIN

7PIN

12PIN

5PIN

6PIN

5.0			
4.0			
3.0			
2.0			
1.0	21.08.30	NEW	TGC
REV.	DATE	DESCRIPTION	DRAWING

DRAWING: TGC	GENERAL TOLERANCE	
	.X:=±0.30	.X':=±2°
CHECKED:	.XX:=±0.20	.XX':=±1°
	.XXX:=±0.10	.XXX':=±0.5°
APPROVAL:	UNIT: MM	PROJECTION:
	SCALE: 1/1	
	SHEET: 2/2	



CHIN-BAN
Electronics Technology

DESCRIPTION: 3.0 Pitch Wafer 180° DIP K Type Single Row	
PART NO: 1WF09-148XXX-00XXX	REV: 1.0
DRAWING NO: UK0483	SIZE: A4