







RoHS

NO.	COMPONENTS	MATERIALS	SPECIFICATION:FINISH/COLOR	QTY.
1	HOUSING	NYLON.UL94V-0	WHITE/BLACK	1



- 1.NOTES:
1.1 ALL MATERIAL MUST BE COMPLY WITH Rohs.
1.2 MATERIAL: NYLON66
2.PRODUCT PERFORMANCE:
2.1 RATED VOLTAGE(MAX.):50V AC/DC
2.2 RATED CURRENT(MAX.):1.0A AC/DC
2.3 DIELECTRIC STRENGTH:500V AC FOR 1 MINUTE BETWEEN ADJACENT TERMINAL, NO BREAKDOWN
2.4 INSULATION RESISTANCE:500 MEGOHMS MIN. 500V DC FOR 1 MINUTE BETWEEN ADJACENT TERMINAL
2.5 CONTACT RESISTANCE:20 MILLIOHM MAX.
2.6 OPERATING TEMPERATURE:-25°C to +85C
3.PART NO. LEGEND:

30001-D1X0XX-A4001



PIN	DIM A	DIM B	DIM C
2	1.50	3.40	4.50
3	3.00	4.90	6.00
4	4.50	6.40	7.50
5	6.00	7.90	9.00
6	7.50	9.40	10.50
7	9.00	10.90	12.00
8	10.50	12.40	13.50
9	12.00	13.90	15.00
10	13.50	15.40	16.50
11	15.00	16.90	18.00
12	16.50	18.40	19.50
13	18.00	19.90	21.00
14	19.50	21.40	22.50
15	21.00	22.90	24.00
16	22.50	24.40	25.50

7.0	22.03.08	新增黑色款规格	ShunMingWen	DRAWING: ShunMingWen	GENERAL TOLERANCE .X:=±0.30 .X*:=±2° .XX:=±0.20 .XX*:=±1° .XXX:=±0.10 .XXX*:=±0.5°		CHIN-BAN Electronic Technology		
6.0	22.01.04	新增12PIN及调整品号	ShunMingWen		CHECKED:	UNIT: MM	PROJECTION:	DESCRIPTION: PH1.5mm WAFER WIRE-HOUSING	
5.0	21.11.10	新增13/14PIN规格	ShunMingWen	APPROVAL:		SCALE: 1/1		PART NO: 30001-D1X0XX-A4001	
4.0	21.04.16	新增9PIN规格	ShunMingWen		SHEET: 1/1	DRAWING NO: UK0418		SIZE: A4	
3.0	21.03.23	新增耐灼热丝款规格	ShunMingWen						
NO.	DATE	DESCRIPTION	DRAWING						