





G010

SECTION A-A
SCALE 1:1


PART NO. LEGEND:

F4TXXU-A1X3-AX

R:TAPE & REEL
C:TUBE
T:CONTACT-TIN PLATING
G:CONTACT-GOLD PLATING
1:PULL:LCP BLACK
A:HOUSING:LCP WHITE
U:SMT
XX:NO. OF POSITIONS
T:UPPER CONTACT



RECOMMENDED P.C.B PATTERN LAYOUT



RECOMMENDED FPC/FFC DIMENSION

Note:

1. Material:

1.1 Housing: thermoplastic high temp.UL94V-0;
Color: natural.1.2 Latch: thermoplastic high temp.UL94V-0;
Color: black.

1.3 Terminal: copper alloy.

1.4 Fitting Nail: copper alloy.

2. Finsh:

2.1 Terminal:

Underplating: Au/matt Tin overall.

2.2 Fitting Nail:

Underplating: matt Tin overall.

▲ Non-tooled parts

NO.OF POSITIONS DIM LIST:

29P	28.00	30.10	34.00	35.10	5.75	7.00
28P	27.00	29.10	33.00	34.10		
27P	26.00	28.10	32.00	33.10		
26P	25.00	27.10	31.00	32.10		
25P	24.00	26.10	30.00	31.10		
24P	23.00	25.10	29.00	30.10		
23P	22.00	24.10	28.00	29.10		
22P	21.00	23.10	27.00	28.10		
21P	20.00	22.10	26.00	27.10		
20P	19.00	21.10	25.00	26.10		
19P	18.00	20.10	24.00	25.10	5.20	6.45
18P	17.00	19.10	23.00	24.10		
17P	16.00	18.10	22.00	23.10		
16P	15.00	17.10	21.00	22.10		
15P	14.00	16.10	20.00	21.10		
14P	13.00	15.10	19.00	20.10		
13P	12.00	14.10	18.00	19.10		
12P	11.00	13.10	17.00	18.10		
11P	10.00	12.10	16.00	17.10		
10P	9.00	11.10	15.00	16.10		
9P	8.00	10.10	14.00	15.10	5.20	6.45
8P	7.00	9.10	13.00	14.10		
7P	6.00	8.10	12.00	13.10		
6P	5.00	7.10	11.00	12.10		
5P	4.00	6.10	10.00	11.10		
4P	3.00	5.10	9.00	10.10		
PIN	DIM=A	DIM=B	DIM=C	DIM=D	DIM=E	DIM=F

DRAWING:

Frank

CHECKED:

Tony

APPROVAL:

yang jie

GENERAL TOLERANCE

.X:=±0.15 .X*:=±5°

.XX:=±0.10 .XX*:=±3°


.XXX:=±0.05 .XXX*:=±1°

UNIT: MM

PROJECTION:

SCALE: 1/1

SHEET: 1/1

**CHIN-BAN**
electronics (H.K) co., ltd

DESCRIPTION:

1.0mm PITCH FPC CONN. H2.0mm UPPER CONTACT

PART NO: F4TXXU-A1X3-AX

REV: 1.0

DRAWING NO:

SIZE: A4