




ORDERING INFORMATION

- U 6 F 05 E - C X T 1 - B W - 1  
(1)(2)(3)(4)(5) (6)(7)(8)(9) (10)(11)
- SERIES NO.  
U: USB CONNECTOR SERIES
  - USB TYPE  
6: MICRO.USB 5Pin
  - USB MALE & FEMALE TYPE  
F: FEMALE
  - NUMBER OF PIN  
05: 5 POSITIONS
  - TAIL CONSTRUCTION TYPE  
E: TERMINAL: SMD TYPE  
SHELL: DIP TYPE
  - HOUSING COLOR  
C:COLOR:BLACK AND MATERIAL :LCP
  - CONTACT PLATING  
1: G/F 2: 5u'GOLD  
3: 10u'GOLD 4: 15u'GOLD  
5: 30u'GOLD 6: 3u'GOLD
  - SHELL PLATING  
T: TIN PLATING
  - PLASTIC ORIENTATION POST TYPE  
1: WITH POST
  - B TYPE OR AB TYPE  
B: B TYPE
  - SUFFIX NO.1  
W: FOR FLEXTRONICS

ELECTRICAL

- Current rating:  
Signal(pins 2,3,4): 1.0A;  
power(pins 1,5): 1.8A
- Contact resistance:30 milliohms max
- Insulation resistance:1000 Megohms min
- Withstanding voltage:100V AC/minute
- Temperature range:-30°C to +85°C

