


1.Description

The 78DXX three-terminal positive regulators are available in the TO-252 package with several fixed output voltages making it useful in a wide range of applications.


2.Features

- Output Current up to 1A
- Output Voltages of 5,6,8,9,12,15,18,24V
- Thermal Overload Protection Short Circuit Protection
- Output Transistor Safe Operating area (SOA) Protection

3.Pinning information



4.Internal Block Diagram





5. Absolute Maximum Rating

Parameter		Symbol	Value	Units
DC Input Voltage	for V _O =5 to 18 V	V _I	35	V
	for V _O =20, 24V		40	V
Output Current		I _{OUT}	1	A
Power Dissipation (T _C =25°C)	SOT-223	P _D	8.3	W
	TO-251/TO-252		10	
	TO-252-3			
Junction Temperature		T _J	-40 to 120	°C
Storage Temperature		T _{STG}	-55 to 150	°C

6. Thermal Data

Parameter		Symbol	Value	Units
Junction to Case	SOT-223	θ_{JC}	15	$^{\circ}\text{C/W}$
	TO-251/TO-252		12.5	
	TO-252-3			



7.1 Electrical Characteristics (78D05)

(Refer to the test circuits, 25°C, $I_o=350\text{mA}$, $V_i=10\text{V}$, unless otherwise specified, $C_i=0.33\mu\text{F}$, $C_o=0.1\mu\text{F}$)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Output Voltage	V_o	$I_o=5\text{mA}\sim 350\text{mA}$, $V_i=7\sim 20\text{V}$	4.75	5	5.25	V
Line Regulation(Note)	ΔV_o	$I_o=200\text{mA}$ $T_j=25^\circ\text{C}$			100	mV
		$V_i=7\text{V}\sim 25\text{V}$ $V_i=8\text{V}\sim 25\text{V}$			50	mV
Load Regulation(Note)	ΔV_o	$T_j=25^\circ\text{C}$			100	mV
		$I_o=5\text{mA}\sim 500\text{mA}$ $I_o=5\text{mA}\sim 200\text{mA}$			50	mV
Quiescent Current	I_Q	$T_j=25^\circ\text{C}$			8	mA
Quiescent Current Change	ΔI_Q	$I_o=5\text{mA}\sim 350\text{mA}$			0.5	mA
		$I_o=200\text{mA}$, $V_i=8\sim 25\text{V}$			0.8	mA
Output Voltage Drift	$\Delta V/\Delta T$	$I_o=5\text{mA}$, $T_j=0\sim 125^\circ\text{C}$		-0.5		mV/ $^\circ\text{C}$
Output Noise Voltage	V_N	$f=10\text{Hz}\sim 100\text{KHz}$		40		μV
Ripple Rejection	RR	$f=120\text{Hz}$, $V_i=8\sim 18\text{V}$		80		dB
Dropout Voltage	V_D	$T_j=25^\circ\text{C}$, $I_o=500\text{mA}$		2		V
Short Circuit Current	I_{SC}	$T_j=25^\circ\text{C}$, $V_i=35\text{V}$		800		mA
Peak Current	I_{PK}	$T_j=25^\circ\text{C}$		1300		mA

Notes:

Load and line regulation are specified at constant junction temperature. Change in V_o due to heating effects must be taken into account separately. Pulse testing with low duty is used.



7.2 Electrical Characteristics (78D06)

(Refer to the test circuits, 25°C, $I_o=350\text{mA}$, $V_i=11\text{V}$, unless otherwise specified, $C_i=0.33\mu\text{F}$, $C_o=0.1\mu\text{F}$)

Parameter	Symbol	Conditions		Min	Typ	Max	Units
Output Voltage	V_o	$I_o=5\text{mA}\sim 350\text{mA}$, $V_i=8\sim 21\text{V}$		5.7	6	6.3	V
Line Regulation(Note)	ΔV_o	$I_o=200\text{mA}$ $T_j=25^\circ\text{C}$	$V_i=8\text{V}\sim 25\text{V}$			100	mV
			$V_i=9\text{V}\sim 25\text{V}$			50	mV
Load Regulation(Note)	ΔV_o	$T_j=25^\circ\text{C}$	$I_o=5\text{mA}\sim 500\text{mA}$			120	mV
			$I_o=5\text{mA}\sim 200\text{mA}$			60	mV
Quiescent Current	I_Q	$T_j=25^\circ\text{C}$				8	mA
Quiescent Current Change	ΔI_Q	$I_o=5\text{mA}\sim 350\text{mA}$				0.5	mA
		$I_o=200\text{mA}$, $V_i=9\sim 25\text{V}$				0.8	mA
Output Voltage Drift	$\Delta V/\Delta T$	$I_o=5\text{mA}$, $T_j=0\sim 125^\circ\text{C}$			-0.5		mV/ $^\circ\text{C}$
Output Noise Voltage	V_N	$f=10\text{Hz}\sim 100\text{KHz}$			45		μV
Ripple Rejection	RR	$f=120\text{Hz}$, $V_i=9\sim 19\text{V}$			80		dB
Dropout Voltage	V_D	$T_j=25^\circ\text{C}$, $I_o=500\text{mA}$			2		V
Short Circuit Current	I_{SC}	$T_j=25^\circ\text{C}$, $V_i=35\text{V}$			800		mA
Peak Current	I_{PK}	$T_j=25^\circ\text{C}$			1300		mA

Notes:

Load and line regulation are specified at constant junction temperature. Change in V_o due to heating effects must be taken into account separately. Pulse testing with low duty is used.



7.3 Electrical Characteristics (78D08)

(Refer to the test circuits, 25°C, $I_o=350\text{mA}$, $V_i=14\text{V}$, unless otherwise specified, $C_i=0.33\mu\text{F}$, $C_o=0.1\mu\text{F}$)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Output Voltage	V_o	$I_o=5\text{mA}\sim 350\text{mA}$, $V_i=10.5\sim 23\text{V}$	7.6	8	8.4	V
Line Regulation(Note)	ΔV_o	$I_o=200\text{mA}$ $T_j=25^\circ\text{C}$			100	mV
		$V_i=10.5\text{V}\sim 25\text{V}$ $V_i=11\text{V}\sim 25\text{V}$			50	mV
Load Regulation(Note)	ΔV_o	$T_j=25^\circ\text{C}$			160	mV
		$I_o=5\text{mA}\sim 500\text{mA}$ $I_o=5\text{mA}\sim 200\text{mA}$			80	mV
Quiescent Current	I_Q	$T_j=25^\circ\text{C}$			8	mA
Quiescent Current Change	ΔI_Q	$I_o=5\text{mA}\sim 350\text{mA}$			0.5	mA
		$I_o=200\text{mA}$, $V_i=10.5\sim 25\text{V}$			0.8	mA
Output Voltage Drift	$\Delta V/\Delta T$	$I_o=5\text{mA}$, $T_j=0\sim 125^\circ\text{C}$		-0.8		mV/ $^\circ\text{C}$
Output Noise Voltage	V_N	$f=10\text{Hz}\sim 100\text{KHz}$		52		μV
Ripple Rejection	RR	$f=120\text{Hz}$, $V_i=11.5\sim 21.5\text{V}$		80		dB
Dropout Voltage	V_D	$T_j=25^\circ\text{C}$, $I_o=500\text{mA}$		2		V
Short Circuit Current	I_{SC}	$T_j=25^\circ\text{C}$, $V_i=35\text{V}$		800		mA
Peak Current	I_{PK}	$T_j=25^\circ\text{C}$		1300		mA

Notes:

Load and line regulation are specified at constant junction temperature. Change in V_o due to heating effects must be taken into account separately. Pulse testing with low duty is used.



7.4 Electrical Characteristics (78D09)

(Refer to the test circuits, 25°C, $I_o=350\text{mA}$, $V_i=15\text{V}$, unless otherwise specified, $C_i=0.33\mu\text{F}$, $C_o=0.1\mu\text{F}$)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Output Voltage	V_o	$I_o=5\text{mA}\sim 350\text{mA}$, $V_i=11.5\sim 24\text{V}$	8.45	9	9.55	V
Line Regulation(Note)	ΔV_o	$I_o=200\text{mA}$ $T_j=25^\circ\text{C}$			100	mV
		$V_i=11.5\text{V}\sim 25\text{V}$ $V_i=12\text{V}\sim 25\text{V}$			50	mV
Load Regulation(Note)	ΔV_o	$T_j=25^\circ\text{C}$			180	mV
		$I_o=5\text{mA}\sim 500\text{mA}$ $I_o=5\text{mA}\sim 200\text{mA}$			90	mV
Quiescent Current	I_Q	$T_j=25^\circ\text{C}$			8	mA
Quiescent Current Change	ΔI_Q	$I_o=5\text{mA}\sim 350\text{mA}$			0.5	mA
		$I_o=200\text{mA}$, $V_i=11.5\sim 25\text{V}$			0.8	mA
Output Voltage Drift	$\Delta V/\Delta T$	$I_o=5\text{mA}$, $T_j=0\sim 125^\circ\text{C}$		-0.8		mV/ $^\circ\text{C}$
Output Noise Voltage	V_N	$f=10\text{Hz}\sim 100\text{KHz}$		52		μV
Ripple Rejection	RR	$f=120\text{Hz}$, $V_i=12.5\sim 22.5\text{V}$		80		dB
Dropout Voltage	V_D	$T_j=25^\circ\text{C}$, $I_o=500\text{mA}$		2		V
Short Circuit Current	I_{SC}	$T_j=25^\circ\text{C}$, $V_i=35\text{V}$		800		mA
Peak Current	I_{PK}	$T_j=25^\circ\text{C}$		1300		mA

Notes:

Load and line regulation are specified at constant junction temperature. Change in V_o due to heating effects must be taken into account separately. Pulse testing with low duty is used.



7.5 Electrical Characteristics (78D12)

(Refer to the test circuits, 25°C, $I_o=350\text{mA}$, $V_i=19\text{V}$, unless otherwise specified, $C_i=0.33\mu\text{F}$, $C_o=0.1\mu\text{F}$)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Output Voltage	V_o	$I_o=5\text{mA}\sim 350\text{mA}$, $V_i=14.5\sim 27\text{V}$	11.4	12	12.6	V
Line Regulation(Note)	ΔV_o	$I_o=200\text{mA}$ $T_j=25^\circ\text{C}$			100	mV
		$V_i=14.5\sim 30\text{V}$ $V_i=16\sim 30\text{V}$			50	mV
Load Regulation(Note)	ΔV_o	$T_j=25^\circ\text{C}$			240	mV
		$I_o=5\text{mA}\sim 500\text{mA}$ $I_o=5\text{mA}\sim 200\text{mA}$			120	mV
Quiescent Current	I_Q	$T_j=25^\circ\text{C}$			8	mA
Quiescent Current Change	ΔI_Q	$I_o=5\text{mA}\sim 350\text{mA}$			0.5	mA
		$I_o=200\text{mA}$, $V_i=14.5\sim 30\text{V}$			0.8	mA
Output Voltage Drift	$\Delta V/\Delta T$	$I_o=5\text{mA}$, $T_j=0\sim 125^\circ\text{C}$		-0.8		mV/ $^\circ\text{C}$
Output Noise Voltage	V_N	$f=10\text{Hz}\sim 100\text{KHz}$		75		μV
Ripple Rejection	RR	$f=120\text{Hz}$, $V_i=15\sim 25\text{V}$		80		dB
Dropout Voltage	V_D	$T_j=25^\circ\text{C}$, $I_o=500\text{mA}$		2		V
Short Circuit Current	I_{SC}	$T_j=25^\circ\text{C}$, $V_i=35\text{V}$		800		mA
Peak Current	I_{PK}	$T_j=25^\circ\text{C}$		1300		mA

Notes:

Load and line regulation are specified at constant junction temperature. Change in V_o due to heating effects must be taken into account separately. Pulse testing with low duty is used.



7.6 Electrical Characteristics (78D15)

(Refer to the test circuits, 25°C, $I_o=350\text{mA}$, $V_i=23\text{V}$, unless otherwise specified, $C_i=0.33\mu\text{F}$, $C_o=0.1\mu\text{F}$)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Output Voltage	V_o	$I_o=5\text{mA}\sim 350\text{mA}$, $V_i=17.5\sim 30\text{V}$	14.25	15	15.75	V
Line Regulation(Note)	ΔV_o	$I_o=200\text{mA}$ $T_j=25^\circ\text{C}$			100	mV
		$V_i=17.5\text{V}\sim 30\text{V}$ $V_i=20\text{V}\sim 30\text{V}$			50	mV
Load Regulation(Note)	ΔV_o	$T_j=25^\circ\text{C}$			300	mV
		$I_o=5\text{mA}\sim 500\text{mA}$ $I_o=5\text{mA}\sim 200\text{mA}$			150	mV
Quiescent Current	I_Q	$T_j=25^\circ\text{C}$			8	mA
Quiescent Current Change	ΔI_Q	$I_o=5\text{mA}\sim 350\text{mA}$			0.5	mA
		$I_o=200\text{mA}$, $V_i=17.5\sim 30\text{V}$			0.8	mA
Output Voltage Drift	$\Delta V/\Delta T$	$I_o=5\text{mA}$, $T_j=0\sim 125^\circ\text{C}$		-1		mV/ $^\circ\text{C}$
Output Noise Voltage	V_N	$f=10\text{Hz}\sim 100\text{KHz}$		100		μV
Ripple Rejection	RR	$f=120\text{Hz}$, $V_i=18.5\sim 28.5\text{V}$		70		dB
Dropout Voltage	V_D	$T_j=25^\circ\text{C}$, $I_o=500\text{mA}$		2		V
Short Circuit Current	I_{SC}	$T_j=25^\circ\text{C}$, $V_i=35\text{V}$		800		mA
Peak Current	I_{PK}	$T_j=25^\circ\text{C}$		1300		mA

Notes:

Load and line regulation are specified at constant junction temperature. Change in V_o due to heating effects must be taken into account separately. Pulse testing with low duty is used.



7.7 Electrical Characteristics (78D18)

(Refer to the test circuits, 25°C, $I_o=350\text{mA}$, $V_i=26\text{V}$, unless otherwise specified, $C_i=0.33\mu\text{F}$, $C_o=0.1\mu\text{F}$)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Output Voltage	V_o	$I_o=5\text{mA}\sim 350\text{mA}$, $V_i=20.5\sim 33\text{V}$	17.1	18	18.9	V
Line Regulation(Note)	ΔV_o	$I_o=200\text{mA}$ $T_j=25^\circ\text{C}$			100	mV
		$V_i=21\text{V}\sim 33\text{V}$ $V_i=24\text{V}\sim 33\text{V}$			50	mV
Load Regulation(Note)	ΔV_o	$T_j=25^\circ\text{C}$			360	mV
		$I_o=5\text{mA}\sim 500\text{mA}$ $I_o=5\text{mA}\sim 200\text{mA}$			180	mV
Quiescent Current	I_Q	$T_j=25^\circ\text{C}$			8	mA
Quiescent Current Change	ΔI_Q	$I_o=5\text{mA}\sim 350\text{mA}$			0.5	mA
		$I_o=200\text{mA}$, $V_i=21\sim 33\text{V}$			0.8	mA
Output Voltage Drift	$\Delta V/\Delta T$	$I_o=5\text{mA}$, $T_j=0\sim 125^\circ\text{C}$		-1.2		mV/ $^\circ\text{C}$
Output Noise Voltage	V_N	$f=10\text{Hz}\sim 100\text{KHz}$		100		μV
Ripple Rejection	RR	$f=120\text{Hz}$, $V_i=22\sim 32\text{V}$		70		dB
Dropout Voltage	V_D	$T_j=25^\circ\text{C}$, $I_o=500\text{mA}$		2		V
Short Circuit Current	I_{SC}	$T_j=25^\circ\text{C}$, $V_i=35\text{V}$		800		mA
Peak Current	I_{PK}	$T_j=25^\circ\text{C}$		1300		mA

Notes:

Load and line regulation are specified at constant junction temperature. Change in V_o due to heating effects must be taken into account separately. Pulse testing with low duty is used.



7.8 Electrical Characteristics (78D24)

(Refer to the test circuits, 25°C, $I_o=350\text{mA}$, $V_i=33\text{V}$, unless otherwise specified, $C_i=0.33\mu\text{F}$, $C_o=0.1\mu\text{F}$)


Parameter	Symbol	Conditions		Min	Typ	Max	Units
Output Voltage	V_o	$I_o=5\text{mA}\sim 350\text{mA}$, $V_i=27\sim 35\text{V}$		22.8	24	25.2	V
Line Regulation(Note)	ΔV_o	$I_o=200\text{mA}$ $T_j=25^\circ\text{C}$	$V_i=27\text{V}\sim 35\text{V}$			100	mV
			$V_i=28\text{V}\sim 35\text{V}$			50	mV
Load Regulation(Note)	ΔV_o	$T_j=25^\circ\text{C}$	$I_o=5\text{mA}\sim 500\text{mA}$			480	mV
			$I_o=5\text{mA}\sim 200\text{mA}$			240	mV
Quiescent Current	I_Q	$T_j=25^\circ\text{C}$				8	mA
Quiescent Current Change	ΔI_Q	$I_o=5\text{mA}\sim 350\text{mA}$				0.5	mA
		$I_o=200\text{mA}$, $V_i=27\sim 38\text{V}$				0.8	mA
Output Voltage Drift	$\Delta V/\Delta T$	$I_o=5\text{mA}$, $T_j=0\sim 125^\circ\text{C}$			-1.2		mV/ $^\circ\text{C}$
Output Noise Voltage	V_N	$f=10\text{Hz}\sim 100\text{KHz}$			170		μV
Ripple Rejection	RR	$f=120\text{Hz}$, $V_i=28\sim 38\text{V}$			70		dB
Dropout Voltage	V_D	$T_j=25^\circ\text{C}$, $I_o=500\text{mA}$			2		V
Short Circuit Current	I_{SC}	$T_j=25^\circ\text{C}$, $V_i=35\text{V}$			800		mA
Peak Current	I_{PK}	$T_j=25^\circ\text{C}$			1300		mA

Notes:

Load and line regulation are specified at constant junction temperature. Change in V_o due to heating effects must be taken into account separately. Pulse testing with low duty is used.




8. Typical Application





9.1 SOT-223Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	b1	c	D	E	E1	e	L	θ
Min	-	0.020	1.500	0.660	2.900	0.230	6.300	6.700	3.300	2.300	0.750	0°
Max	1.800	0.100	1.700	0.840	3.100	0.350	6.700	7.300	3.700	BSC	-	10°



9.2TO-252 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A1	A2	A3	b	c	D	D1	D2	E	E1	E2	e	L1	L2	L3	θ
Min	0.00	2.18	0.90	0.65	0.46	6.35	4.95	4.32	9.40	5.97	5.21	2.286	0.89	1.70	0.60	0.00
Max	0.13	2.39	1.10	0.85	0.61	6.73	5.46	4.90	10.41	6.22	5.38		BSC	1.27	1.90	1.00



10.Ordering information



yy: Year Code
ww: Week Code

Order Code	Package	Base QTY	Delivery Mode
UMW 78Dxx	TO-252	2500	Tape and reel



11.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.