







REVISIONS				
LTR	DESCRIPTION	DATE	REVISED	APPROVED




P.C.B LAND PATTERN


Specifications:
Rating:DC50V 1A
Force:5-35N
Contact resistance:
Less than30mΩ
Insulation resistance:
Over100MΩ on DC 500V measured.
Voltage withstand:
AC 500V For 1minute,



SCHEMATIC



HEX NUT



FLAT WASHER

9	FLAT WASHER	1	STEEL	T=0.5	MB:Ni	
8	HEX NUT	1	BRASS		MB:Ni	
7	SLEEVE	1	BRASS		MB:Ni	
6	T TERMINAL-R	1	BRONZE	Y=0.4	MB:Cu,Ag	No.3
5	TIP SPPING	1	BRONZE	Y=0.4	MB:Cu,Ag	No.2
4	EARTH SPPING	1	BRONZE	Y=0.2	MB:Cu,Ag	
3	IRONAND STEEL	1	STEEL	T=0.5	MB:Cu,Sn	No.1
2	COVER	1	ABS	94HB	RED	
1	HOUSING	1	ABS	94HB	BLACK	
LTR	PART NAME	QTY	MATERIAL		FINISH	REMARK

DSND	ZHANGGUOJING	DATE	2013-09-20	TOLERANCE	SCALE 2/1	NAME	PHONE JACK
CHKD		DATE		X.X ±0.3	UNIT:mm	CAT.NO.	CK-6318B-S
APPD		DATE		X.XX ±0.2			
				X.XXX ±0.1			
				ANGLE ±3.0°			

浙江创都电子科技有限公司

DWN.NO.