

CUSTOMER: _____

DATE: _____

APPROVAL SPECIFICATION



PRODUCT NAME: Winding Wire Common Mode Choke Coil

YOUR PART NO.:

OUR PART NO.: MGRC3225L601T-2-LF

VERSION: V1.0

RECEPTION THE SPECIFICATION HAS BEEN ACCEPTED. <div style="display: flex; justify-content: space-between;"> <div>COMPANY:</div> <div>DATE:</div> </div>		
CFMD	CHKD	RCVD

MANUFACTURING NAME

SHENZHEN MICROGATE TECHNOLOGY CO., LTD

Address: Microgate Technology Building, No.16 ,
Science&Technology Road , Pingshan District ,
Shenzhen China

Postcode :518122

TEL: 86-755-28085000

FAX: 86-755-28085605

CFMD.	CHKD.	DSGD.
Remo	Xiaojian Cai	Wei Liu

CATALOG

	Component SPEC Version Record.....	3
1	Scope.....	4
2	Product Identification.....	4
3	Appearance, Dimensions	4
4	Electrical Schematic.....	4
5	Testing Conditions.....	5
6	Rating.....	5
7	Reliable Performance.....	6-7
8	Recommended Soldering Conditions.....	8-9
9	Packaging.....	9-10
10	Products Storage.....	10
11	Transportation.....	11
12	Warning and Attentions.....	11-13
13	Solder Volume.....	13
14	Circuit Design.....	13
15	Cleaning.....	13

SHENZHEN MICROGATE TECHNOLOGY COLTD.

Add: Microgate Technology Building, No.16 , Science&Technology Road , Pingshan District , Shenzhen
China

Tel: 0755-28085000 Fax: 0755-28085605 Postcode: 518122

2/13

Component SPEC Version Record

Rev.	Effective Date	Changed Contents	Change Reasons	Approved By
1.0	2019.07.24	New released	/	Remo

SHENZHEN MICROGATE TECHNOLOGY COLTD.

Add: Microgate Technology Building, No.16 , Science&Technology Road , Pingshan District , Shenzhen
China

Tel: 0755-28085000 Fax: 0755-28085605 Postcode: 518122

3/13

1.Scope


This specification applies to the MGRC3225 series of Common Mode Choke Coil.

2.Product Identification


<u>MGRC</u>	<u>3225</u>	<u>L</u>	<u>601</u>	<u>T</u>	-	<u>2</u>	-	<u>LF</u>
①	②	③	④	⑤		⑥		⑦

- ① Series name (Wire Wound Chip Common Mode Choke Coil)
- ② Dimensions L×W: (3225=3.2×2.5 mm)
- ③ Material code (L For Larger Current)
- ④ Impedance: (Example 601=60×10¹=600Ω)
- ⑤ Packing Style: (T: Taping B: Bulk)
- ⑥ Number of signal lines
- ⑦ Lead Free

3.Appearance, Dimensions



4.Electrical Schematic



SHENZHEN MICROGATE TECHNOLOGY COLTD.

Add: Microgate Technology Building, No.16 , Science&Technology Road , Pingshan District , Shenzhen China

Tel: 0755-28085000

Fax: 0755-28085605

Postcode: 518122

4/13

5. Testing Conditions

<Unless otherwise specified>

Temperature : Ordinary Temperature 5 to 35°C

Humidity : Ordinary Humidity 25 to 85% (RH)

<In case of doubt>

Temperature : 20±2°C


Humidity : 60 to 75% (RH)

Atmospheric Pressure : 86 to 106 kPa

6. Rating

Operating Temperature Range : -40 to +85°C

Part No.	Common-mode Impedance Z(Ω)at 100MHz	DC Resistance Rdc (mΩ) Max	Rated Current Idc (mA) Max	Rated Voltage Vdc (V)	Insulation Resistance (MΩ)
MGRC3225L601T-2-LF	600±25%	120	1000	50	10



SHENZHEN MICROGATE TECHNOLOGY COLTD.

Add: Microgate Technology Building, No.16 , Science&Technology Road , Pingshan District , Shenzhen China




Tel: 0755-28085000

Fax: 0755-28085605

Postcode: 518122

5/13

7.Reliable Performance

NO.	Item	Specifications	Test Methods
1	Solder-Ability	Terminal area shall be at least 95% covered .	Solder: 96.5% Sn +3.0%Ag+0.5%Cu Temperature: 245°C±5°C Flux: rosin Duration: 3.5±0.5s
2	Leaching Resistance	1) No case deformation or change in appearance. 2) $ \Delta Z/Z_0 \leq 20\%$	①The peak temperature: 260+5/-0°C. ②Reflow:2 times. ③Temperature curve is as below: 
3	Terminal Strength	The terminal and body should be no damage	Solder a chip to test substrate, and then laterally apply a load 10N in the X, Y and Z directions 
4	Bending Strength	No mechanical damage should be noticed	Soldering a chip to a test subatrate, bend the substrate by 2mm and then return 

SHENZHEN MICROGATE TECHNOLOGY COLTD.

Add: Microgate Technology Building, No.16 , Science&Technology Road , Pingshan District , Shenzhen China

Tel: 0755-28085000

Fax: 0755-28085605

Postcode: 518122

6/13

NO.	Item	Specifications	Test Methods
5	Vibration	1) No mechanical damage shall be noticed 2) $ \Delta Z/Z_0 \leq 20\%$	Frequency: 10 to 55Hz Amplitude: 1.5mm Direction and time :X, Y and Z directions for 2 hours each.
6	Humidity resistance		a. Test condition Temp.: $85 \pm 2^\circ\text{C}$ Humidity: 90%~95% Test time: 1000 ± 24 h b. Measurement method: The component should be stabilized at normal condition for (24 ± 2) hours before test.
7	High temperature resistance		a. Test condition Applied rated current. Temp.: $85 \pm 2^\circ\text{C}$ Test time: 1000 ± 24 h b. Measurement method: The component should be stabilized at normal condition for (24 ± 2) hours before test.
8	Low temperature resistance		a. Test condition Temp.: $-40 \pm 2^\circ\text{C}$ Test time: 1000 ± 24 h b. Measurement method: The component should be stabilized at normal condition for (24 ± 2) hours before test.
9	Thermal shock (Temperature cycle)		a. Test condition 1) Temp.: -40°C , time: 30 ± 3 min 2) Temp.: $+85^\circ\text{C}$, time: 30 ± 3 min 5 cycles b. Measurement method: The component should be stabilized at normal condition for (24 ± 2) hours before test.

SHENZHEN MICROGATE TECHNOLOGY COLTD.

Add: Microgate Technology Building, No.16 , Science&Technology Road , Pingshan District , Shenzhen China

Tel: 0755-28085000


Fax: 0755-28085605

Postcode: 518122

7/13

8. Recommended Soldering Conditions

(1) Recommended Footprint




a	1.90 mm
b	3.70 mm
c	2.55 mm
d	0.70 mm

(2) Recommended Reflow soldering conditions

Profile Feature	Lead-Free Assembly
Average Ramp-Up Rate (T _{smax} to T _p)	3°C /second max.
Preheat <ul style="list-style-type: none"> Temperature Min (T_{smin}) Temperature Max (T_{smax}) Time (t_{smin} to t_{smax}) 	150 °C 200 °C 60-180 seconds
Time maintained above: <ul style="list-style-type: none"> Temperature (T_L) Time (t_L) 	217 °C 60-150 seconds
Peak/Classification Temperature (T _p)	255 °C
Peak/Classification Time (T _p)	30 seconds max.
Time within 5 °C of actual Peak Temperature (t _p)	20-40 seconds
Ramp-Down Rate	6 °C/second max.
Time 25 °C to Peak Temperature	8 minutes max.

Note 1: All temperatures refer to topside of the package, measured on the package body surface.

Standard soldering profile



SHENZHEN MICROGATE TECHNOLOGY COLTD.

Add: Microgate Technology Building, No.16 , Science&Technology Road , Pingshan District , Shenzhen China

Tel: 0755-28085000

Fax: 0755-28085605

Postcode: 518122

8/13


(3) Reworking with soldering iron

The following conditions must be strictly followed when using a soldering iron.

Pre-heating	150°C, 1 minute
Tip temperature	350°C max
Soldering iron output	30w max
End of soldering iron	φ 1mm max
Soldering time	5 seconds max

9.Packaging


(1) Dimensions of Tape:



(Dimensions in mm; Tolerance : ±0.1)

Symbol	W	P	P ₀	P ₁	A ₀	B ₀	K ₀	t
Dimension	8.00	4.00	4.00	2.00	2.80	3.50	2.20	0.24

(2) Dimensions of Reel



SHENZHEN MICROGATE TECHNOLOGY COLTD.

Add: Microgate Technology Building, No.16 , Science&Technology Road , Pingshan District , Shenzhen China

Tel: 0755-28085000

Fax: 0755-28085605


Postcode: 518122

9/13

(3) Pulling strength of tapes:

Carrier tape	10N or more (1kgf or more)
Cover tape	5N or more (1kgf or more)


(4) Taping figure and drawing direction:



Tape material: Base tape: Polystyrene Cover tape: polyester

(5) Peeling strength of cover tape:

Cover tape	0.10~1.0N
------------	-----------



Test condition:

Temperature: 5~35°C

Humidity: 45~85%

(6) Packing quantity

Φ180 mm reel T type: 1500pcs/reel

10. Products Storage

- The solder ability of the external electrode may be deteriorated if packages are stored where they are exposed to high temperature or high humidity. Besides, to ensure packing material's good state, packages must be stored at -10°C to 40°C and 70% RH.
- The solder ability of the external electrode may be deteriorated if packages are stored where they are exposed to dust or harmful gas (e.g. HCl, sulfurous gas of H₂S).
- Packaging materials may deform if packages are exposed directly to sunlight.
- Minimum packages, such as polyvinyl heat-seal packages shall not be opened until they are used. If opened, use the reels as soon as possible.
- Solderability shall be guaranteed for 12 months from the date of delivery on condition that they are stored at the environment specified in specification. For those parts, which passed more than the time shall be checked solder-ability before use.

SHENZHEN MICROGATE TECHNOLOGY COLTD.

Add: Microgate Technology Building, No.16, Science&Technology Road, Pingshan District, Shenzhen China

Tel: 0755-28085000

Fax: 0755-28085605

Postcode: 518122

10/13

11. Transportation

The cases shall not be damaged, destroyed and rained on.

12. Warning and Attentions

(1) General Handling Precautions

- a. Handling
 - i. Always wear static control bands to protect against ESD.
 - ii. Any devices used (soldering iron, measuring instruments) should be properly grounded.
 - iii. Use non-magnetic tweezers when handing the chips.
- b. Breakaway PC boards(splitting along perforations)
 - i. When splitting the PCB after mounting product, care should be taken not to give any stresses of deflection or twisting to the board.
 - ii. Board separation should not be done manually, but by using the appropriate devices.
- c. Mechanical considerations
 - i. Please do not give the product any excessive mechanical shocks.
 - ii. Please do not add any shock and power to a product in transportation.
- d. Pick-up pressure
 - i. Please do not push to add any pressure to a winding part; please do not give any shock and push into a ferrite core exposure part

(2) Precautions on Use

- a. Always wear static control bands to protect against ESD.
- b. Any devices used (soldering iron, measuring instruments) should be properly grounded.
- c. Use non-magnetic tweezers when handing the chips.
- d. Pre-heating when soldering, and refer to the recommended condition specified in specification.
- e. Don't apply current in excess of the rated current value. It may cause damage to components due to over-current.
- f. Keep clear of anything that may generate magnetic fields such as speakers, coils.
- g. When soldering, the electrical characteristics (such as impedance) may be varied due to hot energy and mechanical stress.
- h. When coating products with resin, the relatively high resin curing stress may change the electrical characteristics. For exterior coating, select resin carefully so that electrical and mechanical performance of the product is not affected. Before using, please evaluate reliability with the product mounted in your application set.
- i. When mount chips with adhesive in preliminary assembly, do appropriate check before the soldering stage, i.e., the size of land pattern, type of adhesive, amount applied, hardening of the adhesive on proper usage and amounts of adhesive to use.
- j. Mounting density: Add special attention to radiating heat of products when mounting other components nearby. The excessive heat by other products may cause deterioration at joint of this product with substrate.
- k. Since some products are constructed like an open magnetic circuit, narrow spacing between components may cause magnetic coupling.
- l. Please do not give the product any excessive mechanical shocks in transportation.
- m. Please do not touch wires by sharp terminals such as tweezers to avoid causing any damage to wires.

SHENZHEN MICROGATE TECHNOLOGY COLTD.

Add: Microgate Technology Building, No.16 , Science&Technology Road , Pingshan District , Shenzhen China

Tel: 0755-28085000 Fax: 0755-28085605 Postcode: 518122


11/13

- n. Please do not add any shock and power to the soldered product to avoid causing any damage to chip body.
- o. Please do not touch the electrodes by naked hand as the solderability of the external electrodes may deteriorate by grease or oil on the skin.


(3) PCB Bending Design

The following shall be considered when designing and laying out PCB's.

- a. PCB shall be designed so that products are not subjected to the mechanical stress from board warp or deflection.



- b. Products location on PCB separation.



- c. When splitting the PCB board, or insert (remove) connector, or fasten thread after mounting components, care is required so as not to give any stress of deflection or twisting to the board. Because mechanical force may cause deterioration of the bonding strength of electrode and solder, even crack of product body. Board separation should not be done manually, but by using appropriate devices.

(4) Recommended PCB Design for SMT Land-Patterns

When chips are mounted on a PCB, the amount of solder used (size of fillet) and the size of PCB Land-Patterns can directly affect chip performance. Therefore, the following items must be carefully considered in the design of solder land patterns.

- a. Please use the PCB pad and solder paste we recommend, and contact us in advance if they need to be changed.
- b. The amount of solder applied can affect the ability of chips to withstand mechanical stresses which may lead to breaking or cracking. Therefore, when designing land-patterns it is necessary to consider the appropriate size and configuration of the solder pads which in turn determines the amount of solder necessary to form the fillets.
- c. When more than one part is jointly soldered onto the same land or pad, the pad must be designed that each component's soldering point is separated by solder-resist.

Recommended land dimensions please refer to product specification.

13.Solder Volume


Solder shall be used not to exceed as shown below.

SHENZHEN MICROGATE TECHNOLOGY COLTD.

Add: Microgate Technology Building, No.16 , Science&Technology Road , Pingshan District , Shenzhen China

Tel: 0755-28085000 Fax: 0755-28085605 Postcode: 518122

12/13



- Accordingly increasing the solder volume, the mechanical stress to chip is also increased. Exceeding solder volume may cause the failure of mechanical or electrical performance.
- Before soldering, please ensure that the solder should not adhere to the wire part of chip.
- Please pay particular attention to whether there is flux remaining on surface of the wire part of chip after subjected to reflow soldering since this may causing short circuit of parts.

14. Circuit Design

Operating environment: The products described in this specification are intended for use in general electronic equipment, (office supply equipment, telecommunications systems, measuring equipment, and household equipment). They are not intended for use in mission-critical equipment or systems requiring special quality and high reliability (traffic systems, safety equipment, aerospace systems, nuclear control systems and medical equipment including life-support systems) where product failure might result in loss of life injury or damage. For such uses, contact Sunlord Sales Department in advance

15. Cleaning

Products shall be cleaned on the following conditions:

- Cleaning temperature shall be limited to 60°C Max. (40°C Max. for fluoride and alcohol type cleaner.)
- Ultrasonic cleaning shall comply with the following conditions, avoiding the resonance phenomenon at the mounted products and PCB.

Power: 20W/1 Max.

Frequency: 28 KHz to 40 KHz

Time: 5 minutes Max

- Cleaner

- Alternative cleaner

- Isopropyl alcohol (IPA)
- HCFC-225

- Aqueous agent

- Surface Active Agent Type (Clean through-750H)
- Hydrocarbon Type (Techno Cleaner-335)
- Higher Alcohol Type (Pine Alpha ST-100S)
- Alkali saponifier Type (※ Aqua Cleaner 240)

※ Alkali saponification shall be diluted to 20% volume with de-ionized water.

※ Please contact our technical service department before using other cleaner.

- There shall be no residual flux and residual cleaner after cleaning. In the case of using aqueous agent, product shall be dried completely after rinse with de-ionized water in order to remove the cleaner.
- Some products may become slightly whitened. However, product performance or usage is not affected.
- Please take care of winding part while cleaning.
- After cleaning, parts could be subjected to the next reflow soldering till the solvent remaining on surface of parts being volatilized.

SHENZHEN MICROGATE TECHNOLOGY COLTD.

Add: Microgate Technology Building, No.16, Science & Technology Road, Pingshan District, Shenzhen China

Tel: 0755-28085000

Fax: 0755-28085605

Postcode: 518122

13/13