

标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

NOTES:

1. MATERIAL:

1.1. HOUSING: PBT ,COLOR IS BLACK;

1.2. CONTACT: PHOSPHOR BRONZE, $\phi 0.46 \pm 0.02\text{mm}$;

2. FINISH: CONTACT: PLATED GOLD OVER NI;

3. RECINNEBDED PCB THICKNESS: 1.0mm Min;

4. ELECTRICAL:

4.1. VOLTAGE RATING: 125 VAC RMS;

4.2. CURRENT RATING: 1.5 AMP;

4.3. CONTACT RESISTANCE: 35MILLIOHMS MAX.;

4.4. WITHSTAND VOLTAGE: 1000 VAC RMS

50(60)Hz,1MIN.;

4.5. INSULATION RESISTANCE: 1000MEGOHMS MIN @500V

DC;

5. MECHANICAL:

5.1. MATING/UNMATING FORCE: 30N MAX.;






5.2. RETENTION STRENGTH: 50N MIN.;

5.3. OPERATING LIFE: 750 CYCLES MIN.;

6. SALT SPRAY TEST: 12H;

7. SOLDERABILITY: $245 \pm 5^\circ\text{C}$, $5 \pm 0.5\text{S}$;

8 ENVIRONMENTAL:

8.1. STORAGE TEMPERATURE RANGE: $-40^\circ\text{C} \sim +85^\circ\text{C}$;8.2. OPERATION TEMPERATURE RANGE: $-25^\circ\text{C} \sim +70^\circ\text{C}$;

RECOMMENDED PCB LAYOUT

TOP VIEW(TOL: ± 0.05)

2	接触	铜	镀金G/F	
1	底座	PBT	黑色	
序号	品名	材质	电镀/颜色	备注

	深圳市虹成电子有限公司		品名 TITLE	网口 RJ55
			料号 PART NO	HC-WK88-H13-1X4-55QS
UNLESS OTHERWISE, GENERAL TOLERANCE:		比列 SCALE	1:1	
X. xxx ± 0.10 X. xx ± 0.20 X. x ± 0.30		单位 UNIT	MM	制图 DRAW
ANGULAR: X. xx° $\pm 1^\circ$ X. x° $\pm 3^\circ$ X. ° $\pm 5^\circ$		张数 PART NO	1 OF 1	审核 CHECKED
		版本 REV	A	批准 APPROVE
		夏操云		赵亮亮

