



汇隆电子(金华)有限公司
HUILONG ELECTRONIC (JINHUA) CO.,LTD

SPECIFICATION FOR APPROVAL

CUSTOMER _____

NOMINAL FREQUENCY _____ 54.000000 MHz _____

HOLDER TYPE _____ 2520 _____

SPEC. NO. (P/N) _____ HH54000010 _____

CUSTOMER P/N _____

ISSUE DATE _____ Mar.11,2021 _____

APPROVED	PREPARED	QA
		
APPROVED BY CUSTOMER :		AVL Status
Please return one copy with approval toHLC		

浙江省金华市经济开发区工业园区秋涛北街
399号
No.399 Qiutao North Str.,Industrial
Area,Economic Development
Zone,Jinhua,Zhejiang,China
TEL: 0086-579-82273331



ISO9001
ISO14001



RoHS Compliant (Pb- Free)



TYPE HH SEAM SEALED X'TAL

ELECTRICAL SPECIFICATIONS

HLC Parts Number : HH54000010

Item	Symbol	Specifications				Notes
		Min	Type	Max	Units	
Nominal frequency	FO	54.000000			MHz	
Mode of Oscillation	OT	Fundamental				
Load Capacitance	LC	19			pF	
Frequency Tolerance	FT	± 3			ppm	at 25°C ± 3°C
Frequency Stability		± 14			ppm	with working temperature Reference to 25°C
Working temperature range	TR	-40~100			°C	
Drive Level	DL		100	500	μW	
Series Resonant Resistance RR	CI/RR	15			Ω	Max.
Insulation Resistance	IR	>500			MΩ	
Shunt Capacitance C0	C0	3			pF	Max.
Aging+Reflow	dF/F25	-3		3	ppm	5year
Storage temperature range		-55 ~ 125			°C	
DLDF		<0				
SPDB		<-3			dB	F0±500KHz

Circuit : Measured by SAUNDERS & ASSOCIATES 250B-1
NETWORK ANALYZER

Insulation Resistance : More Than 500 MΩ at DC 100V


Hermetically (1)Fine Leak : Helium Bombing 4kg /cm² for 1 Hours
(2)Gross Leal : Leak Rate Less Than 1*10⁻⁹ Pa · m³/sec
By Heliot 701W1 M/C



TYPE HH SEAM SEALED X'TAL

RELIABILITY SPECIFICATIONS

NO.	TEST ITEM	TEST METHODS
1	DROP TEST	Device are dropped from a height of 75 cm onto 2 mm thickness stainless plate executing 3 times of random drops.
2	MECHANICAL SHOCK	Device are shocked to half sine wave (1000 G) three mutually perpendicular axes each 3 times.
3	VIBRATION	Frequency range 10 ~ 2000 Hz Amplitude 1.5 mm Sweep Time 20 minute Test Time 2 hours
4	SOLDERABILITY	MIL - STD - 20E Method 208C Temperature 245°C±5°C Material H63A (Silver 2 ~ 3 %) Immersion depth 0.5 mm minimum Immersion time 3 ± 0.5 seconds Flux Rosin resin methyl alcohol solvent (1 : 4)
5	RESISTANCE TO SOLDERING HEAT	MIL - SLD -202, Method 210, Condition I or J 10 sec immersion into 260 ± 5°C solder pot, above 180°C is 90 ~ 120 sec.
6	LOW TEMP. STORAGE	Leave at - 55 °C ± 2°C for 1000 ± 12 hours
7	HIGH TEMP. STORAGE	Leave at 125 °C ± 2°C for 1000 ± 12 hours
8	THERMAL SHOCK	Total 100 cycles of the following temperature cycle





TYPE HH SEAM SEALED X'TAL

HLC

*** 54.0xx**

HLC: HLC Use Code x: CL Code

x: Date Code

CL	Cod	CL	Cod	CL	Code
0pf	0	7.5pf	H	11.2pf	a
6pf	1	11pf	I	11.4pf	b
8pf	2	8.5pf	J	13.5pf	d
10pf	3	7.1pf	K	20.5pf	e
12pf	5	19pf	L		
15pf	6	12.5pf	M		
16pf	7	27pf	N		
18pf	8	7.3pf	O		
20pf	9	13pf	P		
22pf	A	11.5pf	Q		
25pf	B	7pf	R		
28pf	C	14pf	S		
30pf	D	23pf	T		
32pf	E	11.1pf	U		
9.5pf	F	33pf	V		
9pf	G	10.5pf	W		
		9.2pf	Y		
		50pf	Z		

Jan-17	N	Jan-18	A
Feb-17	P	Feb-18	B
Mar-17	Q	Mar-18	C
Apr-17	R	Apr-18	D
May-17	S	May-18	E
Jun-17	T	Jun-18	F
Jul-17	U	Jul-18	G
Aug-17	V	Aug-18	H
Sep-17	W	Sep-18	J
Oct-17	X	Oct-18	K
Nov-17	Y	Nov-18	L
Dec-17	Z	Dec-18	M


备注：年份印字代码原则按奇偶年两年一个循环

HUILONG ELECTRONIC (JINHUA) CO.,LTD



TYPE HH SEAM SEALED X'TAL


DIMENSIONS






TYPE HH SEAM SEALED X'TAL

SUGGESTED IR REFLOW PROFILE



Total Time : 200 Sec.Max
Solder melting point : 185°C

PACKING



1. 230mm minimum leader which consist of carrier and/or tape followed by a minimum of 160mm of empty carrier tape sealed with cover tape.
2. 160mm minimum trailer of empty carrier tape sealed with cover tape.





HUILONG ELECTRONIC (JINHUA) CO.,LTD

H0-R-4-014



TYPE HH SEAM SEALED X'TAL

PACKING



HUILONG ELECTRONIC (JINHUA) CO.,LTD