



SOT-23-3L

$V_{(BR)DSS}$	$R_{DS(on)}$ Typ	$I_D @ 25$
-30V	38mΩ@-10V	-4.1A
	50mΩ@-4.5V	



1. Gate
2. Source
3. Drain


Feature

- Advanced Trench Technology
- Excellent $R_{DS(on)}$ and Low Gate Charge performance
- Lead Free

Application

- Load Switch
- Switching circuits
- High-speed line driver
- Power Management Functions

Equivalent Circuit



Absolute Maximum Ratings ($T_A=25^{\circ}\text{C}$ unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	-30	V
Gate-Source Voltage	V_{GS}	±20	V
Continuous Drain Current	I_D	-4.1	A
Pulsed Drain Current (Note 1)	I_{DM}	-16.4	A
Power Dissipation(Note 2)	P_D	1.3	W
Thermal Resistance from Junction to Ambient(Note 2)	$R_{\theta JA}$	90	$^{\circ}\text{C/W}$
Junction Temperature and Storage Temperature	T_J, T_{stg}	-50 ~150	$^{\circ}\text{C}$

Notes:

Stresses exceeding maximum ratings may damage the device.

Maximum Ratings are stress ratings only.

Functional operation above the Recommended Operating Conditions is not implied.

Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

Ta = 25°C unless otherwise specified

Symbol	Parameter	Condition	Min	Typ	Max	Unit
V_{(BR)DSS}	Drain-Source Breakdown Voltage	V_{GS}=0V, I_D=-250μA	-30	--	--	V
I_{DSS}	Drain-Source Leakage Current	V_{DS}=-30V, V_{GS}=0V	--	--	-1	uA
I_{GSS}	Gate-Source Leakage Current	V_{GS}=±20V, V_{DS}=0V	--	--	±100	nA
V_{GS(TH)}	Gate Threshold Voltage	V_{DS}=V_{GS}, I_D=-250μA	-1.2	-1.5	-2.5	V
R_{DS(ON)}	Drain-Source On-State Resistance(Note 3)	V_{GS}=-10V, I_D=-4A	--	38	55	mΩ
		V_{GS}=-4.5V, I_D=-3A	--	50	75	mΩ

Dynamic Electrical Characteristics

Symbol	Parameter	Condition	Min	Typ	Max	Unit
C_{iss}	Input Capacitance	V_{DS}=-15V V_{GS}=0V f=1MHz	--	540	--	pF
C_{oss}	Output Capacitance		--	70	--	pF
C_{rss}	Reverse Transfer Capacitance		--	55	--	pF
Q_g	Total Gate Charge	V_{DS}=-15V V_{GS}=-10V I_D=-2A	--	10	--	nC
Q_{gs}	Gate Source Charge		--	2.1	--	nC
Q_{gd}	Gate Drain Charge		--	2.7	--	nC

Switching Characteristics

Symbol	Parameter	Condition	Min	Typ	Max	Unit
t_{d(on)}	Turn on Delay Time	V_{DS}=-15V V_{GS}=-10V I_D=-2A R_G=3Ω	--	3	--	ns
t_r	Turn on Rise Time		--	2.8	--	ns
t_{d(off)}	Turn Off Delay Time		--	25	--	ns
t_f	Turn Off Fall Time		--	13	--	ns

Source Drain Diode Characteristics

Symbol	Parameter	Condition	Min	Typ	Max	Unit
I_S	Maximum Continuous Drain to Source Diode Forward Current	T_A=25°C	--	--	-4.1	A
V_{SD}	Drain-Source Diode Forward Voltage	I_S=-1A, V_{GS}=0V	--	-0.8	-1.2	V

Notes:

- 1.Pulse width limited by maximum allowable junction temperature
- 2.The value of P_D&R_{θJA} is measured with the device mounted on 1 in² FR-4 board with 2oz.Copper, double sided, in a still air environment with Ta=25°C.
- 3.Pulse test ; Pulse width≤300us, duty cycles≤2%

Typical Characteristics




Fig1. Typical Output Characteristics




Fig2. Normalized Threshold Voltage Vs. Temperature




Fig3. Typical Transfer Characteristics




Fig4. On-Resistance vs. Drain Current and Gate




Fig5. Typical Source-Drain Diode Forward Voltage




Fig6. Maximum Safe Operating Area

Typical Characteristics




Fig7. Typical Capacitance Vs. Drain-Source Voltage




Fig8. Typical Gate Charge Vs. Gate-Source Voltage




Fig9. Normalized Maximum Transient Thermal Impedance





Fig10. Switching Time Test Circuit and waveforms


Outlitne Drawing

SOT-23-3L Package Outline Dimensions



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
c	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E1	1.500	1.700	0.059	0.067
E	2.650	2.950	0.104	0.116
e	0.950(BSC)		0.037(BSC)	
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°

Suggested Pad Layout



Note:

1. Controlling dimension: in/millimeters.
2. General tolerance: $\pm 0.05\text{mm}$.
3. The pad layout is for reference purposes only.

Important Notice and Disclaimer

Microdiode Electronics (Shenzhen) reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

Microdiode Electronics (Shenzhen) makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Microdiode Electronics (Shenzhen) assume any liability for application assistance or customer product design. Microdiode Electronics (Shenzhen) does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of Microdiode Electronics (Shenzhen). Microdiode Electronics (Shenzhen) products are not authorized for use as critical components in life support devices or systems without express written approval of Microdiode Electronics (Shenzhen).