



汇 隆 电 子 (金 华) 有 限 公 司
HUILONG ELECTRONIC (JINHUA) CO.,LTD

SPECIFICATION FOR APPROVAL

CUSTOMER

NOMINAL FREQUENCY

24.000000 MHz

HOLDER TYPE

3225

SPEC. NO. (P/N)

HL24000183

CUSTOMER P/N

ISSUE DATE

Dec.15,2021

APPROVED	PREPARED	QA
		
APPROVED BY CUSTOMER :		AVL Status
Please return one copy with approval to HLC		

浙江省金华市经济开发区工业园区秋涛北街399号
No.399 Qiutao North Str.,Industrial Area,Economic
Development Zone,Jinhua,Zhejiang,China
TEL: 0086-579-82273331
FAX: 0086-579-82273198
<http://www.cn-hlc.com>



RoHS Compliant (Pb- Free)



TYPE HL SEAM SEALED X'TAL

ELECTRICAL SPECIFICATIONS

HLC Parts Number : HL24000183

Item	Symbol	Specifications				Notes
		Min	Type	Max	Units	
Nominal frequency	FO	24.000000			MHz	
Mode of Oscillation	OT	Fundamental				
Load Capacitance	LC	12			pF	
Frequency Tolerance	FT	± 10			ppm	at 25°C $\pm 3^{\circ}\text{C}$
Frequency Stability		± 20			ppm	with working temperature Reference to 25°C
Working temperature range	TR	-20~70			°C	
Drive Level	DL	100			μW	
Series Resonant Resistance RR	CI/RR	30			Ω	Max.
Insulation Resistance	IR	>500			M Ω	
Shunt Capacitance C0	C0	5			pF	Max.
Aging		± 2			ppm/yr.	
Storage temperature range		-40 ~ 105			°C	
Unit Weight					g	

HUILONG ELECTRONIC (JINHUA) CO.,LTD

H0-R-4-014



TYPE HL SEAM SEALED X'TAL

MARKING

HLC

* 24.0xx

HLC: HLC Use Code x: CL Code x: Date Code

CL	Code	CL	Code	CL	Code
0pf	0	7.5pf	H	11.2pf	a
6pf	1	11pf	I	11.4pf	b
8pf	2	8.5pf	J	13.5pf	d
10pf	3	7.1pf	K	20.5pf	e
12pf	5	19pf	L	8.8pf	f
15pf	6	12.5pf	M	17pf	g
16pf	7	27pf	N	4.3pf	h
18pf	8	7.3pf	O		
20pf	9	13pf	P		
22pf	A	11.5pf	Q		
25pf	B	7pf	R		
28pf	C	14pf	S		
30pf	D	23pf	T		
32pf	E	11.1pf	U		
9.5pf	F	33pf	V		
9pf	G	10.5pf	W		
		9.2pf	Y		
		50pf	Z		

Jan-21	N	Jan-22	A
Feb-21	P	Feb-22	B
Mar-21	Q	Mar-22	C
Apr-21	R	Apr-22	D
May-21	S	May-22	E
Jun-21	T	Jun-22	F
Jul-21	U	Jul-22	G
Aug-21	V	Aug-22	H
Sep-21	W	Sep-22	J
Oct-21	X	Oct-22	K
Nov-21	Y	Nov-22	L
Dec-21	Z	Dec-22	M

备注：年份印字代码原则按奇偶年两年一个循环

HUILONG ELECTRONIC (JINHUA) CO.,LTD


H0-R-4-014



TYPE HL SEAM SEALED X'TAL

RELIABILITY SPECIFICATIONS






NO.	TEST ITEM	TEST METHODS
1	DROP TEST	Device are dropped from a height of 150 cm onto 2 mm thickness stainless plate executing 3 times of random drops.
2	MECHANICAL SHOCK	Device are shocked to half sine wave (1000 G) three mutually perpendicular axes each 3 times.
3	VIBRATION	Frequency range 10 ~ 2000 Hz Amplitude 1.5 mm Sweep Time 20 minute Test Time 2 hours
4	SOLDERABILITY	MIL - STD - 20E Method 208C Temperature 245°C ± 5°C Material H63A (Silver 2 ~ 3 %) Immersion depth 0.5 mm minimum Immersion time 3 ± 0.5 seconds Flux Rosin resin methyl alcohol solvent (1 : 4)
5	RESISTANCE TO SOLDERING HEAT	MIL - SLD -202, Method 210, Condition I or J 10 sec immersion into 260 ± 5°C solder pot, above 180°C is 90 ~ 120 sec.
6	LOW TEMP. STORAGE	Leave at - 55 °C ± 2°C for 1000 ± 12 hours
7	HIGH TEMP. STORAGE	Leave at 125 °C ± 2°C for 1000 ± 12 hours
8	THERMAL SHOCK	Total 100 cycles of the following temperature cycle





TYPE HL SEAM SEALED X'TAL

DIMENSIONS




1	Quartz Blank
2	Electrode
3	Lid
4	Base
5	Conductive adhesive






TYPE HL SEAM SEALED X'TAL

SUGGESTED IR REFLOW PROFILE



Total Time : 200 Sec.Max
Solder melting point : 185°C

PACKING



1. 230mm minimum leader which consist of carrier and/or tape followed by a minimum of 160mm of empty carrier tape sealed with cover tape.
2. 160mm minimum trailer of empty carrier tape sealed with cover tape.





HUILONG ELECTRONIC (JINHUA) CO.,LTD

H0-R-4-014



TYPE HL SEAM SEALED X'TAL

PACKING



HUILONG ELECTRONIC (JINHUA) CO.,LTD