



汇隆电子(金华)有限公司
HUILONG ELECTRONIC (JINHUA) CO.,LTD

SPECIFICATION FOR APPROVAL

CUSTOMER _____

NOMINAL FREQUENCY 10.000000 MHz

HOLDER TYPE HC-49US

SPEC. NO. (P/N) HA10000A002

CUSTOMER P/N _____

ISSUE DATE Sep.30,2022

APPROVED	PREPARED	QA
彭达梅	金文波	訾红华
APPROVED BY CUSTOMER:		AVL Status
Please return one copy with approval to HLC		

浙江省金华市经济开发区工业园区秋涛北街399号
No.399 Qiutao North Str.,Industrial Area,Economic
Development Zone,Jinhua,Zhejiang,China
TEL: 0086-579-82273331
FAX: 0086-579-82273198
<http://www.cn-hlc.com>



RoHS Compliant (Pb- Free)



TYPE HL SEAM SEALED X'TAL

ELECTRICAL SPECIFICATIONS

HLC Parts Number : HA10000A002

Item	Symbol	Specifications				Notes
		Min	Type	Max	Units	
Nominal frequency	FO	10.000000			MHz	
Mode of Oscillation	OT	Fundamental				
Load Capacitance	LC	20			pF	
Frequency Tolerance	FT	± 20			ppm	at 25°C $\pm 3^\circ\text{C}$
Frequency Stability		± 20			ppm	with working temperature Reference to 25°C frequency
Working temperature range	TR	-40~85			°C	
Drive Level	DL	100			μW	
Series Resonant Resistance RR	CI/RR	60			Ω	Max.
Shunt Capacitance C0	C0	7			pF	Max.
Aging		± 3			ppm/yr.	
Storage temperature range		-50 ~ 105			°C	
Unit Weight					g	

HUILONG ELECTRONIC (JINHUA) CO.,LTD



TYPE HL SEAM SEALED X'TAL

MARKING



HLC: HLC Use Code x: CL Code

x: Date Code

CL	Code	CL	Code	CL	Code
0pf	0	7.5pf	H	11.2pf	a
6pf	1	11pf	I	11.4pf	b
8pf	2	8.5pf	J	13.5pf	d
10pf	3	7.1pf	K		
12pf	5	19pf	L		
15pf	6	12.5pf	M		
16pf	7	27pf	N		
18pf	8	7.3pf	O		
20pf	9	13pf	P		
22pf	A	11.5pf	Q		
25pf	B	7pf	R		
28pf	C	14pf	S		
30pf	D	23pf	T		
32pf	E	11.1pf	U		
9.5pf	F	33pf	V		
9pf	G	10.5pf	W		
		9.2pf	Y		
		50pf	Z		

Jan-21	N	Jan-22	A
Feb-21	P	Feb-22	B
Mar-21	Q	Mar-22	C
Apr-21	R	Apr-22	D
May-21	S	May-22	E
Jun-21	T	Jun-22	F
Jul-21	U	Jul-22	G
Aug-21	V	Aug-22	H
Sep-21	W	Sep-22	J
Oct-21	X	Oct-22	K
Nov-21	Y	Nov-22	L
Dec-21	Z	Dec-22	M

备注：年份印字代码原则按奇偶年两年一个循环


HUILONG ELECTRONIC (JINHUA) CO.,LTD



TYPE HL SEAM SEALED X'TAL

RELIABILITY SPECIFICATIONS

NO.	TEST ITEM	TEST METHODS
1	DROP TEST	Device are dropped from a height of 75 cm onto 3 mm thick wood to perform 3 times of random drops.
2	MECHANICAL SHOCK	Device are shocked to half sine wave (1000 G) three mutually perpendicular axes each 3 times.
3	VIBRATION	Frequency range 10 ~ 2000 Hz Amplitude 1.5 mm Sweep Time 20 minute Test Time 2 hours
4	SOLDERABILITY	MIL - STD - 20E Method 208C Temperature 245°C±5°C Material H63A (Silver 2 ~ 3 %) Immersion depth 0.5 mm minimum Immersion time 3 ± 0.5 seconds Flux Rosin resin methyl alcohol solvent (1 : 4)
5	RESISTANCE TO SOLDERING HEAT	MIL - SLD -202, Method 210, Condition I or J 10 sec immersion into 260 ± 5°C solder pot, above 180°C is 90 ~ 120 sec.
6	LOW TEMP. STORAGE	Leave at - 55 °C ± 2°C for 1000 ± 12 hours
7	HIGH TEMP. STORAGE	Leave at 125 °C ± 2°C for 1000 ± 12 hours
8	THERMAL SHOCK	Total 100 cycles of the following temperature cycle




HUILONG ELECTRONIC (JINHUA) CO.,LTD




TYPE HL SEAM SEALED X'TAL

DIMENSIONS



Inner structure




HUILONG ELECTRONIC (JINHUA) CO.,LTD



TYPE HL SEAM SEALED X'TAL

SUGGESTED IR REFLOW PROFILE



Total Time: 200 Sec.Max


Solder melting point : 185°C

HUILONG ELECTRONIC (JINHUA) CO.,LTD



TYPE HL SEAM SEALED X'TAL

PACKING



Packing quantity: 1000pcs per box and 10 000pcs per container .

HUILONG ELECTRONIC (JINHUA) CO.,LTD