

MDD3080

30V N-Channel Enhancement Mode POWER MOSFET

1. Description

This N-Channel MOSFET is produced using MDD's advanced Power Trench technology. This process has been optimized to minimize on-state resistance and yet maintain superior switching performance with best in class soft body diode.

2. Features

- Max $R_{DS(on)}$ = 4.4m Ω at V_{GS} = 10 V, I_D = 30 A
- Extremely Low Reverse Recovery Charge, Q_g
- 100% UIS Tested
- RoHS Compliant

3. Application



- Power Management in Telecom., Industrial Automation
- Motor Drives and Uninterruptible Power Supplies
- Current Switching in DC/DC&AC/DC(SR) Sub-systems

4. Absolute Maximum Ratings ($T_A=25^{\circ}\text{C}$ unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	30	V
Gate-Source Voltage	V_{GS}	± 20	V
Continuous Drain Current (Note 1)	I_D	80	A
Single Pulsed Avalanche Energy (Note 3)	E_{AS}	247	mJ
Thermal Resistance, steady-state	$R_{\theta JA}$	65	$^{\circ}\text{C}/\text{W}$
Power Dissipation	P_D	83	W
Junction Temperature	T_J	-55~+150	$^{\circ}\text{C}$
Storage Temperature	T_{stg}	-55~+150	$^{\circ}\text{C}$

Note: 1) Calculated continuous current based on maximum allowable junction temperature.
2) Repetitive rating, pulse width limited by max. junction temperature.
3) E_{AS} condition : $T_J=25^{\circ}\text{C}$, $V_{DD}=15\text{V}$, $V_{GS}=10\text{V}$, $L=0.5\text{mH}$, $R_g=25\Omega$, $I_{AS}=17\text{A}$.

5. Pinning information

Pin	Symbol	Description	Simplified outline	Equivalent Circuit	Marking	Package
1	G	Gate			MDD 3080 XXY: Date code	TO-252
2	D	Drain				
3	S	Source				

6. $T_A=25^{\circ}\text{C}$ unless otherwise specified

Symbol	Parameter		Condition	Min	Typ	Max	Unit
$V_{(BR)DSS}$	Drain-Source Breakdown Voltage		$V_{GS}=0V, I_D=250\mu A$	30	—	—	V
I_{SS}	Gate-Source Leakage Current	Forward	$V_{GS}=20V$	—	—	100	nA
		Reverse	$V_{GS}=-20V$	—	—	-100	nA
I_{DSS}	Drain-Source Leakage Current		$V_{DS}=30V, V_{GS}=0V$	—	—	1	μA
$V_{GS(TH)}$	Gate Threshold Voltage		$V_{DS}=V_{GS}, I_D=250\mu A$	1.2	1.55	2.2	V
$R_{DS(ON)}$	Drain-Source On-State Resistance		$V_{GS}=10V, I_D=30A$	—	3.5	4.4	m Ω
			$V_{GS}=4.5V, I_D=20A$	—	4.8	7.4	m Ω

7. Dynamic Electrical Characteristics

Symbol	Parameter	Condition	Min	Typ	Max	Unit
C_{iss}	Input Capacitance	$V_{GS}=0V$ $V_{DS}=20V$ $f=1MHz$	—	2330	—	pF
C_{oss}	Output Capacitance		—	280	—	pF
C_{rss}	Reverse Transfer Capacitance		—	245	—	pF
Q_g	Total Gate Charge	$V_{GS}=0$ to 10V $V_{DS}=20V$ $I_D=20A$	—	48	—	nC
Q_{gs}	Gate Source Charge		—	10	—	nC
Q_{gd}	Gate Drain Charge		—	10	—	nC

8. Switching Characteristics

Symbol	Parameter	Condition	Min	Typ	Max	Unit
$t_{d(on)}$	Turn on Delay Time	$V_{GS}=10V$ $V_{DD}=20V$ $I_D=20A$ $R_G=3\Omega$	—	10	—	ns
t_r	Turn on Rise Time		—	28	—	ns
$t_{d(off)}$	Turn Off Delay Time		—	40	—	ns
t_f	Turn Off Fall Time		—	7	—	ns

9. Source Drain Diode Characteristics

Symbol	Parameter	Condition	Min	Typ	Max	Unit
V_{SD}	Drain-Source Diode Forward Voltage	$I_S=30A, V_{GS}=0V$	—	0.8	1.2	V
t_{rr}	Body Diode Reverse Recovery Time	$I_F=20A$ $di/dt=100A/\mu s$	—	11	—	ns
Q_{rr}	Body Diode Reverse Recovery Charge		—	5	—	nC

10. Test Circuits And Waveforms




Figure 1. Gate charge test circuit & waveform





Figure 2. Switching time test circuit & waveforms





Figure 3. Unclamped inductive switching (UIS) test circuit & waveforms






Figure 4. Diode reverse recovery test circuit & waveforms



11. Electrical Characteristics Diagrams




Figure 1. Typ. output characteristics




Figure 2. Typ. transfer characteristics




Figure 3. On-Resistance vs. Drain Current




Figure 4. Gate Charge Characteristics




Figure 5. Normalized on Resistance vs. Junction Temperature





Figure 6. Forward characteristic of body diode

12. Outline Drawing

TO-252 Package Outline Dimensions



TO-252(D-PAK) mechanical data

UNIT		A	B	b	C	D	E	F	G	H	L	L1	L2	L3	S	M	N	J	K	T
mm	max	6.7	5.5	0.8	2.5	6.3	0.6	1.8	2.29	0.55	3.1	1.2	1.0	1.75	0.1	1.8	1.3	3.16	1.80	4.83
	min	6.3	5.1	0.3	2.1	5.9	0.4	1.3	TYPICAL	0.45	2.7	0.8	0.6	1.40	0.0	TYPICAL	TYPICAL	ref.	ref.	ref.
mil	max	264	217	31	98	248	24	71	90	22	122	47	39	69	4	71	51	124	71	190
	min	248	201	12	83	232	16	51	TYPICAL	18	106	31	24	55	0	TYPICAL	TYPICAL	ref.	ref.	ref.

13. Important Notice and Disclaimer

Microdiode Electronics (Shenzhen) reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

Microdiode Electronics (Shenzhen) makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Microdiode Electronics (Shenzhen) assume any liability for application assistance or customer product design. Microdiode Electronics (Shenzhen) does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of Microdiode Electronics (Shenzhen).

Microdiode Electronics (Shenzhen) products are not authorized for use as critical components in life support devices or systems without express written approval of Microdiode Electronics (Shenzhen).