



汇隆电子(金华)有限公司
HUILONG ELECTRONIC (JINHUA) CO.,LTD

SPECIFICATION FOR APPROVAL

CUSTOMER _____

NOMINAL FREQUENCY _____ 25.000625 MHz _____

HOLDER TYPE _____ HC-49US _____

SPEC. NO. (P/N) _____ HA25625G002 _____

CUSTOMER P/N _____

ISSUE DATE _____ Mar.6,2018 _____

APPROVED	PREPARED	QA
彭达梅	金文波	陈全根
APPROVED BY CUSTOMER :		AVL Status
Please return one copy with approval toHLC		

浙江省金华市经济开发区工业园区秋涛北街399号

No.399 Qiutao North Str.,Industrial Area,Economic Development Zone,Jinhua,Zhejiang,China

TEL: 0086-579-82273331

FAX: 0086-579-82273198

<http://www.cn-hlc.com>



ISO9001
ISO14001



RoHS Compliant (Pb- Free)



TYPE HL SEAM SEALED X'TAL

ELECTRICAL SPECIFICATIONS

HLC Parts Number : HA25625G002

Item	Symbol	Specifications				Notes
		Min	Type	Max	Units	
Nominal frequency	FO	25.000625			MHz	
Mode of Oscillation	OT	Fundamental				
Load Capacitance	LC	20			pF	
Frequency Tolerance	FT	± 10			ppm	at 25°C $\pm 3^{\circ}\text{C}$
Frequency Stability		± 20			ppm	with working temperature Reference to 25°C
Working temperature range	TR	-40~85			°C	
Drive Level	DL	100			μW	
Series Resonant Resistance R _s	CI/RR	30			Ω	Max.
Shunt Capacitance C ₀	C ₀	7			pF	
Aging		± 5			ppm/yr.	
Storage temperature range		-50 ~ 105			°C	
Unit Weight					g	



TYPE HL SEAM SEALED X'TAL

MARKING



HLC: HLC Use Code x: CL Code

x: Date Code

CL	Code	CL	Code
0pf	0	9pf	G
6pf	1	7.5pf	H
8pf	2	11pf	I
10pf	3	8.5pf	J
12pf	5	7.1pf	K
15pf	6	19pf	L
16pf	7	12.5pf	M
18pf	8	27pf	N
20pf	9	7.3pf	O
22pf	A	13pf	P
25pf	B	11.5pf	Q
28pf	C	7pf	R
30pf	D	14pf	S
32pf	E	23pf	T
9.5pf	F	11.1pf	U
		33pf	V
		10.5pf	W
		9.2pf	Y

Jan-17	N	Jan-16	A
Feb-17	P	Feb-16	B
Mar-17	Q	Mar-16	C
Apr-17	R	Apr-16	D
May-17	S	May-16	E
Jun-17	T	Jun-16	F
Jul-17	U	Jul-16	G
Aug-17	V	Aug-16	H
Sep-17	W	Sep-16	J
Oct-17	X	Oct-16	K
Nov-17	Y	Nov-16	L
Dec-17	Z	Dec-16	M


备注：年份印字代码原则按奇偶年两年一个循环



TYPE HL SEAM SEALED X'TAL

RELIABILITY SPECIFICATIONS


NO.	TEST ITEM	TEST METHODS
1	DROP TEST	Device are dropped from a height of 75 cm onto 3 mm thick wood to perform 3 times of random drops.
2	MECHANICAL SHOCK	Device are shocked to half sine wave (1000 G) three mutually perpendicular axes each 3 times.
3	VIBRATION	Frequency range 10 ~ 2000 Hz Amplitude 1.5 mm Sweep Time 20 minute Test Time 2 hours
4	SOLDERABILITY	MIL - STD - 20E Method 208C Temperature $245^{\circ}\text{C} \pm 5^{\circ}\text{C}$ Material H63A (Silver 2 ~ 3 %) Immersion depth 0.5 mm minimum Immersion time 3 ± 0.5 seconds Flux Rosin resin methyl alcohol solvent (1 : 4)
5	RESISTANCE TO SOLDERING HEAT	MIL - SLD -202, Method 210, Condition I or J 10 sec immersion into $260 \pm 5^{\circ}\text{C}$ solder pot, above 180°C is 90 ~ 120 sec.
6	LOW TEMP. STORAGE	Leave at $-55^{\circ}\text{C} \pm 2^{\circ}\text{C}$ for 1000 ± 12 hours
7	HIGH TEMP. STORAGE	Leave at $125^{\circ}\text{C} \pm 2^{\circ}\text{C}$ for 1000 ± 12 hours
8	THERMAL SHOCK	Total 100 cycles of the following temperature cycle






TYPE HL SEAM SEALED X'TAL

DIMENSIONS




Inner structure





TYPE HL SEAM SEALED X'TAL

SUGGESTED IR REFLOW PROFILE




Total Time : 200 Sec.Max

Solder melting point : 185°C



TYPE HL SEAM SEALED X'TAL

PACKING



Packing quantity: 1000pcs per box and 10 000pcs per container .