






RoHS2.0+REACH




加防尘盖示意图



外壳DIP脚长度
(DIM:A=3.00)



SPECIFICATION
MATERIAL
See drawing
STANDARD DATA
Rating current:5A
ELECTRICAL
Insulator resistance:100Mohms Min.
Withstanding voltage:100VAC/minute
Contact resistance:40mohms Max
MECHANICAL
Mating force:5~20N Max.
Unmating force:6~20N Min.
Durability:10000 cycles Min.
DRAWINGS MARKED"⊗"FOR FAI DIMENSION.



RECOMMENDED PCB LAYOUT(t=0.80±0.05)
COMPONENT SIDE(GENERAL TOLERANCE:±0.05)

A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

NO. 序号	PARTS NAME 名称	Q'TY 用量	MATERIAL 材质	FINISH 处理
1	长端子	1SET	C7025 T=0.15MM	半金雾锡1U" Min
2	短端子	1SET		
3	长端子Molding	1PCS	LCP 黑色	BLACK
4	短端子Molding	1PCS		
5	BMI弹片	1PCS	SUS301 T=0.10MM	NI 50μ" Min
6	BMI弹片Molding	1PCS	LCP	BLACK
7	SHELL	1PCS	SUS304 T=0.20MM	NI 50μ" Min
8	卡勾	1PCS	SUS301 T=0.40MM	NI 50μ"min SN 100μ" min

5.0			
4.0			
3.0			
2.0			
1.0			
NO.	DATE	DESCRIPTION	DRAWING

DRAWING:
Frank
CHECKED:
yangjie
APPROVAL:

GENERAL TOLERANCE
.X:=±0.30 .X*:=±2°
.XX:=±0.25 .XX*:=±1°
.XXX:=±0.15 .XXX*:=±0.5°
UNIT: MM PROJECTION:
SCALE: 1:1
SHEET: 1/1

CHIN-BAN
Electronic Technology

DESCRIPTION: TYPE C 16PIN 沉板单排0.95mm 冲压壳DIP脚3.00mm
PART NO: USBC1-AM-063
OLD CODE:
DRAWING NO:
REV: 1.0
SIZE: A4