








RoHS2.0+REACH



SPECIFICATION
MATERIAL
See drawing
STANDARD DATA
Rating current:5A
ELECTRICAL
Insulator resistance:100Mohms Min.
Withstanding voltage:100VAC/minute
Contact resistance:40mohms Max
MECHANICAL
Mating force:5~20N Max.
Unmating force:6~20N Min.
Durability:10000 cycles Min.
DRAWINGS MARKED "◎" FOR FAI DIMENSION.



A1	GND	B12	GND
A2	SSTXP1	B11	SSRXP1
A3	SSTXN1	B10	SSRXN1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	SSRXN2	B3	SSTXN2
A11	SSRXP2	B2	SSTXP2
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

NO. 序号	PARTS NAME 名称	Q'TY 用量	MATERIAL 材质	FINISH 处理
1	长端子	1SET	C7025 T=0.15MM	半金雾锡1U" Min
2	短端子	1SET		
3	长端子Molding	1PCS	LCP 黑色	BLACK
4	短端子Molding	1PCS		
5	BMT弹片	1PCS	SUS301 T=0.10MM	Ni 50μ" Min
6	BMT弹片Molding	1PCS	LCP	BLACK
7	SHELL	1PCS	SUS304 T=0.20MM	Ni 50μ" Min
8	卡勾	1PCS	SUS301 T=0.40MM	Ni 50u"min SN 100u" min

5.0				DRAWING: Frank	GENERAL TOLERANCE .X:=±0.30 .X*:=±2° .XX:=±0.25 .XX*:=±1° .XXX:=±0.15 .XXX*:=±0.5°			
4.0								
3.0				CHECKED: yangjie	UNIT: MM	PROJECTION:	DESCRIPTION: USB TYPE CM 24PIN SMT CONNECTOR	
2.0								
1.0				APPROVAL:	SCALE: 1:1		PART NO: USBC1-AM-064	REV: 1.0
NO.	DATE	DESCRIPTION	DRAWING		SHEET: 1/1		OLD CODE:	DRAWING NO: