





1

2

3

4

A



### 技术要求:

- 1、单位: mm
- 2、线径: 0.4
- 3、材质: 碳钢镀镍-满足ROHS
- 4、样式: 芯网电子SMT贴片弹簧
- 5、工艺: 高温260摄氏度热处理
- 6、未标注公差以在±0.25计
- 7、表面无脏污、无材质不良
- 8、联系电话: 05925216722
- 9、型号: MLF9-9.5-6-0.4N
- 10、盐雾测试: 百分五盐雾测试满足24小时
- 11、包装方式: 一盘600个



C

D

E

F

A



B

C

D

E

F



标识	W	A0	B0	K0	K1	P	碳钢线			厦门市芯网电子 科技有限公司	
尺寸	16.00	6.20	6.20	10.10	--	12.00					
误差	+0.30 -0.30	+0.15 -0.15	+0.15 -0.15	+0.10 -0.10	+0.10 -0.10	+0.10 -0.10	P0	P2	T		
标识	F	E	D0	P0	P2	T	阶段标记			2:1	
尺寸	7.50	1.75	1.50	4.00	2.00	0.40					
误差	+0.10 -0.10	+0.10 -0.10	+0.10 -0.10	+0.10 -0.10	+0.15 -0.15	+0.05 -0.05					

1

2

3

4