


1. 产品尺寸图Product Dimension Drawing



2. 产品电器参数Product electrical parameters

防护等级 (Ingress protection)	IP50
插拔测试 (Plugging and unplugging test)	<500次
产品耐温 (The product is temperature resistant)	-20° C / +85° C
盐雾腐蚀 (Salt Spray Corrosion)	>48 hr
额定电流Current rating	5A
额定电压 (Rated voltage)	125V
工作电压 (AC.V)	200
Operating voltage (AC.V)	
耐电压 (AC.V)	1500
Withstand voltage (AC.V)	
绝缘阻抗 (mΩ) DC500V	1500
Insulation Resistance (mΩ)DC500V	
绝缘电阻 (mΩ) DC1A	5
Insulation Resistance (mΩ)DC1A	

3. 环境及表面处理产品特性Environmental and surface treatment product characteristics

外壳材料 Housing material	锌合金镀镍Zinc alloy nickel plating
绝缘体材料 Insulator material	橡胶黑木Rubber black wood
触体材料 Contact material	黄铜镀银Brass silver-plated

未注公差 tolerances are not noted		TONGRUIJOIN		东莞市通瑞电子科技有限公司					
0~5	±0.10	设计 DESIGNED	名称 PARTNAME	母头 (直式)	材料 MATERIAL		比例 SCALE	1:1	
6~10	±0.15	校对 CHECKED	型号 Model	AD. MT. GX12. 306. NYA	电镀 PLATING		单位 UNIT	mm	
10~50	±0.20	审核 APPROVED	图号 DRAWING NO.		视图 view		版本 REV	A/0	
51~100	±0.25								
100+	±0.25%								