


RoHS2.0+REACH



NOTES:

1. MATERIAL:

1.1 HOUSING:LCP+30% G/F,COLOR:BLACK, UL94V-0;

1.2 CONTACTS: C2680 T=0.25mm

1.3 SHELL SPCC

1.4 ISOLATED:SPCC

2. FINISH:

2.1 CONTACT:

GOLD(SEE TABLE) PLATING ON CONTACT AREA.

100u" MIN. BRIGHT-TIN PLATING ON SOLDER TAIL

AREA,50u" MIN. NICKEL UNDERPLATING OVERALL,

2.2 SHELL:

80u" MIN. NICKEL UNDERPLATING.

3. ELECTRICAL CHARACTERISTICS:

CURRENT RATING: 0.5Amper Maximum

VOLTAGE: 30V AC.


CONTACT RETENTION FORCE:0.7KGfMINIMUM.

CONTACT RESISTANCE: 30 MILLIOHMS MAXIMUM.

INSULATION RESISTANCE: 1000MEGOHMS MINIMUM.

DIELECTRIC WITHSTANDING VOLTAGE: 750V AC AT SEE LEVEL.

TEMPERATURE: -55?~85? .



RECOMMENDED PC BOARD LAYOUT
(COMPONENT SIDE VIEW)

5.0				DRAWING:	GENERAL TOLERANCE	CHIN-BAN Electronic Technology	
4.0				Frank	.X:=±0.30 .X':=±2° .XX:=±0.25 .XX':=±1° .XXX:=±0.15 .XXX':=±0.5°		
3.0				CHECKED:	UNIT: MM PROJECTION:		
2.0				yangjie	SCALE: 1:1		
1.0				APPROVAL:	SHEET: 1/1	DESCRIPTION: USB20 AF 双层弯脚有边	
NO.	DATE	DESCRIPTION	DRAWING			PART NO: USB30-AF-010	REV: 1.0
						OLD CODE:	SIZE: A4
						DRAWING NO:	