



H3-TC4-25+

500-2500MHz 50Ω 1:4 Balun


APPLICATIONS

- balanced to unbalanced transformation
- push-pull amplifiers
- PCS/DCS,MMDS

FEATURES

- Surface mount
- Impedance ratio: 1:4
- RoHS compliant and Pb free
- Available on tape and reel

DIMENSIONS




A	B	C
3.81	3.81	4.00 Max
D		
1.27		

Unless otherwise stated dimensions are in mm


Tolerance: .xx ± 0.25, .xxx ± 0.05

Land Pattern



E	F	G
4.83	3.30	1.40
H	J	
0.76	1.27	

FUNCTIONAL SCHEMATIC




Pin Configuration

Pin No.	Function
1	Secondary Dot
2	Secondary CT
3	Secondary
4	Primary Dot
5	Primary


ELECTRICAL SPECIFICATIONS@25°C:

Parameters (P#: ENA PORT)	frequency band	Min.	Typ.	Max.	Unit
Port Impedance, Z0 (P1 / P2 / P3)			50 /100/100		Ohm
Insertion Loss	500-1500MHz		1.7	2.0	dB
	500-2500MHz		2.5	3.0	dB
Amplitude Balance	500-2500MHz		0.5		dB
Phase Balance	500-2500MHz		8.0		Deg

TEST CURVE



APPLICATION & TEST CIRCUIT



RF ports: P1/P2/P3

ABSOLUTE MAXIMUM RATINGS

Parameter	Value
Input Power	250mW Max
DC Current	30mA Max
Operating Temperature Range	-40 to 85°C
Storage Temperature Range	-55 to 100°C

Tel: +86-28-85589664

E-mail: mr_li@henglitaitech.com

Web: www.hltchips.com

Address: No.198 Tianqin East Street, Gaoxin West District, Chengdu City