

东莞市振宝佳电子有限公司
物料承认书
SPECIFICATION FOR APPROVAL

客户名称 CUSTOMER			
客户产品名称 CUSTOMER PART NAME		供应商产品名称 VENDOR PART NAME	
客户规格型号 SPECIFICATION		振宝佳规格型号 SPECIFICATION 供应商产品编码	
客户产品编码 CUSTOMER PART NO.		VENDOR PART NO.	
制作 (PRE.) : 审核 (CHKD BY) : 批准 (APPROVAL BY) :			

客户承认结果 (APPROVAL RESULT) : <input type="checkbox"/> 合格(OK) <input type="checkbox"/> 不合格(NG) <input type="checkbox"/> 其他 (OTHER) : 说明 (REMARK) : 日期: 年 月 日	承办(APPD):
	审核(CHKD BY):
	批准 (APPROVAL BY) :

<p>东莞市振宝佳电子有限公司</p> <p>公司地址: 广东省东莞市塘厦镇128工业区</p> <p>联 系 人: 陈泽生</p> <p>电 话: 0769-87919026/13509243270</p> <p>E--MAIL: zhenbaojia@126.com</p>

●Features

- High rated current
- Frequency up to 3 MHz
- 125℃ maximum total temperature operation
- Low core loss
- Ultra low buzz noise due to molding construction
- Halogen Free & ROHS compliant

●Applications

- Laptops and PCs
- Switch and servers
- Base stations
- DC/DC converters
- Battery powered devices
- SSD modules



● Product Identification

ZBJ TC 322512 -2R2 M T B
 ① ② ③ ④ ⑤ ⑥ ⑦

① Brand code (品牌代码)

② T-core integrated molding (T-CORE一体成型)

③ Specifications and models (规格型号)

④ Inductance value (感值)

R22=0.22UH 3R3=3.3UH 100=10UH 101=100UH


⑤ Inductance Tolerance N=±30% M=±20% K=±10%

⑥ Packaging (包装) T:编带整盘 B:散装


⑦ Coating color B=Black G=Gray

● Dimensions (unit:mm)

Outline Dimensions



PCB Pattern



Series	L	G	W	E	T	A	B	C
322512	3.2+0.2	1.0±0.2	2.5+0.2	1.05±0.2	1.20Max	3.20	0.90	2.50

●Electrical characteristics



P/N	L0(μH) @ (0A) 1MHz	Rdc(mΩ)		Heat rating current Irms(A)		Saturation current Isat(A)	
		Typical	Max	Typical	Max	Typical	Max
ZBJTC322512-R10MT	0.10	5.2	7.0	12.0	11.0	18.0	16.5
ZBJTC322512-R22MT	0.22	6.6	10	9.2	8.7	11.5	11
ZBJTC322512-R24MT	0.24	7.0	12	9.0	8.5	11	10.5
ZBJTC322512-R33MT	0.33	9.0	14	8.4	8.1	10	9.5
ZBJTC322512-R47MT	0.47	14	19	7.5	7.2	8.6	8.2
ZBJTC322512-R68MT	0.68	18	23	7.3	6.8	8.1	7.7
ZBJTC322512-1R0MT	1.0	26	30	5.3	4.8	6.6	5.8
ZBJTC322512-1R5MT	1.5	37	44	4.7	4.3	5.1	4.7
ZBJTC322512-2R2MT	2.2	58	70	3.6	3.0	4.6	4.2
ZBJTC322512-3R3MT	3.3	75	95	2.9	2.5	3.7	3.2
ZBJTC322512-4R7MT	4.7	115	135	2.3	2.0	2.9	2.6
ZBJTC322512-6R8MT	6.8	177	210	2.1	1.9	2.8	2.4
ZBJTC322512-100MT	10.0	210	230	2.2	1.8	2.3	1.9

●Test remarks

- 1、All test data is referenced to 25 °C ambient.
- 2、Test Condition:1MHz, 1.0Vrms.
- 3、Irms:DC current (A) that will cause an approximate ΔT of 40 °C .
- 4、Isat:DC current (A) that will cause L0 to drop approximately 30%.
- 5、Operating Temperature Range -55°C to + 125°C .
- 6、The part temperature (ambient + temp rise) should not exceed 125 under °C the worst case operating conditions. Circuit design, component placement, PCB trace size and thickness, airflow and other cooling provision all affect the part temperature. Part temperature should be verified in the end application.
- 7、The rated current as listed is either the saturation current or the heating current depending on which value is lower.

●Reliability


Item	Specification and Requirement	Test Method								
Solderability	1. No case deformation or change in apperance 2. New solder coverage More than 90%	1.Preheat: 125℃±5℃ ， 60S±2S 2.Tin: lead-free. 3.Temperature:245℃±5℃， flux 3.0S±0.5S.								
Mechanical shock	1. No case deformation or change in apperance 2. ΔL/Lo≦±10%	1. Acceleration: 100G 2. Pulse time:: 6ms 3. 3 times in each positive and negative direction of 3 mutual perpendicular directions								
Mechanical vibration	1. No case deformation or change in apperance 2. ΔL/Lo≦±10%	1. The test samples shall be soldered to the board. Then it shall be submitted to below test conditions. <table><tr><td>Fre. Range</td><td>10~55Hz</td></tr><tr><td>Total Amplitude</td><td>1.5mm</td></tr><tr><td>Sweeping Method</td><td>10Hz to 55Hz to 10Hz</td></tr><tr><td>Time</td><td>For 2 hours on each X,Y,Z axis.</td></tr></table> 2. Recovery: At least 2 hours of recovery underthe standard condition after the test, followed by the measurement within 24 ±2 hours.	Fre. Range	10~55Hz	Total Amplitude	1.5mm	Sweeping Method	10Hz to 55Hz to 10Hz	Time	For 2 hours on each X,Y,Z axis.
Fre. Range	10~55Hz									
Total Amplitude	1.5mm									
Sweeping Method	10Hz to 55Hz to 10Hz									
Time	For 2 hours on each X,Y,Z axis.									
Thermal Shock	Inductance change: Within ± 10% Without distinct damage in appearance	1. First -55℃ for 30 minutes, last 125℃ for 30 minutes as 1 cycle. Go through 1000 cycles. 2. Max transfer time is 2 minutes. 3. Measured at room temperature after placing for 24±2 hours								
Humidity Resistance	Inductance change: Within ± 10% Without distinct damage in appearance	1.Reflow 2 times, 2.85℃,85%RH,1000 hours 3.Measured at room temperature after placing for 24±2 hours								
Low temperature storage	Inductance change: Within ± 10% Without distinct damage in appearance	1. Temperature: -55 ± 2℃ 2. Time: 1000 hours 3. Measured at room temperature after placing for 24±2 hours								

High temperature storage	Inductance change: Within $\pm 10\%$ Without distinct damage in appearance	<ol style="list-style-type: none"> 1. Temperature: $+125 \pm 2^\circ\text{C}$ 2. Time: 1000 hours 3. Measured at room temperature after placing for 24 ± 2 hours
Board Flex	Inductance change: Within $\pm 10\%$ Without distinct damage in appearance	<ol style="list-style-type: none"> 1. Run through IR reflow for 2 times; 2. Place the 100mm X 40mm board into a fixture similar to the one shown in below Figure with the component facing down 3. The apparatus shall consist of mechanical means to apply a force which will bend the board (D) x = 2 mm minimum. 4. The duration of the applied forces shall be 60 ± 5 sec. The force is to be applied only once to the board. 
Terminal Strength	No removal or split of the termination or other defects shall occur.	<ol style="list-style-type: none"> 1. The test samples shall be soldered to the board 2. Push the product vertically from the side of the sample using the thrust tester. 3. Automotive electronics: 17.7N, 60S ± 1s, X, Y direct. 

● Soldering Condition

(This is for recommendation, please customer perform adjustment according to actual application)

Recommend Reflow Soldering Profile : (solder : Sn96.5 / Ag3 / Cu0.5)



Profile Feature	Lead (Pb)-Free solder
Preheat:	
Temperature Min (T _{smin})	150°C
Temperature Max (T _{smax})	200°C
Time (T _{smin} to T _{smax}) (ts)	60 - 120 seconds
Average ramp-up rate: (T _{smax} to T _p)	3°C / second max.
Time maintained above : Temperature (T _L)	217°C
Time (t _L)	60- 150 seconds
Peak Temperature (T _p)	260°C
Time within $\pm 5^{\circ}\text{C}$ of actual peak Temperature (t _p) ²	10 seconds
Ramp-down Rate	6°C/second max.
Time 25°C to Peak Temperature	8minutes max.

Allowed Re-flow times : 2 times


Remark : To avoid discoloration phenomena of chip on terminal electrodes, please use N2 Re-flow furnace .

●Packaging, Storage and Transportation

Tape Carrier Packaging:

Type	Standard Quantity (pcs/reel)
322512	3000

●Dimension of plastic tapping: (Unit: mm)



Series	W	A0	B0	D1	F	K0	P1	T
公差	/	/	/	±0.20	±0.10	/	±0.10	±0.05
322512	8.0±0.10	2.90+0.10/-0.05	3.50+0.10/-0.05	1.0	3.5	1.35±0.10	4.0	0.25

●Peel force of top cover tape

The peel speed shall be about 300mm/minute

The peel force of top cover tape shall be between 0.1 to 1.3 N

Label

- Label on the reel
- Customer's part Number
- Lot Number
- Quantity
- date code
- Shipping Label
- Customer's part Number
- Manufacturer's part Number
- Quantity
- date code

