



产 品 规 格 书

PRODUCT SPECIFICATION

客户名称 CUSTOMER: _____

产品型号 MODEL: HMB1275-05B

客户型号 USER'S MODEL: _____

日 期 DATE: 2019-12-12

江苏华能电子有限公司			客户回签		
HUAWHA			CUSTOMER		
SERVE RATITY			CUSTOMER RATIGY		
拟制	审核	批准	检验	审核	批准
REPORT	CHECKED	APPROVED	TEST	CHECKED	APPROVED
唐华萍	工 程 部 用 章	张长华			

江苏华能电子有限公司
JIANGSU HUAWHA ELECTRONICS CO.,LTD
地址：江苏省泰州市兴化市陈堡镇工业园区
ADD:Chenbao Industrial Park, Chenbao Town, Xinghua,Taizhou City, Jiangsu China.
电话 [TEL:0523-83710666](tel:0523-83710666) 传真 FAX:0523-83724866
网址: www.huawha.com 邮箱: hndz_wwj@huawha.com

1.基本规格/General specification



项目/Item		规格/Spec	条件/Condition
1	额定电压 Rated voltage	5VDC	
2	工作电压 Operation voltage	3~7VDC	
3	声压 Sound Pressure Level=SPL	Min 88dB	测试环境：标准状态，标准驱动电路， 额定电压 测试距离：0.1m Standard State,Standard Drive Circuit. Rated voltage,Distance at 0.1m
4	电流 current	Max30mA	
5	振荡频率 Oscillation frequency	2700±200Hz	
6	工作温度范围 Operating Temperature	-20~+70℃	
7	保存温度范围 Storage temperature	-30~+85℃	
8	外部尺寸 Externals size （mm）	φ 12*H7.5	参阅附图 Refer to the attached drawing
9	重量 Mass	1.8g	
10	材质 Housing Material	PBT	

2.电气和声学测试条件/Electrical And Acoustical Measuring Condition





驱动电路/Recommended Driving Circuit

设置 Recommended Setting


Resonant frequency, 1/2 duty cycle. Square wave.
Signal amplitude should be large enough to saturate the transistor.



3. 可靠性测试/Reliability Test

	项目 ITEM	测试方法 TEST
1	高温试验 High Temperature Test	在 $+80^{\circ}\text{C}\pm 2^{\circ}\text{C}$ 储存温度下存放 96 小时，恢复 2 小时后测试 After being placed in a chamber with $+80\pm 2^{\circ}\text{C}$ for 96 hours and then being placed in normal condition for 2 hours
2	低温试验 Low Temperature Test	在 $-20^{\circ}\text{C}\pm 2^{\circ}\text{C}$ 储存温度下存放 96 小时，恢复 2 小时后测试 After being placed in a chamber with $-20\pm 2^{\circ}\text{C}$ for 96 hours and then being placed in normal condition for 2 hours
3	恒定湿热试验 Humidity Test	
4	温度变化试验 Temperature Cycle Test	
5	振动试验 Vibration Test	
6	跌落试验 Drop Test	70cm 高自由掉落到 40mm 的木板上，每个方向三次 Drop on a hard wood board of 40mm thick, any directions, three times, at the height of 70cm
7	插针的抗拉强度试验 Terminal Strength Pulling Test	插针承受 1.0kg 拉力，负荷时间 5s The force 5 seconds of 1.0kg is applied to each terminal.
8	可焊性试验 Solder ability Test	焊锡温度 $255\pm 5^{\circ}\text{C}$ ，浸润时间为 $3\pm 0.5\text{s}$ ，试验后目测产品情况 Lead terminals are immersed in rosin for 5 seconds and then immersed in solder bath of $255\pm 5^{\circ}\text{C}$ for 3 ± 0.5 seconds.
9	回流焊测试 Soldering Test	


4.尺寸图 Dimension



*Unit: mm; Tolerance: ± 0.3 mm Except Specified

*Housing Material: Black PBT

5.频率响应/Frequency Response



5Vo-p 50% duty Square wave, 10cm

5.包装 picking



QTY:100PCS



QTY:1000PCS



QTY:5000PCS

SIZE:50*42*27cm