





REV.	ECN NO OR DESCRIPTION	REVISED	DATE



SPECIFICATION:

1.ELECTRICAL CHARACTERISTICS:

1.1 CURRENT RATING: VBUS AND GND CONTACTS RATED AT 1.25A/2A PARALLELED FOR A TOTAL OF 5A/8A.

1.2 TEMPERATURE RANGE: -40 °C ~ 85 °C

1.3 CONTACT RESISTANCE: 30 MILLIONHM MAX.

1.4 DIELECTRIC WITHSTANDING VOLTAGE: 100 VAC r.m.s

1.5 INSULATION RESISTANCE: 100 MEGOHMS MIN.

2.MECHANICAL CHARACTERISTICS

2.1 INSERTION FORCE: 5~20N

2.2 EXTRACTION FORCE: Initial:8~20N,ATER TEST 6~20N

2.3 DURABILITY:10,000CYCLES

3. THE SHELL LENTH IS LESS THAN THE MINIMUM


SPECIFIED BY THE USB TYPE C

STANDARD.AS SUCH IS

CANNOT INDENOENDENTLY BE GUARANTEED TO MEET ALL

TYPE C MECHANICAL REQUIREMENTS.

PIN ASSIGNMENT												BLADE	SHELL
A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12		
GND	TX1+	TX1-	VBUS	CC1	D+	D-	SBU1	VBUS	RX2+	RX2-	GND	GND	GND
GND	RX1+	RX1-	VBUS	SBU2	D-	D+	CC2	VBUS	TX2-	TX2+	GND		
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1		



4	MID_PLATE	1 PCS	STAINLESS STEEL	Ni Plated
3	CONTACT	1 SET	COPPER ALLOY	Au & Ni Plated
2	MOLDING HOUSING	1 PCS	PLASTIC	None
1	SHELL	1 PCS	STAINLESS STEEL	Ni Plated
NO.	DESCRIPTION	QTY.	MATERIAL	FINISHED
UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD		
DECIMALS: ANGLES:		TITLE TYPE C 16PIN沉板反板上1.38HCustomer Drawing		
X :±0.25	X :±2°	DWN xiong	PART NO. MC-136-C138L750-A	
X.X :±0.20	X.X :±1°	CHKD lee	SCALE:1:1	UNIT: mm
X.XX :±0.15		APVD wang	SIZE: A4	SHEET:10F 1
CUSTOMER COPY				
		REV: A4		

