










RoHS
Compliant
2011/65/EU



REV.	ECN NO OR DESCRIPTION	REVISED	DATE



SPECIFICATION:

1.ELECTRICAL CHARACTERISTICS:

- 1.1 CURRENT RATING: 5 A
- 1.2 TEMPERATURE RANGE: -40 °C ~ 85 °C
- 1.3 CONTACT RESISTANCE: 30 MILLIONHM MAX.
- 1.4 DIELECTRIC WITHSTANDING VOLTAGE: 100 VAC r.m.s
- 1.5 INSULATION RESISTNACE: 100 MEGOHMS MIN.

2.MECHANICAL CHARACTERISTICS

- 2.1 INSERTION FORCE: 5~20N
- 2.2 EXTRACTION FORCE: Initial:8~20N,ATER TEST 6~20N
- 2.3 DURABILITY:10,000CYCLES

3.THE SHELL LENGTH IS LESS THAN THE
MINIMUM SPECIFIIED BY THE USB
TYPE C STANDARD AS SUCH IS CONNOT
INDENOENDTLY BE GUARANTEED TO MEET
ALL TYPE C MECHANICAL REQUIREMENTS.

PIN ASSIGNMENT												BLADE	SHELL
GND	TX1+	TX1-	VBUS	CC1	D+	D-	SBU1	VBUS	RX2-	RX2+	GND		
GND	RX1+	RX1-	VBUS	SBU2	D-	D+	CC2	VBUS	TX2-	TX2+	GND	GND	GND
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1		

5	OUT_SHELL	1 PCS	STAINLESS STEEL	Ni Plated
4	MID PLATED	1 SET	STAINLESS STEEL	Ni Plated
3	CONTACT 1&2	1 SET	COPPER ALLOY	Au & Ni Plated
2	IM HOUSING	1 PCS	H.T.PLASTIC	None
1	SHELL	1 PCS	STAINLESS STEEL	Ni Plated
NO.	DESCRIPTION	QTY.	MATERIAL	FINISHED

UNLESS OTHERWISE
SPECIFIED TOLERANCES



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

DECIMALS:	ANGLES:	TITLE	TYPE C 24PIN Mid mount 1.6H Customer Drawing
X : ± 0.25	X : $\pm 2^\circ$	DNW	xiong
X.X : ± 0.20	X.X : $\pm 1^\circ$	CHKD	lee
X.XX : ± 0.15		APVD	wang

CUSTOMER COPY