








RoHS
Compliant
2011/65/EU



REV.	ECN NO OR DESCRIPTION	REVISED	DATE

NOTE:

1. MATERIAL:
HOUSING: LCP WITH 30% GF, UL 94V-0, BLACK COLOR.
CONTACTS: PHOSPHOR BRONZE.
BOARDLOCKS: BRASS.
2. FINISH:
CONTACTS: GOLD FLASH PLATED ON CONTACT AREA, [100 μ] MIN..
BRIGHT-TIN ON SOLDER TAIL, WITH ENTIRE CONTACT
UNDERPLATED [50 μ] MIN.. NICKEL.
BOARDLOCKS: [100 μ] MIN. BRIGHT-TIN OVER[50 μ] MIN.
NICKEL ON ENTIRE BOARDLOCK.
3. PART NUMBER DESCRIPTION :



TOLERANCE: ± 0.05 ,
RECOMMENDED PCB LAYOUT
(TOP VIEW)

SATA-002-F22S1BY-A	3.08	2.28	1.80	2.30	05
SATA-002-F22S1BY-B	3.15	2.35	1.70	2.40	04
SATA-002-F22S1BY-C	3.20	2.40	2.30	2.45	03
SATA-002-F22S1BY-D	3.30	2.50	2.30	2.55	02
SATA-002-F22S1BY-E	3.08	2.28	2.30	2.30	01
PART NO.	DIM D	DIM C	DIM B	DIM A	ITEM
P.C.BOARD	CONNECTOR				

UNLESS OTHERWISE
SPECIFIED TOLERANCES



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

DECIMALS:	ANGLES:	TITLE	SATA7+15P H4.2板上SMT下二针2.08针		
X : ± 0.25	X : $\pm 2^\circ$	DWN	xiong	PART NO.	SATA-002-F22S1BY-A
X.X : ± 0.20	X.X : $\pm 1^\circ$	CHKD	lee	SCALE:1:1	UNIT: mm
X.XX : ± 0.10		APVD	wang	SIZE: A4	SHEET:10F 1 REV: A4

CUSTOMER COPY