










REV.	ECN NO OR DESCRIPTION	REVISED	DATE



P.C.B LAYOUT VIEW TOLERANCE ±0.05

SPECIFICATION:

1.ELECTRICAL CHARACTERISTICS:

- 1.1 CURRENT RATING: 5 A
- 1.2 TEMPERATURE RANGE: -40 °C ~ 85 °C
- 1.3 CONTACT RESISTANCE: 30 MILLIONHM MAX.
- 1.4 DIELECTRIC WITHSTANDING VOLTAGE: 100 VAC r.m.s
- 1.5 INSULATION RESISTNACE: 100 MEGOHMS MIN.

2.MECHANICAL CHARACTERISTICS

- 2.1 INSERTION FORCE: 5~20N
- 2.2 EXTRACTION FORCE: Initial:8~20N,ATER TEST 6~20N
- 2.3 DURABILITY:10,000CYCLES

3.THE SHELL LENTH IS LESS THAN THE MINIMUM SPECIFIED BY THE USB TYPE C STANDARD.AS SUCH IS CONNOT INDENOENDENTLY BE GUARANTEED TO MEET ALL TYPE C MECHANICAL REQUIREMENTS.

PIN ASSIGNMENT												BLADE	SHELL
A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12		
GND	TX1+	TX1-	VBUS	CC1	D+	D-	SBU1	VBUS	RX2+	RX2-	GND		
GND	RX1+	RX1-	VBUS	SBU2	D+	D-	CC2	VBUS	TX2+	TX2-	GND	GND	GND
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1		

2	IM HOUSING	1 PCS	HIGH TEM. PLASTIC+COPPER ALLOY +STAINLESS STEEL		TERMINAL Au & Ni Plated
1	SHELL+OUT SHELL	1 PCS	STAINLESS STEEL		Ni Plated
NO.	DESCRIPTION	QTY.	MATERIAL		FINISHED
UNLESS OTHERWISE SPECIFIED TOLERANCES			东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD		
DECIMALS:	ANGLES:		TITLE	TYPE C 16PIN沉板上1.48H壳长3.0漏舌2.45	
X :±0.25	X :±2°		DWN	xiong	PART NO. MC-133-C148L30
X.X :±0.20	X.X :±1°		CHKD	lee	SCALE:1:1 UNIT: mm 
X.XX :±0.15		APVD	wang	SIZE: A4	SHEET:10F 1 REV: A4
CUSTOMER COPY					