










RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm

PIN ASSIGNMENTS

A5	CC1	B12	GND
A9	VBUS	B9	VBUS
A12	GND	B5	CC2
PIN	SIGNAL NAME	PIN	SIGNAL NAME

备注(NOTE):

1 材质:

1.1 胶芯: LCP UL94 V-0

1.2 端子: (C2680, ; 镍底, 镀金0.5U

1.3 外壳: 不锈钢201—表面镀镍40—50U

2. 电气特性:

2.1. 接触区: 接触电阻30mΩ Max,
允许10mΩ变化量, 测试条件: 20mv,
100mA下测量,

2.2. 额定电流: 最大3A

2.3. 额定电压: 5V.

2.4. 耐电电压: 100VAC.

2.5. 绝缘电阻: 至少100兆欧

3. 机械性能:

3.1. 插入力: 0.5—2.0Kg

3.2. 拔出力: 0.8—2.0Kg

3.3. 插拔次数: 5000+.

4. 工作环境: -20℃ to +85℃

MANUFACTURE DWG

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co., LtdUNLESS OTHERWISE
SPECIFIED TOLERANCES

TITLE:

TYPE-C 6PIN板上四脚插板SMT

PAR TYPEC-250-BRP6L68

DECIMALS:

ANGLES:

.X: ±0.30

X.' : ±10'

.XX: ±0.20

X.X' : ±8'

.XXX: ±0.10

X.XX' : ±5'

DWN Lucas

CHKD Ethan

APVD Jacob

SCALE 1:1 UNIT: MM

SIZE: A4

SHEET: 1F1

REV: A