









SPECIFICATIONS:

1. MATERIAL:
1.1 INSULATOR: HIGH TEMPERATURE PLASTIC UL 94 V-0; BLACK
1.2 CONTACT: COPPER ALLOY
1.3 SHELL: STAINLESS STEEL
2. ELECTRICAL CHARACTERISTICS:
2-1. CONTACT RESISTANCE 30mΩ Max.
2-2. DIELECTRIC WITHSTANDING VOLTAGE: 500V AC MIN
2-3. INSULATION RESISTANCE: 100MΩ MIN.
3. Mechanical Characteristics:
3-1. Mating Force: 10-20N
3.2. Extraction Force: 10-20N
3.3. Durability: 5000 Cycles
4. PLATING:
4.1 TERMINAL:
60u" MIN NICKEL ALL OVER
100u" MIN Tin ON SOLDER AREA
1u" Au ON CONTACT AREA
4.2 SHELL: 60u" MIN. NICKEL ALL OVER



REV.	REVISION RECORD	DATE	GENERAL TOLERANCES		SCALE: M	NAME	DATE	PART NO:		
A	NEW REVISION	2021.03.12	LINEAR	ANGLES	APPROVED			广东富盈兴业精密科技实业有限公司		
			0.0±0.30	X° ±5°						
			0.00±0.20	.X° ±3°	DESIGNER			W-US53104-0A00B-C085		
			UNIT: MM							
			SIZE: A4	0.000±0.10	DRAWN			REV: A	SHEET: 1/2	
				.XX° ±2°						

TITLE: USB2.0 AF STD CH=0.65 H3.35 L12.5 DIP 非标超薄