

REV	CONTENT	CHK	DATE
V0.0	CONTENT	YL	22.11.21

Electrical :



- | | | |
|---|----------------|------------------------|
| | UL | IEC |
| 1.Rated Voltage : | 300V | 250V |
| 2.Rated Current : | 8A | 7A |
| 3.Torque Value : | M2 , 1.77Lb.in | M2 , 0.2N.m |
| 4.Wire Range: | 28-16AWG | 0.5-1.5mm ² |
| 5.Stripping Length : | 6-7mm | |
| 6.Withstanding Voltage : | AC1600V/1Min. | |
| 7.Operating Temperature : | -40°C~+105°C | |
| 8.RoHS Compliance | | |
| 9."★" is the key quality control point. | | |

15ETYK - 3.5 - XXP - X X - 00





① ② ③ ④ ⑤ ⑥

- ① Sereies NO. ④ 1 Single Pitch
2 Double Pitch
- ② Pitch ⑤ Color: 1 Grey
2 Blue
3 Black
4 Green
5 Orange
6 Red
7 Transparent
8 Yellow
9 White
- ③ Poles
02 02Contacts
03 03Contacts
...
24 24Contacts

⑥ Customer Request: 00--Standard



SECTION A-A



A	Total Pitch Tolerances									Nominal dimension range									$\perp$		$\div$	$-$ $//$			
	in mm									in mm															
	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	
	0	30	53	70	90	115	150	250	350	0	30	53	70	90	over	115	150	200	250	0	over		0	100	over
	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	10	all	to	to	150
	30	53	70	90	115	150	250	350	500	30	53	70	90	115	150	200	250	320	10				100	150	
	± 0.18	± 0.20	± 0.25	± 0.3	± 0.35	± 0.44	± 0.60	± 0.70	± 0.85	± 0.20	± 0.25	± 0.30	± 0.35	± 0.44	± 0.55	± 0.70	± 0.80	± 0.90	0.2	0.3	0.3	0.2	0.3	0.5	

5	SCREW	XX	P	STEEL	Zn Plated				
4	BLOCK	XX	P	BRASS	Ni Plated				
3	CLAMP	XX	P	PHOSPHOR BRONZE	Ni Plated				
2	COVER	XX	1	PA66 UL94V-0	SEE NOTE				
1	HOUSING	XX	1	PA66 UL94V-0	SEE NOTE				
ITEM	NAME OF PART		NO. OF PART	Q'TY	MATERIAL	NOTE			
DWG.	YL	DATE	22.11.21	SIZE	A4	UNITS	mm	SHEET/OF	1 / 1
CHK.		DATE		SCALE	1:1				
APP.		DATE			NAME				
				15ETYK-3.5-XXP-XX-00					
 拓宜(上海)工控电器设备有限公司 Topone(Shanghai) Industrial Control Electrical Equipment Co., LTD.				DWGNO.		XXXX			