

REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE
A0		NEW	C.W	23.04.12

NOTES1:

UL Standard

- 1.Rated voltage/current : 300V / 8A
- 2.Withstanding voltage : AC1500V/1Min.
- 3.Wire range : 28~16AWG

IEC Standard

1. Pollution degree	2
Overvoltage category	II
Rate impulse voltage(KV)	2.5KV
Rate voltage(V)	250V
Rate current(A)	8A





- 2.Wire diameter range : 0.2~1.0mm²

NOTES2:

- 1.Dimension shall be interpreted per ASME Y14.5-2009
- 2.Pitch : 3.50mm, Poles : N=02~24P
- 3.Stripping length : 10mm
- 4.Operating temperature: -40°C~+105°C
- 5.Undimensioned tolerances:

Pitch range in mm			Nominal dimension range in mm					—	∩	∇
TO	Over 6 TO	Over 10 TO	TO	Over 30 TO	Over 60 TO	Over 100 TO	Over 150 TO	0.1/10		
6	10	24	30	60	100	150			≤	
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2°		

- 5.RoHS Compliance



Ordering Information

JL15EDGKN - 1000A - 350 XX X X 1

- Pitch
350=3.5PH
- No.of pins
2P~24P
- Housing Color
B=Black
G=Green(Convention)
U=Blue
R=Red
W=White
Y=Yellow
O=Orange
E=Grey
- Packing
O=Pe bag
A=Tray
T=Tube

DRAW		SCALE	FIT	JILN ® 东莞市锦凌电子有限公司 DONGGUAN JINLING ELECTRONIC CO.,LTD	
CHECK		UNIT	mm		
APPROVE		SIZE	A4	PART NO.	JL15EDGKN-1000A-350XXXX1
		SHEET	1/1	TITLE:	JL15EDGKN-3.5-1000A-XXP插拔式母座/方形按钮
		PROJ.			