


Features

- 0.8 μ A Current at no Load(TYP.)
- $\pm 2\%$ Output Accuracy
- 300mA Output Current
- Compact package:
SOT353 & SOT23-5 & SOT23-3L


Applications

- Portable consumer equipments
- Radio control systems
- Wireless Communication Equipments
- Ultra Low Power Micro controller


PIN CONFIGURATION



SOT353



SOT23-5



SOT23-3L

Pin Number			Pin Name	Pin Function
SOT353	SOT23-5	SOT23-3L		
1	1	3	V _{IN}	Power Input Pin
2	2	1	GND	Ground
3	3	--	EN	Chip Enable Pin
4	4	--	NC	No Internal Connection
5	5	2	V _{OUT}	Output Pin

Ordering Information

TPAP2125X-X.X TRG1

PACKAGE TYPE
N:SOT23
K:SOT23-5
KS:SOT353

OUTPUT VOLTAGE

1.2: 1.2V 1.5: 1.5V
1.8: 1.8V 2.5: 2.5V
2.8: 2.8V 3.0: 3.0V
3.3: 3.3V 3.6: 3.6V

Example: TPAP2125K-3.3TR1G


→ 3.3V Version, in SOT23-5 Package & Tape & Reel Packing Type

Absolute Maximum Ratings


over operating free-air temperature range (unless otherwise noted)

		MIN	MAX	UNIT
VIN	Continuous input voltage range	-0.3	7	V
VOUT	Output voltage range	-0.3	VIN+0.3	
Current	Maximum output current	Internally limited		mA
Temperature	Operating Temperature, Topr	-40	+85	°C
	Storage, Tstg	-40	+150	
	Welding temperature and time, Tsolder		+260, 10s	
Power Dissipation	Pd DFN1X1-4	400		mW
	Pd SOT23-5	300		
	Pd SOT23-3L	250		

BLOCK DIAGRAM



Typical Application Circuit









Electrical Characteristics (TA=25°C, unless otherwise specified)

PARAMETER	SYMBOL	CONDITIONS	MIN.	TYP.	MAX.	UNITS
Input Voltage	V_{IN}	--	1.8	--	7.0	V
Output Voltage	V_{OUT}	--	1.2	--	3.6	V
DC Output Accuracy	--	$I_{OUT}=1mA$	-2	--	2	%
Output Current	I_{OUT}	$V_{IN}=1.8V$	150	--	--	mA
		$V_{IN}=4.3V$	350	--	--	
Dropout Voltage	$V_{dif}^{(2)}$	$I_{OUT}=100mA, V_{OUT}=3.0V$	--	110	--	mV
Supply Current	I_{SS}	$I_{OUT}=0$	0.45	0.8	1.3	μA
Standby Current	I_{STBY}	$CE=V_{SS}$	--	--	0.1	μA
Load Regulation	ΔV_{OUT}	$V_{IN}=V_{OUT}+1V$ $1mA \leq I_{OUT} \leq 100mA$	--	5	--	mV
Line Regulation	$\frac{\Delta V_{OUT}}{V_{OUT} \times \Delta V_{IN}}$	$I_{OUT}=10mA$ $V_{OUT}+1V \leq V_{IN} \leq 6V$	--	0.03	0.2	%/V
Temperature Coefficient	$\frac{\Delta V_{OUT}}{V_{OUT} \times \Delta T_A}$	$I_{OUT}=10mA$ $-40^\circ C < T_A < 85^\circ C$	--	50	--	ppm
Output Current Limit	I_{LIM}	$V_{OUT}=90\% \times V_{OUT}$ ($V_{OUT} \geq 3.0V$)	350	--	--	mA
Short Current	I_{SHORT}	$V_{OUT}=V_{SS}$	--	10	--	mA
Power Supply Rejection Ratio	PSRR	$I_{OUT}=50mA$	100Hz	--	65	dB
			1kHz	--	70	
			10kHz	--	50	
			100kHz	--	35	
CE "High" Voltage	$V_{CE}^{"H"}$	--	1.5	--	V_{IN}	V
CE "Low" Voltage	$V_{CE}^{"L"}$	--	--	--	0.3	V
COUT Auto-Discharge Resistance	$R_{DISCHRG}$	$V_{IN}=5V, V_{OUT}=3.0V$ $V_{CE}=V_{SS}$	--	200	--	Ω







Note:

- Test condition: the device is mounted on FR-4 substrate PC board, with minimum recommended pad layout.
- V_{dif} : The Difference Of Output Voltage And Input Voltage When Input Voltage Is Decreased Gradually Till Output Voltage Equals To 98% Of V_{OUT} .

Typical Operating Characteristics (25 °C, unless otherwise noted)




Typical Operating Characteristics (25 °C, unless otherwise noted)




Package Outline Dimensions (unit: mm)

SOT23-5




Mounting Pad Layout (unit: mm)




Package Outline Dimensions (unit: mm)

SOT23-3L




Mounting Pad Layout (unit: mm)



Package information (Unit: mm)

SOT353



Mounting Pad Layout (unit: mm)

