


產品編碼 P/N	PSPMAA0412~2213 Series	測試設備 TEST INSTRUMENT	Chroma 3302 16502
產品系列 Series	一体成型电感	測試頻率 TEST FREQUENCY	100KHZ/1V

封裝尺寸
Dimension (mm)



系列	封裝尺寸 Dimension					焊盤尺寸 Land Pattern		
Series	A	B	C	D	E	a	b	c
0503	5.2±0.3	5.4±0.3	3.0MAX	2.2±0.3	1.2±0.3	2.5Typ	1.8Typ	4Typ

0503 Series

產品編碼 P/N	@ 25 °C Ambient Temperture					
	感值	公差	DCR		溫升電流 (IRMS)	飽和電流 (ISAT)
	Inductance	Tolerance	mΩ		A	A
	μH	±	Typ	Max	ΔT≈40℃	L0 drop≈30%
PSPMAA0503-R33M-ANP	0.33	20%	4.2	5.0	14.0	18.0
PSPMAA0503-R47M-ANP	0.47	20%	7.4	7.4	12.0	16.0
PSPMAA0503-R68M-ANP	0.68	20%	11.0	13.0	8.0	14.0
PSPMAA0503-1R0M-ANP	1.00	20%	13.0	15.0	7.0	11.0
PSPMAA0503-1R5M-ANP	1.50	20%	20.0	25.0	6.0	8.5
PSPMAA0503-2R2M-ANP	2.20	20%	25.0	35.0	5.5	7.5
PSPMAA0503-3R3M-ANP	3.30	20%	32.0	38.0	5.0	6.0
PSPMAA0503-4R7M-ANP	4.70	20%	50.0	70.0	4.0	5.0
PSPMAA0503-6R8M-ANP	6.80	20%	75.0	100.0	3.5	4.0
PSPMAA0503-8R2M-ANP	8.20	20%	100.0	130.0	3.0	4.0
PSPMAA0503-100M-ANP	10.00	20%	110.0	145.0	2.5	3.5
PSPMAA0503-150M-ANP	15.00	20%	192.0	215.0	2.0	3.0
PSPMAA0503-220M-ANP	22.00	20%	230.0	275.0	1.5	2.5
PSPMAA0503-330M-ANP	33.00	20%	325.0	360.0	1.0	2.0

