

1 2 3 4 5 6 7 8

RoHs

Current Rating: 1.5 Amps

Insulation Resistance: 1000M Ω Min

Contact Resistance: 20m Ω Max

Withstanding Voltage: AC 500V

Operation Temperature: -40 $^{\circ}$ to+105 $^{\circ}$

Contact Material: Brass

Standard: PA6T

Insrlator Material: Polyester(UL 94V-0)

Contact Plating: Gold Flash

Max.Processing Temp: 240 $^{\circ}$ C for30-60seconds (260 $^{\circ}$ C for 5 seconds)

VER	MARK	PR. BY	DESCRIPTION	DATE

(B+0.4) $\pm$ 0.3

A $\pm$ 0.1

2.00

4.50 $\pm$ 0.15

4.30 $\pm$ 0.15

2.00 $\pm$ 0.1

PIN 0.50X0.2

2.80 $\pm$ 0.2

2.00 $\pm$ 0.2

2.00

ϕ 0.80

2.00

A

RECOMMEND P.C.B LAYOUT

PCB TOLERANCE: $\pm$ 0.05 (TOP VIEW)

P/N	PIN	DIM. A	DIM. B
A20020130-2PB2114-H43C28	2*1	0.00	2.00
A20020130-4PB2114-H43C28	2*2	2.00	4.00
A20020130-6PB2114-H43C28	2*3	4.00	6.00
A20020130-8PB2114-H43C28	2*4	6.00	8.00
A20020130-10PB2114-H43C28	2*5	8.00	10.00
A20020130-12PB2114-H43C28	2*6	10.00	12.00
A20020130-14PB2114-H43C28	2*7	12.00	14.00
A20020130-16PB2114-H43C28	2*8	14.00	16.00
A20020130-18PB2114-H43C28	2*9	16.00	18.00
.....			
A20020130-80PB2114-H43C28	2*40	(PIN-1)x2.0	(PIN)x2.0


GENERAL TOLERANCES UNLESS SPECIFIED		PART NO. A20020130-XPB2114-H43C28		TITLE: 2.0FH H4.3 2xnPin 180 度 W4.5 U型 PC2.8 6T	
X. $^{\circ}$ $\pm$ 0.30	X. $^{\circ}$ $\pm$ 5 $^{\circ}$	DESIGN:	James	CUSTOMER	SIZE
X.X $^{\circ}$ $\pm$ 0.20	X.X $^{\circ}$ $\pm$ 1 $^{\circ}$	CHED:	Talen		A4
X.XX $^{\circ}$ $\pm$ 0.10	X.XX $^{\circ}$ $\pm$ 0.5 $^{\circ}$	APPD:	Sophia		MM
MANUFACTURE DWG					UNITS
					MM
					SCALE
					SHEET
					N:A
					1/1

1 2 3 4 5 6 7 8

1 2 3 4 5 6 7 8

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)

P/N	PIN	$DIM. A$	$DIM. B$
A20020130-2PB2114-H43C28	2*1	0. 00	2. 00
A20020130-4PB2114-H43C28	2*2	2. 00	4. 00
A20020130-6PB2114-H43C28	2*3	4. 00	6. 00
A20020130-8PB2114-H43C28	2*4	6. 00	8. 00
A20020130-10PB2114-H43C28	2*5	8. 00	10. 00
A20020130-12PB2114-H43C28	2*6	10. 00	12. 00
A20020130-14PB2114-H43C28	2*7	12. 00	14. 00
A20020130-16PB2114-H43C28	2*8	14. 00	16. 00
A20020130-18PB2114-H43C28	2*9	16. 00	18. 00
.....			
A20020130-80PB2114-H43C28	2*40	$(PIN-1) \times 2. 0$	$(PIN) \times 2. 0$



GENERAL TOLERANCES UNLESS SPECIFIED		<			
--	--	---	--	--	--