




RoHS

SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)

VER	MARK	PR. BY	DESCRIPTION	DATE



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

P/N	PIN	DIM. A	DIM. B
A25420220-1PB2113-H85C32	1	0.00	2.54
A25420220-2PB2113-H85C32	2	2.54	5.08
A25420220-3PB2113-H85C32	3	5.08	7.62
A25420220-4PB2113-H85C32	4	7.62	10.16
A25420220-5PB2113-H85C32	5	10.16	12.70
A25420220-6PB2113-H85C32	6	12.70	15.24
A25420220-7PB2113-H85C32	7	15.24	17.78
A25420220-8PB2113-H85C32	8	17.78	20.32
A25420220-9PB2113-H85C32	9	20.32	22.86
.....			
A25420220-40PB2113-H85C32	40	(PIN-1) X 2.54	(PIN) X 2.54

GENERAL TOLERANCES
UNLESS SPECIFIED

X.° ±0.30	X.° ±5°
X.X° ±0.20	X.X° ±1°
X.XX° ±0.10	X.XX° ±1°

MANUFACTURE DWG



深圳市华明通电子有限公司
Shenzhen Huamingtong Electronics Co., Ltd

PART NO.
A25420220-XPB2113-H85C32

TITLE: 2.54FH H8.5 1xnPin
180度 Y型 PC3.2 6T

DESIGN: James
CHED: Talen
APPD: Sophia

CUSTOMER	SIZE	UNITS
	A4	MM
	SCALE	SHEET
	N:A	1/1

