

# HER501 THRU HER508

## High Efficiency Rectifier



**Voltage:** 50~1000 Volts

**Current:** 5 Amperes

**Package:** DO-27

### Features

- NH'S High Efficiency Rectifier Chip Technology
- Low Switching Loss For High Efficiency
- Low Leakage Current For High Reliability
- Ultra Fast Switching Speed

### Mechanical Data

- **Case:** Molded With UL-94 ClassV-0 Recognized, RoHS-Compliant
- **Polarity:** Look At The Diagram And Polarity On The Right
- **Terminals:** Tin Plated Leads,Solderable Per J-STD-002 And JESD22-B102

### Typical Applications

- Switch Mode Power Supplies (SMPS)
- Fast Chargers
- LED Driver And Monitor Lighting
- Automotive Electronics And Charging Posts

### Diagram:



### Polarity:



Single Phase,Half Wave,60Hz,Resistive Or Inductive Load.For Capacitive Load,Derate Current By 20%

### Maximum Ratings (Ta=25°C Unless Otherwise Specified)

Parameter	Test Conditions	Symbol	HER 501	HER 502	HER 503	HER 505	HER 506	HER 507	HER 508	Unit
Maximum Repetitive Peak Reverse Voltage		$V_{RRM}$	50	100	200	400	600	800	1000	V
Maximum RMS Voltag		$V_{RMS}$	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage		$V_{DC}$	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current		$I_{F(AV)}$	5							A
Peak Forward Surge Current	8.3ms Single Half Sine-wave Superimposed On Rate Load	$I_{FSM}$	125							A
Current Squared Time	$t < 8.3ms$	$I^2t$	64.8							A <sup>2</sup> sec

### Electrical Characteristics (Ta=25°C Unless Otherwise Specified )

Parameter	Test Conditions	Symbol	HER 501	HER 502	HER 503	HER 505	HER 506	HER 507	HER 508	Unit
Maximum Instantaneous Forward Voltage	I <sub>F</sub> = 5.0 A	V <sub>F</sub>	1.00				1.30	1.70		V
Maximum DC Reverse Current at Rated DC Blocking Voltage	Ta=25°C ,V <sub>R</sub> =VRRM Ta=125°C ,V <sub>R</sub> =VRRM*80%	I <sub>RRM</sub>	5 200							uA uA
Typical Junction Capacitance	4 V,1MHz	C <sub>J</sub>	60			25	20			pF
Maximum Reverse Recovery Time	IF=0.5A, IR=1.0A, IRR=0.25A	Trr	50				75			nS

### Thermal Characteristics (Ta=25°C Unless Otherwise Specified )

Parameter	Test Conditions	Symbol	HER 501	HER 502	HER 503	HER 505	HER 506	HER 507	HER 508	Unit
Operating Junction Temperature Range		T <sub>J</sub>	-55~150							℃
Storage Temperature Range		T <sub>STD</sub>	-55~150							
Thermal Resistance Junction To Ambient With Steady-State	Still Air Environment With Ta=25℃	R <sub>θJA</sub>	53.0							℃/W
Thermal Resistance Junction-Case With Steady-State	At 0.375"(9.5mm) lead length Mounted On vertical P.C. Board	R <sub>θJC</sub>	16.0							

Notes: 1.Pulse Test: 300 Us Pulse Width,1% Duty Cycle

**HER501 THRU HER508**

High Efficiency Rectifier



Typical Characteristics Curves




Fig.1-FORWARD CURRENT DERATING CURVE




Fig.2- TYPICAL INSTANTANEOUS FORWARD




Fig.3- TYPICAL REVERSE CHARACTERISTICS




Fig.4- TYPICAL JUNCTION CAPACITANCE




Fig.5-MAX. NON-REPETITIVE SURGE CURRENT





Fig.6-REVERSE RECOVERY TIME CHARACTERISTIC AND TEST CIRCUIT

HER501 THRU HER508  
High Efficiency Rectifier



OUTLINE DRAWINGS


DO-27



OUTLINE DIMENSIONS						
Dim.	Milimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	4.90	-	5.60	0.1929	-	0.2205
B	8.00	-	10.00	0.3150	-	0.3937
C	1.00	-	1.40	0.0394	-	0.0551
D	24.50	-	26.50	0.9646	-	1.0433

COMPONENT PITCH DIMENSION DIAGRAM

DO-27



OUTLINE DIMENSIONS						
Dim.	Milimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	9.50	-	10.50	0.3740	-	0.4134
B	51.00	-	53.00	2.0079	-	2.0866
C	5.50	-	6.50	0.2165	-	0.2559
D	-	-	1.20	-	-	0.0472
[L2-L1]	-	-	1.00	-	-	0.0394

# HER501 THRU HER508

High Efficiency Rectifier



## MARKING



## MARKING INSTRUCTION

NH=Niuhan Trademark  
FF=Product Line Code,According To Actual Changes  
DDK=Inernal Code,According To Actual Changes  
HER5xx=Modelx=01,02,03,05,06,07,08  
White band denotes cathode

## PACKING INFORMATION

Package Type	Package Code	Product Weight Approx(g/Pcs)	Package Method	Quantity (Pcs/Min. Pack.)	Quantity (Pcs/Inner Box)	Quantity (Pcs/Carton)
DO-27	P1	1	Tube	1000	1000	20000
DO-27	P2	1	Tape	1250	1250	12500

**HER501 THRU HER508**


**High Efficiency Rectifier**



**Recommended wave soldering condition**

Product	Peak Temperature	Soldering Time
Pb-free devices	260 +0/-5 °C	5 +1/-1 seconds

**Recommended temperature profile for IR reflow**



Profile feature	Sn-Pb eutectic Assembly	Pb-free Assembly
Average ramp-up rate (T <sub>smax</sub> to T <sub>p</sub> )	3°C/second max.	3°C/second max.
Preheat -Temperature Min(TS min) -Temperature Max(TS max) -Time(ts min to ts max)	100°C 150°C 60-120 seconds	150°C 200°C 60-180 seconds
Time maintained above: -Temperature (TL) - Time (tL)	183°C 60-150 seconds	217°C 60-150 seconds
Peak Temperature(TP)	240 +0/-5 °C	260 +0/-5 °C
Time within 5°C of actual peak temperature(tp)	10-30 seconds	20-40 seconds
Ramp down rate	6°C/second max.	6°C/second max.
Time 25 °C to peak temperature	6 minutes max.	8 minutes max.

Note : All temperatures refer to topside of the package, measured on the package body surface.

**HER501 THRU HER508**

**High Efficiency Rectifier**



**Disclaimer**

- Reproducing and modifying information of the document is prohibited without permission from Niuhan Electronics Technology Co., LTD
- Niuhan Electronics Technology Co., LTD. reserves the rights to make changes of the content herein the document anytime without notification.
- Niuhan Electronics Technology Co., LTD. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Niuhan Electronics Technology Co., LTD. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Niuhan Electronics Technology Co., LTD. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Niuhan Electronics Technology Co., LTD. for any damages resulting from such improper use or sale.
- When the appearance of the product and chip size does not change, in order to product the customer. quality, change the internal structure and the production process Niuhan can not notify