

Features

- Zero Forward/Reverse Recovery Current
- High Blocking Voltage
- High Frequency Operation
- Positive Temperature Coefficient on V_F
- Temperature Independent Switching Behavior
- High surge current capability

Benefits

- Higher System Efficiency
- Parallel Device Convenience without thermal runaway
- Higher Temperature Application
- No Switching loss
- Hard Switching & Higher Reliability
- Environmental Protection

Applications

- Server/Telecom Power Supplies
- Solar Inverters
- AC/DC converters
- DC/DC converters
- Uninterruptable power supplies



Maximum Ratings

Parameter	Symbol	Test Conditions	Value	Unit
Repetitive Peak Reverse Voltage	V_{RRM}	$T_J = 25^{\circ}\text{C}$	650	V
Surge Peak Reverse Voltage	V_{RSM}	$T_J = 25^{\circ}\text{C}$	650	V
DC Blocking Voltage	V_R	$T_C = 25^{\circ}\text{C}$	650	V
Forward Current	I_F	$T_C \leq 135^{\circ}\text{C}$ $T_C \leq 150^{\circ}\text{C}$	35 30	A
Non-Repetitive Forward Surge Current	I_{FSM}	$T_C = 25^{\circ}\text{C}$, $t_p = 8.3\text{ms}$, Half Sine Wave	210	A
Power Dissipation	P_{tot}	$T_C = 25^{\circ}\text{C}$	234	W
Maximum Case Temperature	T_C		143	$^{\circ}\text{C}$
Operating Junction and Storage Temperature	T_J, T_{STG}		-55 to 175	$^{\circ}\text{C}$
TO-247 Mounting Torque		M3 Screw	1	Nm

Ordering Information

Order number	Package	Marking	Operation Temperature Range	MSL Grade	Ship, Quantity	Green
SSD3065CTDL	TO-247-2	SC6D30065H	-55 to 175 $^{\circ}\text{C}$	1	TUBE, 450	Rohs

Electrical Characteristics

Parameter	Symbol	Test Conditions	Typ.	Max.	Unit
Forward Voltage	V_F	$I_F = 30A, T_J = 25^{\circ}C$	1.5	1.8	V
		$I_F = 30A, T_J = 175^{\circ}C$	1.78	2.3	
Reverse Current	I_R	$V_R = 650V, T_J = 25^{\circ}C$	2	20	μA
		$V_R = 650V, T_J = 175^{\circ}C$	15	200	
Total Capacitance	C	$V_R = 0V, T_J = 25^{\circ}C, f = 1MHz$	1805	/	pF
		$V_R = 200V, T_J = 25^{\circ}C, f = 1MHz$	176		
		$V_R = 400V, T_J = 25^{\circ}C, f = 1MHz$	145		
Total Capacitive Charge	Q_C	$V_R = 650V, I_F = 30A$ $di/dt = 200A/\mu s, T_J = 25^{\circ}C$	66	/	nC

Thermal Characteristics

Parameter	Symbol	Typ.	Unit
Thermal Resistance from Junction to Case	$R_{\theta JC}$	0.64	$^{\circ}C/W$
Thermal Resistance from Junction to Ambient	$R_{\theta JA}$	80	$^{\circ}C/W$
Soldering Temperature	T_{solder}	260	$^{\circ}C$

Typical Performance




Figure 1. Forward Characteristics




Figure 2. Reverse Characteristics

Typical Performance




Figure 3. Power Derating




Figure 4. Total Capacitive Charge vs. Reverse Voltage




Figure 5. Total Capacitance vs. Reverse Voltage





Figure 6. Transient Thermal Impedance

Package Dimensions

(TO-247-2 Package)



SYMBOL	MIN	MAX	MIN	MAX
	[mm]	[mm]	[INCH]	[INCH]
A	4.69	5.31	0.185	0.209
B	1.49	2.49	0.059	0.098
C	2.21	2.59	0.087	0.102
D	0.40	0.79	0.016	0.031
E	5.38	6.20	0.212	0.244
F	3.50	3.81	0.138	0.150
G	6.15BSC		0.242BSC	
H	20.80	21.46	0.819	0.845
I	19.81	20.32	0.780	0.800
J	4.00	4.50	0.157	0.177
K	1.01	1.40	0.040	0.055
L	2.87	3.12	0.113	0.123
M	1.65	2.13	0.065	0.084
N	15.49	16.26	0.610	0.640
O	13.50	14.50	0.531	0.571
P	16.50	17.50	0.650	0.689
Q	5.45BSC		0.215BSC	
R	2.00	2.75	0.079	0.108
S	7.10	7.50	0.280	0.295

Revision History

Rev.	Change	Date
V1.0	Initial version	2/23/2022

Important Notice

JSMSEMI Semiconductor (JSMSEMI) PRODUCTS ARE NEITHER DESIGNED NOR INTENDED FOR USE IN MILITARY AND/OR AEROSPACE, AUTOMOTIVE OR MEDICAL DEVICES OR SYSTEMS UNLESS THE SPECIFIC JSMSEMI PRODUCTS ARE SPECIFICALLY DESIGNATED BY JSMSEMI FOR SUCH USE. BUYERS ACKNOWLEDGE AND AGREE THAT ANY SUCH USE OF JSMSEMI PRODUCTS WHICH JSMSEMI HAS NOT DESIGNATED FOR USE IN MILITARY AND/OR AEROSPACE, AUTOMOTIVE OR MEDICAL DEVICES OR SYSTEMS IS SOLELY AT THE BUYER' S RISK.

JSMSEMI assumes no liability for application assistance or customer product design. Customers are responsible for their products and applications using JSMSEMI products.

Resale of JSMSEMI products or services with statements diferent from or beyond the parameters stated by JSMSEMI for that product or service voids all express and any implied warranties for the associated JSMSEMI product or s ervice. JSMSEMI is not responsible or liable for any such statements.

JSMSEMI All Rights Reserved. Information and data in this document are owned by JSMSEMI wholly and may not be edited, reproduced, or redistributed in any way without the express written consent from JSMSEMI.

Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the JSMSEMI product that you intend to use.

For additional information please contact Kevin@jsmsemi.com or visit www.jsmsemi.com