

GT - SM 020A - H300-02-K

G-SWITCH



Detail
A=With a
cardholder

Cato code

Card holder series
SM=SIM CARD

Product high(mm)
H300=3.0

Operating mode
02=Push-Push




The letters are in a
forward direction

G-Switch Specification:

- 1.The product surface is free of dirt, scratches and deformities.
 2. The plastic body has no burrs and is fully injected; the contact piece shows no signs of oxidation or rust.
- Note: The thickness of the gold plating layer on the contact piece can be adjusted according to customer requirements.

2	CONTACTANT	PHOSPHOROUS BRONZE	Au PLATING
1	DRAWER	HIGH TEMPERATURE PLASTIC	PBT BLACK UL 94 V-0
NO.	PART NAME	MATERIAL	REMARK



SCALE: 1:1	UNIT: mm	Title: Horizontal SIM Card SMT H3.0mm TRAY				 品赞科技® www.dg-switch.com			
SIZE: A4									
Unless otherwise General tolerance: X ±0.40 X.x ±0.30 X.xx ±0.20 X° ±5° X.x° ±3°									
		DRAWN	CHECKED	APPROVED	DATE				
		Jiang	Xia	Chen	2024.03.10	REV: A0	SHEET: 1/1		