






- 4 "E" IDENTIFIES E-SEAL, LOCATED APROX. AS SHOWN
- 3 MATERIAL: HOUSING: PA66 GF15, SEE TABLE FOR COLOR
END CAP: PA66 GF15
GROMMET: E-SEAL VMO (RED-ORANGE)
N-SEAL VMO (BURNT ORANGE)
BLOCKED VMO (BURNT ORANGE)
INTERFACE SEAL: SILICONE, PHENYL FLUID LUBED (GREEN)
SEAL RETAINER: PA66 GF15

2. THIS PLUG MATES WITH DTP06-2S-XXXX PLUG.
(XXXX = ALL MODIFICATIONS)
1. SECONDARY WEDGE LOCK SOLD SEPARATELY: WP-2P
- NOTES: UNLESS OTHERWISE SPECIFIED

TE INTERNAL PART NUMBER	DEUTSCH PART NUMBER	HOUSING COLOR	STANDARD SEAL	EXTRA THIN SEAL E SEAL	BLOCKED SEAL	SHORT CAP	LONG CAP	FIGURE
DTP04-2P	DTP04-2P	GREY	X					1
DTP04-2P-E004	DTP04-2P-E004	BLACK	X					1
DTP04-2P-E003	DTP04-2P-E003	GREY	X			X		2
DTP04-2P-EE01	DTP04-2P-EE01	BLACK	X				X	3
DTP04-2P-E005	DTP04-2P-E005	BLACK	X	X		X		2
DTP04-2P-C015	DTP04-2P-C015	GREY		X				1
DTP04-2P-CE01	DTP04-2P-CE01	GREY		X		X		2
DTP04-2P-CE02	DTP04-2P-CE02	BLACK		X				1
DTP04-2P-CE03	DTP04-2P-CE03	BLACK		X		X		1
DTP04-2P-CE09	DTP04-2P-CE09	BLACK		X			X	3
DTP04-2P-C017	DTP04-2P-C017	GRAY			X			4

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
IN [mm]

MATERIAL

3

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±.025 (0.64)
4 PLC ±
ANGLES ±
FINISH

-

DWN R. ARAUS 08APR2025
CHK C. OJEDA 08APR2025
APVD C. BHATT 08APR2025

PRODUCT SPEC
108-151012
APPLICATION SPEC
114-151012
WEIGHT

CUSTOMER DRAWING

NAME
2 WAY REC, STANDARD SEAL, EXTRA THIN SEAL, BLOCKED SEAL, SHORT AND LONG CAP, DTP SERIES

SIZE
A

CAGE CODE
00779

DRAWING NO
DTP04-2P-XXXX

RESTRICTED TO
-


SCALE
1:1

SHEET
1

OF
2

REV
A

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD




△ PARTS MARKED FOR INTERNAL USE ONLY
- DATE CODE: MONTH USES SEQUENTIAL ALPHA CHARACTERS, EX: A=JANUARY
YEAR USES LAST NUMERICAL DIGIT, EX: 4=2024

△ FOR CONTACTS AND WIRE PERFORMANCE AND APPLICATION
CHARACTERISTICS SEE PRODUCT SPECIFICATION 108-151000

△ MODIFICATION: GROMMET CAVITIES ARE BLOCKED

NOTES:

TE INTERNAL PART NUMBER	CONTACT SIZE	WIRE RANGE [mm ²] REF. ONLY	SEAL	MIN. INSUL. O. D.	MAX. INSUL. O. D.
DTP04-2P	12	10-14 AWG [5.0 - 2.0]	STANDARD SEAL	.134 [3.40]	.170 [4.32]
DTP04-2P-E004					
DTP04-2P-E003					
DTP04-2P-EE01					
DTP04-2P-E005					
DTP04-2P-C015			E SEAL	.097 [2.46]	.158 [4.01]
DTP04-2P-CE01					
DTP04-2P-CE02					
DTP04-2P-CE03					
DTP04-2P-CE09					
THIS DRAWING IS A CONTROLLED DOCUMENT.			TE Connectivity		
DIMENSIONS: IN [mm]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		DWN R. ARAUS 08APR2025		2 WAY REC, STANDARD SEAL, EXTRA THIN SEAL, BLOCKED SEAL, SHORT AND LONG CAP, DTP SERIES	
		CHK C. OJEDA 08APR2025			
		APVD S. BHATT 08APR2025			
		PRODUCT SPEC			
0 PLC ±		108-151012		SIZE	
1 PLC ±		APPLICATION SPEC		CAGE CODE	
2 PLC ±		114-151012		DRAWING NO	
3 PLC ±.025 (0.64)				DTP04-2P-XXXX	
4 PLC ±				RESTRICTED TO	
ANGLES ±				-	
FINISH		WEIGHT			
MATERIAL SEE SHEET 1		CUSTOMER DRAWING		SCALE 1:1 SHEET 2 OF 2 REV A	