

PDFN5060 Plastic-Encapsulate MOSFETS

Features

- VDS=60V
- ID=55A
- RDS(on)@VGS=10V < 10mΩ
- RDS(on)@VGS=4.5V < 14.5mΩ
- High density cell design for ultra low Rdson
- Voltage controlled small signal switch
- Fast Switching Speedze


Applications

- Power Switching Application
- Hard switched and high frequency circuits
- Uninterruptible power supply

Mechanical Data

- Case: PDFN5060
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant,halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750,Method 2026

Function Diagram



Drain-source Voltage
60 V
Drain Current
55 Ampere



Ordering Information

Table with 7 columns: PACKAGE, PACKAGE CODE, UNIT WEIGHT(g), REEL(pcs), BOX(pcs), CARTON(pcs), DELIVERY MODE. Row 1: PDFN5060, R3, 0.09, 5000, 10000, 80000, 13"

Maximum Ratings (Ta=25°C Unless otherwise specified)

Table with 4 columns: PARAMETER, SYMBOL, UNIT, VALUE. Rows include: Drain-source Voltage (VDS, V, 60), Gate-source Voltage (VGS, V, ±20), Drain Current (ID, A, 55), Pulsed Drain Current (IDM, A, 220), Total Power Dissipation (PD, W, 60), Single pulse avalanche energy (EAS, mJ, 72), Junction temperature (TJ, °C, -55 ~+150), Storage temperature (Tstg, °C, -55 ~+150), Thermal Resistance Junction-to-Case (RθJC, °C / W, 2.08).

● Static Parameter Characteristics (Tj=25°C Unless otherwise specified)

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Drain-Source Breakdown Voltage	BV_{DSS}	$V_{GS}=0V, I_D=250\mu A$	V	60	—	—
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS}=60V, V_{GS}=0V$	μA	—	—	1.0
Gate-Body Leakage Current	I_{GSS}	$V_{GS}=\pm 20V, V_{DS}=0V$	nA	—	—	± 100
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=250\mu A$	V	1.0	1.8	2.5
Static Drain-Source On-Resistance ⁽³⁾	$R_{DS(ON)}$	$V_{GS}=10V, I_D=20A$	m Ω	—	6.5	10
	$R_{DS(ON)}$	$V_{GS}=4.5V, I_D=10A$		—	8.5	14.5

● Dynamic Parameters

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Input Capacitance	C_{iss}	$V_{DS}=30V, V_{GS}=0V, f=1MHz$	pF	—	1210	—
Output Capacitance	C_{oss}			—	338	—
Reverse Transfer Capacitance	C_{rss}			—	15	—

● Switching Parameters







PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Turn-on Delay Time	$t_{D(on)}$	$V_{GS}=10V, V_{DD}=30V, I_D=20A, R_{GEN}=4.7\Omega$	nS	—	14	—
Turn-on Rise Time	t_r		nS	—	26	—
Turn-off Delay Time	$t_{D(off)}$		nS	—	33.8	—
Turn-off fall Time	t_f		nS	—	26.4	—
Total Gate Charge	Q_g	$V_{DS}=30V, I_D=20A, V_{GS}=10V$	nC	—	16	—
Gate-Source Charge	Q_{gs}		nC	—	4	—
Gate-Drain Charge	Q_{gd}		nC	—	3	—

● Drian-Source Diode Characteristics






PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Diode Forward Voltage	V_{SD}	$I_S=55, V_{GS}=0V$	V	—	—	1.2
Maximum Body-Diode Continuous Current	I_S	—	A	—	—	55
Reverse Recovery Time	V_{rr}	$I_S=55A, di/dt=100A/us, T_J=25^\circ C$	nS	—	36	—
Reverse Recovery Charge	Q_{rr}		nC	—	23	—

Note :
(1)Repetitive Rating: Pulse width limited by maximum junction temperature.
(2)EAS condition : Tj=25°C ,VDD=30V,VG=10V,L=0.3mH,IAS=22A,Rg=25Ω.
(3)Pulse Test: Pulse Width ≤ 300μs, Duty Cycle ≤ 2%.


● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)




● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)




Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)





Package Outline Dimensions (PDFN5060)





Suggested Pad Layout





1. Gate Charge Test Circuit & Waveforms



2. Resistive Switching Test Circuit & Waveforms



3. Unclamped Inductive Switching (UIS) Test Circuit & Waveforms



4. Diode Recovery Test Circuit & Waveforms

