



SEA & LAND ELECTRONIC CORP.

WWW.SEALAND-PPTC.COM

ALPHA-TOP TECHNOLOGY CORP.

APPROVAL SHEET

MODEL NO.: SMD1210-150-13.2V

CUSTOMER:

CUSTOMER'S APPROVAL:

AUTHORIZED SIGNATURE/STAMP:

DATE

MANUFACTURER:

HEAD OFFICE:


13F., No. 120-10, Sec. 3, Zhongshan Rd., Zhonghe Dist., New Taipei City 23544, Taiwan
Tel: 886-2-8221-2567
Fax: 882-2-2225-7268
E-mail: service@chipfast.com.tw

China Branch:

Factory Building B) Shuangpeng, Weibu Village, Qiuchang Town,
Huiyang District, Huizhou City, Guangdong Province, P.R.C.)
Tel: 86-752-3562001
Fax: 86-752-3558696
E-mail: service@atppte.com

Submitted by: Chung Cheng
Approved by: YC Lin
DATE: 2-Mar-22

SEA & LAND ELECTRONIC CORP.



Features

- Surface Mount Devices
- Lead free device
- Size 3.2*2.5mm/0.12*0.10 inch
- Surface Mount packaging for automated assembly

Applications

Almost anywhere there is a low voltage power supply, up to 30V and a load to be protected, including:
■ Computer mother board, Modem.
■ Telecommunication equipments.

SMD1210-150-13.2V

Alpha-Top (Sea&Land Alliance)

Performance Specification

Model	Marking	V_{max}	I_{max}	I_{hold}	I_{trip}	P_d	Maximum Time To Trip		Resistance		Agency Approval	
		(Vdc)	(A)	@25°C (A)	@25°C (A)	Max. (W)	Current (A)	Time (Sec)	R_{imin} (Ω)	$R1max$ (Ω)	UL	TUV
SMD1210-150-13.2V	αL	13.2	100	1.50	3.00	0.6	8.0	0.50	0.030	0.110		

I_{hold} = Hold Current. Maximum current device will not trip in 25°C still air.
I_{trip} = Trip Current. Minimum current at which the device will always trip in 25°C still air.
V_{max} = Maximum operating voltage device can withstand without damage at rated current (I_{max}).
I_{max} = Maximum fault current device can withstand without damage at rated voltage (V_{max}).
P_d = Power dissipation when device is in the tripped state in 25°C still air environment at rated voltage.
R_{imin}/max = Minimum/Maximum device resistance prior to tripping at 25°C.
R_{1max} = Maximum device resistance is measured one hour post reflow.
CAUTION : Operation beyond the specified ratings may result in damage and possible arcing and flame.

Environmental Specifications

Test	Conditions	Resistance change
Passive aging	+85°C, 1000 hrs.	±5% typical
Humidity aging	+85°C, 85% R.H. , 168 hours	±5% typical
Thermal shock	+85°C to -40°C, 20 times	±33% typical
Resistance to solvent	MIL-STD-202, Method 215	No change
Vibration	MIL-STD-202, Method 201	No change
Ambient operating conditions : - 40 °C to +85 °C		
Maximum surface temperature of the device in the tripped state is 125 °C		

Agency Approvals :

Regulation/Standard:



2015/863/EU



EN14582

I_{hold} Versus Temperature

Model	Maximum ambient operating temperature (T _{mao}) vs. hold current (I _{hold})									
	-40°C	-20°C	0°C	25°C	40°C	50°C	60°C	70°C	85°C	
SMD1210-150-13.2V	2.13	1.92	1.71	1.50	1.26	1.14	1.01	0.89	0.71	


SMD1210-150-13.2V

Alpha-Top (Sea&Land Alliance)

Construction And Dimension (Unit:mm)


Model	A		B		C		D		E	
	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.
SMD1210-150-13.2V	3.00	3.43	2.35	2.80	0.50	1.20	0.30	0.30	0.10	0.10

Dimensions & Marking



α = Trademark
L = Part identification

Recommended Pad Layout (mm)




Termination Pad Characteristics

Terminal pad materials : Tin-plated Nickel-Copper
Terminal pad solderability : Meets EIA specification RS186-9E and ANSI/J-STD-002 Category 3.


Rework

Use standard industry practices, the removal device must be replaced with a fresh one.

Thermal Derating Curve



Typical Time-To-Trip At 25°C




WARNING:

- Use PPTC beyond the maximum ratings or improper use may result in device damage and possible electrical arcing and flame.
- PPTC are intended for protection against occasional over current or over temperature fault conditions and should not be used when repeated fault conditions or prolonged trip events are anticipated.
- Device performance can be impacted negatively if devices are handled in a manner inconsistent with recommended electronic, thermal, and mechanical procedures for electronic components.
- Use PPTC with a large inductance in circuit will generate a circuit voltage (L di/dt) above the rated voltage of the PPTC.
- Avoid impact PPTC device its thermal expansion like placed under pressure or installed in limited space.
- Contamination of the PPTC material with certain silicon based oils or some aggressive solvents can adversely impact the performance of the devices. PPTC SMD can be cleaned by standard methods.
- Requests that customers comply with our recommended solder pad layouts and recommended reflow profile. Improper board layouts or reflow profile could negatively impact solderability performance of our devices.

SMD1210-150-13.2V

Alpha-Top (Sea&Land Alliance)

Recommended Solder Reflow Conditions




- Recommended reflow methods : IR, vapor phase oven, hot air oven.
 - Devices are not designed to be wave soldered to the bottom side of the board.
 - Recommended maximum paste thickness is 0.25 mm (0.010 inch).
 - Devices can be cleaned using standard method and solvents.
- Note : If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.


Tape And Reel Specifications (mm)

Governing Specifications	EIA 481-2
W	8.0 ± 0.20
P0	4.0 ± 0.10
P1	4.0 ± 0.10
P2	2.0 ± 0.10
A0	2.82 ± 0.10
B0	3.52 ± 0.10
B1max.	4.35
D0	1.5 + 0.1, -0.0
F	7.5 ± 0.05
E1	1.75 ± 0.10
E2min.	6.25
Tmax.	0.6
T1max.	0.1
K0	0.90 ± 0.1
Leader min.	390
Trailer min.	160
Reel Dimensions	
A max.	178
N min.	50
W1	8.4 + 1.5, -0.0
W2max.	22.4

EIA Tape Component Dimensions



EIA Reel Dimensions



Storage And Handling


- Storage conditions : 40°C max, 70% R.H.
- Devices may not meet specified performance if storage conditions are exceeded.

Order Information

SMD1210	150-13.2V	Packaging
Product name	Hold	Tape & Reel Quantity
Size 3225 mm / 1210 inch	Current	4,500 pcs/reel
SMD : surface mount device	1.50A	

Tape & reel packaging per EIA481-1

Labeling Information



0.25A		0.35A		0.50A		0.75A		1.00A		3.00A	
TTT	Ihold	TTT	Ihold	TTT	Ihold	TTT	Ihold	TTT	Ihold	TTT	Ihold
(Sec)	(A)	(Sec)	(A)	(Sec)	(A)	(Sec)	(A)	(Sec)	(A)	(Sec)	(A)
				100	1					40	5.5
				7.762471	1.39					7.762471	7.4645
				1.44544	2.0701					1.44544	13.183
				0.45	3.1					0.45	20
				0.12	5.1					0.18197	30
				0.041	10					0.089125	40

Temperature (°C)	Hold (A)	Derating (A)	Derating %
-40	1.1	1.60	145.455
-30	1.1	1.53	138.636
-20	1.1	1.45	131.818
-10	1.1	1.37	124.091
0	1.1	1.28	116.364
10	1.1	1.19	108.182
20	1.1	1.10	100.000
30	1.1	1.01	91.818
40	1.1	0.92	83.636
50	1.1	0.83	75.455
60	1.1	0.75	67.727
70	1.1	0.66	60.000
80	1.1	0.58	52.273
90	1.1	0.49	44.545